

Portable Field Deployable Fiber Optic Cable Reel Datasheet



Overview

Handle-held Portable Field Deployable Industrial Fiber Optic Cable Reel

The fiber optic cable reel is made of ABS and PC material, which is ideal for using in communication, broadcast and pro audio applications. It is used with industrial jumpers, network cables, audio and video cables, and offers significant cost savings through direct cable integration into reel housing. With a variety of cable assembly options and configurations, flexibility is provided to meet the specific requirements of each application, including storage efficiency, rapid deployment and ease of operation.

Benefits

- Cable Capacity from 50m to 620m or 100m to 1060m
- Keep Your Cords Organized and Ready for Action
- Constructed from ABS and PC Material with a Strong Durable Design and Built to Last
- Convenient Carry Handle for Quick and Easy Transportation
- Used with Industrial Cables, Network Cables, Audio and Video Cables, etc.

Product Specification


CHARACTERISTICS

Product Specification		
Part Number	PTOA-FS-310	PTOA-FS-380
ID	#185817	#185816
Product Color	Black	Black
Main Disk Outer Diameter	312mm (12.28")	380mm (14.96")
Shaft Diameter	176mm (6.93")	236mm (9.29")
Disc Width	123mm (4.84")	174mm (6.85")
Dimensions (LxWxH)	292x392x241mm (11.50"x15.43"x9.49")	339x488x341mm (13.35"x19.21"x13.43")
Net Weight	≤3kg	≤5kg
Gross Weight	≤7kg	≤9kg
Package Size	365x295x425mm (14.37"x11.61"x16.73")	405x310x510mm (15.94"x12.20"x20.08")
Material	ABS+PC	ABS+PC

Product Specification

PTOA-FS-310


Cable Diameter	3.0mm	4.0mm	5.0mm	6.0mm	7.0mm	8.0mm	9.0mm	10.0mm
Capacity	620m	280m	226m	150m	110m	80m	70m	50m



Dimensions are in millimeters.

PTOA-FS-380

Cable Diameter	3.0mm	4.0mm	5.0mm	6.0mm	7.0mm	8.0mm	9.0mm	10.0mm
Capacity	1060m	590m	380m	300m	220m	170m	130m	100m



Dimensions are in millimeters.