

Singlemode Metal Fiber Optic Adapter Datasheet

For 1.25mm Ferrulew/Jacket Strap



Overview

The interface of the fiber optic connector is usually the port connecting the fiber optic connector, which is used for the fiber optic connector or the fiber optic connector, the fiber optic connector.

Benefits

- $\leq 0.2\text{dB}$ (Typical) Low Insertion Loss
- ST Guarantees for Long-term Stable Mechanical Properties and Repeated matching
- Zirconia Ceramic Sleeve with High Precision Alignment
- Protective Dust Cover Keeps the Inside of The Adapter Clean From Dust
- Threaded Adapter for Easy Installation and Removal

Technical Specification

Product	ST to ST Adapter
Mode	Singlemode
Insertion Loss	≤0.2dB
Return Loss	≥45dB
Operating Temperature	-40℃~85℃
Storage Temperature	-40℃~85℃

Product Specification

