


Blank Patch Panel, 24-Port, 1RU, Cable Management Bar Included

MANAGING AND ORGANISING COPPER ETHERNET NETWORK



Overview

The 24-port blank keystone patch panel is ideal for data, voice, and audio/video Ethernet cabling systems. The keystone patch panel can accept both couplers and keystone jacks to configure your Ethernet patch panel to accommodate a variety of schemes. The keystone network patch panel can be mounted to any standard 19-inch relay rack, cabinet or wall bracket to create a specialised rack mount patch panel to fit your individual networking requirements.

Benefits

- Mount to Any EIA 19" Rack or Cabinet in Enterprise Networks and Data Center
- Can Be Clearly Identified with Optional Labels and Icons for Port Identification
- Detachable Rear Strain Relief Bars Help Support and Manage Cables
- Allow Front Accessibility to Installed Modules for Easy Moves, Adds, and Changes
- Accepts Up to 24 Keystone Modules for Applications in 1RU
- Allows Cable to Flow to Each Side of the Rack
- Meets ISO/IEC11801 and TIA/EIA568 Standards

Technical Specification

Parameter	Value
Category	Cat5e/Cat6/Cat6a/Cat7
No. of Ports	24
Shielding Type	Shielded/Unshielded
No. of Rack Spaces	1U
Material	SPCC + ABS Plastics
Color	Black
Type of Patch Panel	Flat
Connector Type	RJ45 Ethernet/HDMI/USB
Dimensions (HxWxD)	1.75"x19"x3.62" (44.5x482.5x92mm)
Operating Temperature Range	-20 to 70°C (-14 to 158°F)

Product Dimension

