

SP650 USB Speakerphone for Home and Office

NOISE REDUCTION ALGORITHM, WITH 4 MICROPHONES, DAISY CHAIN SUPPORT



Overview

The SP650 speakerphone features with 4 smart microphone arrays that ensure comfortable remote communication, ideal for conference calls in the home and office. It can also work as a speaker for the PC to play your favorite music.

Benefits

- Directional Microphone With 5m Pickup Range
- Pair up to 5 Units Together Cascading for Meetings
- Full Duplex Audio Allows Both Sides of the Conversation are Transmitted at the Same Time
- Compatibility with Major Softwares Like Microsoft Teams, Skype, Zoom and etc
- Plug-and-play via USB, Set up Your Meeting in Seconds

Key Features

- **4 Directional Microphones, Bring Your Focused Meeting**

The 4 beam-forming directional microphone arrays provide 5m voice pickup, everyone can be heard with life-like clarity. Ideal for conference calls, music, and multimedia.

- **Full-duplex Audio, Uninterrupted Communication**

Hold completely natural conversations via speakerphone as both sides of the conversation are transmitted at the same time, allowing conversations to flow just as they do in person.

- **Five-level Cascade Technology, Ideal for Midsize & Large Rooms**

By connecting five SP650 in a daisy chain structure, it is now realistic to enjoy a decent meeting of up to 20 people. Every participant can freely utter their mind and clearly hear the other side of the conference call.


- **Universal Compatibility**

A USB speakerphone that works with all leading online conferencing services such as Microsoft Teams, Skype, Zoom and etc.

Device Connection

The SP650 speakerphone delivers enterprise-quality audio, which provides scalable conferencing solutions for business professionals. It is also suitable for other scenarios, like online class, academic speech, family calls and etc.

The multi-purpose speakerphone and camera provide professional video collaboration system for conference rooms. One SP650 is ideal for the meeting room up to 8 participants, you can daisy chain five SP650 to support 30 attendees, expanding the meeting space.



Product Parameters

Speakerphone	
Interface	USB 2.0 Type-C
Pickup Range	5M
Power Supply	5V (USB Power Supply)
Max. Power	4Ω/3W
Product Dimensions (HxWxD)	2.6"x 4.53"x4.72" (66.1x115x120mm)
Net weight	433g
Supported Operating Systems	Windows, Mac OS, Android, iOS
Accessories	USB Cable (3m); POE Cable (3m)
Color	Black
Audio	
Microphone	4 (Directional)
Speaker	1
Max. Volume	83dB
Microphone Frequency	217Hz~20KHz
Speaker Frequency	217Hz~20KHz
Signal Processing	Echo cancellation and Reverberation Suppression
Surroundings	
Operating Temperature	0 to 50°C (32 to 122°F)
Warranty	
Warranty	2 Years

Ordering Information

ID	Description
#173294	FC550S Full HD 1080P All-In-One Video Conference Camera for Small & Midsize Rooms Desktops, with 4 Microphones & 100° HFOV, USB Plug and Play
#173296	SP650 USB Speakerphone for Home & Office, Noise Suppression, with 4 Microphones, Daisy Chain Support