

Floor Mount Support Bracket Unit and Base Datasheet

Modular Structure Design, Easy-to-install, Cost-saving




46"/55" Floor Mount Split Screen Vertical Support Bracket Unit and Base



The Floor Mount Bracket for 46"/55" flat panel displays provides a versatile and secure solution for professional environments such as boardrooms, hotels, stadiums and surveillance rooms. The frame withstands the stress of 2x2, 3x3 and more split screen, offers stable and safe floor-mounted fixtures.

Key Features

1. Front view



2. Side view



Technical Specification

ID Number	174337	174338
Product Type	Floor Mount Support Bracket Unit	Floor Mount Support Bracket Unit
Mounting Type	Floor Mount	Floor Mount
Maximum Height	40.3" (1023mm)	40.3" (1023mm)
Maximum Width	22.8" (578mm)	22.8" (578mm)
Maximum Depth	6.7" (170mm)	6.7" (170mm)
Display Size	46"	46"
Usage	TV and Monitor	TV and Monitor
Weight	30.9lb (14.0kg)	41.2lb (18.7kg)
Color	Black	Black
Material	SGCC	SGCC

Technical Specification

ID Number	174340	174341
Product Type	Floor Mount Support Bracket Unit	Floor Mount Support Bracket Unit
Mounting Type	Floor Mount	Floor Mount
Maximum Height	47.8" (1214mm)	47.8" (1214mm)
Maximum Width	27.0" (685mm)	22.0" (560mm)
Maximum Depth	6.7" (170mm)	11.8" (300mm)
Display Size	55"	55"
Usage	TV and Monitor	TV and Monitor
Weight	34.2lb (15.5kg)	45.6lb (20.7kg)
Color	Black	Black
Material	SGCC	SGCC

Ordering Information

ID Number	Description
174337	46 Inch Split Screen Vertical Support Bracket Unit-3.5, Modularization Floor Mounting
174338	46 Inch Split Screen Vertical Support Bracket Base-3.5-H60, Modularization Floor Mounting
174340	55 Inch Split Screen Vertical Support Bracket Unit-3.5, Modularization Floor Mounting
174341	55 Inch Split Screen Vertical Support Bracket Base-3.5-H60, Modularization Floor Mounting