


Single Mode Fiber Keystone Jack



Overview

The fiber keystone jacks are designed to snap easily into keystone patch panels or wall plates with standard openings, which allows you to route cables through walls and provides a convenient connection to your fiber network, making it a great solution for bringing fiber to the home and office. FS provides fiber keystone jack with LC/SC/ST connectors, including Single Mode and multimode (OM3 and OM4), which have high precision and low insertion loss.

Benefits

- High-precision Mating Structure with $\leq 0.2\text{dB}$ (Typical) Low Insertion Loss
- Sturdy Snap-in Construction for Fast and Tool-less Installation
- Color-coded for Rapid Fiber Management
- Used for Keystone Wall Plates or Panels with Standard-sized Keystone Openings
- One-piece Dust Cap Keeps Adapter's Interior Clean from Dust

Product Specification

Specification	Single Mode Fiber Keystone Jack	
#ID	#143305	#143332
Connector Type	LC-LC	SC-SC
Fiber Mode	Single Mode	Single Mode
Polish Type	APC	APC
Body Style	Duplex	Simplex
Insertion Loss	≤0.2dB	≤0.2dB
Mounting Type	Reduced Flanged	Reduced Flanged
Durability	1000 times	1000 times
Flammability Rate	UL 94V-0	UL 94V-0
Operating/Storage Temperature	-25 to 70°C (-13 to 158°F)	-25 to 70°C (-13 to 158°F)