


# 4U Hinged Wall Mount Rack Bracket

PERFECT FOR SMALL OFFICE AND HOME OFFICE ENVIRONMENT



## Overview

The 4U 19" hinged wall mounting bracket for the patch panel is 6" deep to provide a dependable solution for mounting a patch panel, or other slim 19in networking equipment to a wall which features a hinged design for easy access to configuration buttons, ports, and cables. The wall mounting holes make it expand rack space to the wall, maximizing space in rooms.


## Benefits

- Hinged Design for Easy Access to the Rear of the Mounted Panel for Easy Adjustment
- Made from Solid Steel for Sturdiness and Durability
- Provide a Dependable Solution for Mounting Slim 19" Networking Equipment to a Wall
- Max. Mounting Depth 11.02" and Max. Weight Capacity 44.09lbs for Optimizing Workspace
- Static-free Powder-coated Paint Ensures Long-lasting Use


Product Specification

|                               |                                     |
|-------------------------------|-------------------------------------|
|                               | FS-HWM-4U                           |
| U Height                      | 4                                   |
| Static Weight Capacity        | 44.09lbs (20kg)                     |
| Mounting Rail Profile         | L-Shape                             |
| Mounting Hole Type            | Square                              |
| Rack Type                     | 2-Post                              |
| Frame Type                    | Open Frame                          |
| Material                      | SPCC                                |
| Color                         | Black                               |
| Product Weight                | 3.45kg (7.61lbs)                    |
| Dimensions (HxWxD)            | 7.09"x19.69"x12.01" (180x500x305mm) |
| Max. Mounting Depth           | 11.02" (280mm)                      |
| Finish                        | Black Powdercoat                    |
| Flat Pack (Assembly Required) | No                                  |
| Device Compatibility          | 19" Rack-mountable Patch Panel      |

Accessories List



M6 Screw, Nut and Cup Washer x16




M6 Expansion Screw Bolt x4


## Matching Product List

| Item No. | ID      | Description                                                                             |
|----------|---------|-----------------------------------------------------------------------------------------|
| 1        | #129517 | S2800S-48T4F, 48-Port Gigabit Ethernet L2+ Managed Switch with 4 x 1Gb SFP              |
| 2        | #29838  | 1000BASE-SX SFP Transceiver Module (MMF, 850nm, 550m, LC, DOM)                          |
| 3        | #118904 | 1U 24 Ports Cat6a Shielded Feed-Through Patch Panel                                     |
| 4        | #69081  | 96 Fibers, 48 Ports LC Duplex Single mode Fiber Adapters, 1U High 19" Fiber Patch Panel |
| 5        | #70668  | 2.1m Cat6a Snagless Shielded (SFTP) PVC CM Ethernet Network Patch Cable                 |
| 6        | #43132  | 2m LC UPC to LC UPC Duplex OM2 Multimode PVC (OFNR) 2.0mm Fiber Optic Patch Cable       |
| 7        | #29038  | 1U Horizontal Cable Manager with Finger Duct                                            |
| 8        | #168824 | 2U 19" Rack Blanking Panel                                                              |
| 9        | #72753  | 1U 19" Rack Blanking Panel (10pcs/Pack)                                                 |

Technical Drawing



Front View



Side View

Dimensions are in inches. (Dimensions in parentheses are in millimeters).