

0U Single-Phase Metered PDU

Deliver and manage reliable power to electronic equipment, servers, and network/telecom devices



Overview

Metered PDU provides local real-time monitoring capability and avoid potential overloads with a LCD hot swapping display while offering reliable, rack-mount, multi-outlet power distribution from any protected UPS, generator or mains input power source. It perfectly suited for high-density IT environments and ideal for data centers, server rooms and network wiring closets.

Benefits

- 10ft (3m) Power Cord
- 24 Total Outlets
- Aluminium Alloy Housing
- 0U Vertical Rackmount
- Dedicated to Data Center Operation

Technical Specification

CHARACTERISTICS

	PDU-2PE24I-VME
Physical	
PDU Type	Metered
Phase	Single-phase
Socket	20 IEC320 C13 & 4 C19
Plug	IEC60309 32A 2P+E
Cord length	10ft (3m)
Material	Aluminium Alloy
Indicators	Power LED
No. of Rack Spaces	0U
Dimensions (HxWxD)	70"x 2.2"x 1.75" (1778x 56x 44.5mm)
Weight	10.24kg
Mounting Method	Vertical
Power	
Rating Current	32A
Rating Voltage	230V
Frequency Compatibility	50/60Hz
Performance	
Load Capacity	7.36kW
Surge Protection	No
Screws	Included
Color	Black
Warranty	
Warranty	1 Year