

1U/4U Vertical Wall Mount Rack Bracket

PERFECT FOR SMALL OFFICE AND HOME OFFICE ENVIRONMENT



Overview

The 1U/4U 19" wall mount rack bracket offers a versatile storage solution, recommended for home offices and small businesses with rack-mount equipment that doesn't need to be secured and no room on the premises for a standard 19" wall-mount rack.

The rack bracket allows rackmount equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with the wall) to save space. Alternatively, the 1 U/4U bracket can be installed horizontally under a desk, making it easy to access installed equipment directly from your workspace.

Benefits


- Enable Equipment to Be Mounted Vertically to Provide open and Unrestricted Access
- Made from Solid Steel for Sturdiness and Durability
- Support Most 19" Rack-mountable IT/AV/Network Equipment of Any Depth
- Open Mounting Depth and Max. Weight Capacity 44.09lbs for Optimizing Workspace
- Static-free Powder-coated Paint Ensures Long-lasting Use

Product Specification

	FS-SVWM-1U	FS-SVWM-4U
U Height	1	4
Static Weight Capacity	44.09lbs (20kg)	44.09lbs (20kg)
Mounting Rail Profile	L-Shape	L-Shape
Mounting Hole Type	Square	Square
Rack Type	2-Post	2-Post
Frame Type	Open Frame	Open Frame
Material	SPCC	SPCC
Color	Black	Black
Product Weight	1kg (2.2lbs)	2.169kg (4.78lbs)
Dimensions (HxWxD)	3.98"x19.25"x2.05" (101x489x52mm)	5.98"x20.20"x8.19" (152x513x208mm)
Max. Mounting Depth	Open	Open
Finish	Black Powdercoat	Black Powdercoat
Flat Pack (Assembly Required)	No	No
Device Compatibility	Most 19" Rack-mountable equipment/Patch Panel	Most 19" Rack-mountable equipment/Patch Panel

Accessories List


FS-SVWM-1U




M6 Screw, Nut and Cup Washer x4



M6 Self-tapping Screw x4

FS-SVWM-4U

M6 Screw, Nut and Cup Washer x16




M6 Expansion Screw Bolt x4


Matching Product List

Item No.	ID	Description
1	#134657	S3900-48T6S-R, 48-Port Gigabit Ethernet L2+ Switch, 48 x Gigabit RJ45, with 6 x 10Gb SFP+ Uplinks, Stackable Switch
2	#129517	S2800S-48T4F, 48-Port Gigabit Ethernet L2+ Managed Switch with 4 x 1Gb SFP
3	#96427	FHD High Density 1U Rack Mount Enclosure
4	#189027	Fiber Optical Splice Tray 36 Fusion for FHD Rack Mount Fiber Enclosure
5	#29838	1000BASE-SX SFP Transceiver Module (MMF, 850nm, 550m, LC, DOM)
6	#118904	1U 24 Ports Cat6a Shielded Feed-Through Patch Panel
7	#69081	96 Fibers, 48 Ports LC Duplex Single mode Fiber Adapters, 1U High 19" Fiber Patch Panel
8	#70668	2.1m Cat6a Snagless Shielded (SFTP) PVC CM Ethernet Network Patch Cable
9	#43132	2m LC UPC to LC UPC Duplex OM2 Multimode PVC (OFNR) 2.0mm Fiber Optic Patch Cable
10	#29038	1U Horizontal Cable Manager with Finger Duct
11	#168824	2U 19" Rack Blanking Panel
12	#72753	1U 19" Rack Blanking Panel (10pcs/Pack)


Technical Drawing



Front View




Side View




Top View

Dimensions are in inches. (Dimensions in parentheses are in millimeters).


Technical Drawing



Front View



Side View



Top View

Dimensions are in inches. (Dimensions in parentheses are in millimeters).