

2/4U Adjustable DIN Rail Bracket



Description

The rack-mount DIN kit includes screws and nuts, making it compliant with an array of DIN rail equipment, such as power supplies, programmable time switches and circuit breakers. The adjustable rails can be easily set back to match DIN rail equipment of any depth.

Features




- Unique Depth Adjustment Feature to Fit Equipment in Any Size
- Durable Cold-rolled Steel Construction Designed to Stand up to Heavy Use Over Time
- Smoother and More Stable When Sliding Left and Right
- Rack-mounting Hardware Included for Easy Installation
- Allows Mounting of Any DIN Rail Equipment in EIA 19" Rack or Cabinet
- Suitable for Industrial Media Converter, Industrial Ethernet Switch, Industrial Power Supply etc.

Product Specifications

Specification	DINRAIL2U	DINRAIL4U
Product Type	DIN Rail Bracket	DIN Rail Bracket
Material	SPCC	SPCC
Color	Black	Black
Rack Height	2U	4U
Dimensions (HxWxD)	3.44"x19.06"x14.17" (87.5x484x360mm)	6.50"x19.04"x14.17" (165.1x483.7x360mm)
Weight	1.5kg	3.3kg
Standard	EIA 19"	EIA 19"
Warranty	1 Year	1 Year




Layout and Dimensions

DINRAIL2U



Dimensions are in millimeters.

DINRAIL4U



Dimensions are in millimeters.

Warranty Information

For FS product warranties, visit <https://www.fs.com/policies/warranty.html>