

FS-1USSH Cabinet Shelf Datasheet

Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment.



1U Adjustable Sliding Shelf

This sliding shelf is compatible with 19" EIA standard 4-post open racks or cabinets which can be adjusted from 25.59" to 37.40" (mounting depth) to fit your racks, supporting equipment without rack-mounted brackets such as servers, UPS units, monitors and IT related equipment, etc.

Standards Compliance

- ISO9001 Certificate

Features

- 4-post rack compatible
- 25.59"-37.40" adjustable depth
- SPCC Material
- Supports up to 132.28lbs (60kg)
- Install into 1U of rack space
- Accommodates wide variety of electronic equipment
- Required mounting hardware included

Product Specification


Product Type	Sliding Shelf
No. of Rack Spaces	1U
Rack Type	4 Post
Material	SPCC
Weight Capacity - Stationary	132.28lbs (60.00kg)
Mounting Depth Range	25.59"-37.40" (650-950mm)
Dimensions (HxWxD)	1.69"x19.00"x25.59" (43x483x650mm)
Accessories	M6*12mm screw x8 and M6 nut x8
Application	Matching for EIA 19" racks or cabinets

Product Application

Adjustable sliding shelf supports equipment without rack-mounted brackets such as servers, UPS units, monitors and IT related equipment, etc.



Technical Drawing



Top View

Front View

Dimensions are in inches. (Dimensions in parentheses are in millimeters).

Matching Products List

Item No.	ID	Description
1	#177894	42U GR800-Series Black Network & Server Cabinet 800 x 1100mm
2	#134657	S3900-48T6S-R, 48-Port Gigabit Ethernet L2+ Switch, 48 x Gigabit RJ45, with 6 x 10Gb SFP + Uplinks, Stackable Switch
3	#14101	M6 Model Screw and Nut, 50/Pack