

FS-WMNR-D2P6U Open Frame Wall Mount Rack



Description

This open-frame wall-mount rack provides 6U of storage, enabling 19" wide servers, A/V, or network rack-mount equipment to be installed perpendicular to the wall, allowing you to save space and stay organized. Its design enables maximum airflow with an unobstructed back-end of equipment that reduces hot spots, which helps keep operating.

The open frame rack can be used in closets, back offices, or anywhere where space is limited.


Features

- Open Frame Design for Flexible Management and More Efficient Operation
- Made from Solid Steel for Sturdiness and Durability
- Ideal for Installing 19" Equipment, Patch Panel, Switch, and Shelf in Small Space
- Max. Mounting Depth 15.75" & Max. Weight Capacity 264.55lbs for Optimizing Workspace
- Static-free Powder-coated Paint Ensures Long-lasting Use
- Suitable for Rack Mount Server, Networking, and Telecom Applications

Product Specifications

Specifications	
Number of Rack Spaces	6U
Stationary Weight Capacity	264.55lbs (120kg)
Mounting Rail Profile	G-Shape
Mounting Hole Type	Square
Rack Type	2-Post
Frame Type	Open Frame
Material	SPCC
Color	Black
Product Weight	24.14lbs (10.95kg)
Dimensions (HxWxD)	16.10"x21.77"x17.95" (409x553x456mm)
Maximum Device Depth	15.75" (400mm)
Finish	Black Powdercoat
Flat Pack (Assembly Required)	No
Device Compatibility	19" IT/AV/Equipment/Patch Panel/Shelf

Accessory List




M6 Screw, Nut and Cup Washer x24




M6 Expansion Screw Bolt x4


Layout and Dimensions



Front View



Side View



Top View

Dimensions are in millimeters. (Dimensions in parentheses are in inches).

Compatible Accessory List

1. Horizontal Cable Managers

ID	Description
SKU: 72911	Horizontal Single Sided Cable Manager, 0RU, 5 Snap-in D-Rings, 4.29 in. Depth
SKU: 120680	Horizontal Single Sided Manager, 1RU, 5 Snap-in D-Rings, 3.37 in. Depth
SKU: 29038	Horizontal Single Sided Cable Manager, 1RU, Finger Duct, 3.43 in. Depth
SKU: 68690	Horizontal Cable Manager, 1RU, 4 D-Rings & Brush Strip, 3.46 in. Depth
SKU: 64184	Horizontal Single Sided Cable Manager, 1RU, D-Rings & Side Rings, 3.46 in. Depth
SKU: 173305	Horizontal Single Sided Cable Manager, 1RU, 5 D-Rings, 3.46 in. Depth
SKU: 220085	Horizontal Single Sided Steel Manager, 1RU, Finger Duct, 4.44 in. Depth
SKU: 29040	Horizontal Dual Sided Cable Manager, 1RU, Finger Duct, 6.85 in. Depth
SKU: 315741	Horizontal Dual Sided High Capacity Cable Manager, 1RU, Finger Duct, 9.07 in. Depth
SKU: 29039	Horizontal Single Sided Manager, 2RU, Finger Duct with Cover, 3.43 in. Depth
SKU: 315743	Horizontal Single Sided High Capacity Cable Manager, 2RU, Finger Duct with Cover, 4.56 in. Depth
SKU: 220087	Horizontal Dual Sided Steel Manager, 2RU, Finger Duct, 9.1 in. Depth

2. Vertical Cable Managers

ID	Description
SKU: 64186	Vertical Single Sided Cable Manager, 5RU, Bend Radius Finger
SKU: 192607	Vertical Single Sided Cable Manager, 5RU, Bend Radius Finger, 10-Pack

3. Horizontal PDUs

ID	Description
SKU: 119617	1.88kW Single-Phase 15A/125V Basic PDU, 8 x NEMA 5-15R Outlets, NEMA 5-15P Plug, 6.6ft Cord, 1U Rack-Mount
SKU: 157099	1.20kW Single-Phase 10A/120V Basic PDU, 8 x C13 Outlets, IEC320 C14 Plug, 10ft Cord, 1U Rack-Mount
SKU: 157097	1.92kW Single-Phase 16A/120V Basic PDU, 10 x NEMA 5-20R Outlets, NEMA 5-20P Plug, 10ft Cord, 1U Rack-Mount
SKU: 157094	1.92kW Single-Phase 16A/120V Basic PDU, 6 x C13 & 2 x C19 Outlets, IEC320 C20 Plug, 10ft Cord, 1U Rack-Mount
SKU: 157088	1.20kW Single-Phase 10A/120V Monitored PDU, 8 x C13 Outlets, IEC320 C14 Plug, 6.6ft Cord, 1U Rack-Mount
SKU: 157089	1.80kW Single-Phase 15A/120V Monitored PDU, 8 x NEMA 5-15R Outlets, NEMA 5-15P Plug, 10ft Cord, 1U Rack-Mount
SKU: 157090	2.40kW Single-Phase 20A/120V Monitored PDU, 8 x NEMA 5-20R Outlets, NEMA L5-20P Plug, 10ft Cord, 1U Rack-Mount
SKU: 157095	1.92kW Single-Phase 16A/120V Basic PDU, 10 x NEMA 5-20R Outlets, NEMA L5-20P Plug, 10ft Cord, 1U Rack-Mount
SKU: 157098	3.33kW Single-Phase 16A/208V Basic PDU, 10 x C13 Outlets, NEMA L6-20P Plug, 10ft Cord, 1U Rack-Mount
SKU: 157092	6.24kW Single-Phase 30A/208V Monitored PDU, 12 x C13 & 4 x C19 Outlets, NEMA L6-30P Plug, 10ft Cord, 2U Rack-Mount

4. Blanking Panels

ID	Description
SKU: 133347	1U 19" Tool-less Rack Blanking Panel, Magnetic Design (10pcs/Pack)
SKU: 72753	1U 19" Rack Blanking Panel (10pcs/Pack)
SKU: 181854	1U 19" Tool-less Rack Blanking Panel (10pcs/Pack)
SKU: 317019	1U 19" Rack Blanking Panel (10pcs/Pack)
SKU: 168824	2U 19" Rack Blanking Panel
SKU: 181855	2U 19" Tool-less Rack Blanking Panel
SKU: 284589	2U 19" Tool-less Rack Blanking Panel, ABS

4. Blanking Panels

ID	Description
SKU: 168825	4U 19" Rack Blanking Panel
SKU: 181856	4U 19" Tool-less Rack Blanking Panel
SKU: 284593	4U 19" Tool-less Rack Blanking Panel, ABS
SKU: 284595	4U 19" Tool-less Rack Blanking Panel, ABS (5pcs/Pack)

5. DIN Rail Bracket

ID	Description
SKU: 178163	Adjustable DIN Rail Bracket for EIA 19" Mount, 2RU, Black

6. Fans

ID	Description
SKU: 173815	Horizontal Cabinet 1U Fan Tray, 2 Fans, with Power Switch and Digital Temperature Unit, 110V-120V
SKU: 173817	Horizontal Cabinet 3U Fan Panel, 3 Fans, with Power Switch, 110V-120V
SKU: 220051	Horizontal Rackmount 1U Fan Tray, 2 Fans, with Power Switch and Digital Temperature Unit, 220V-240V
SKU: 220053	Horizontal Rackmount 1U Fan Tray, 4 Fans, with Power Switch and Digital Temperature Unit, 220V-240V
SKU: 217919	Horizontal Rackmount 3U Fan Panel, 3 Fans, with Power Switch, 220V-240V (Australian Standard)

Warranty Information

For FS product warranties, visit <https://www.fs.com/policies/warranty.html>