


LC/UPC to LC/UPC Duplex Fiber Keystone Jack



Overview

These fiber keystone jacks are used for connecting two LC fiber optic cables to extend the length of the cable run. The duplex adapter accepts two simplex connectors or one duplex connector. The fiber keystone jacks are designed to snap easily into keystone patch panels or wall plates with standard openings, which allows you to route cables through walls and provides a convenient connection to your fiber network, making it a great solution for bringing fiber to the home and office. FS provides fiber keystone jack with LC/SC/ST connectors, including Single Mode and multimode (OM3 and OM4), which have high precision and low insertion loss.

Benefits

- High-precision Mating Structure with $\leq 0.2\text{dB}$ (Typical) Low Insertion Loss
- Sturdy Snap-in Construction for Fast and Tool-less Installation
- Color-coded for Rapid Fiber Management
- Used for Keystone Wall Plates or Panels with Standard-sized Keystone Openings
- One-piece Dust Cap Keeps Adapter's Interior Clean from Dust

Product Specification

	Specification					
ID	#143313	#206437	#143316	#206441	#143325	#206439
Connector Type	LC-LC	LC-LC	LC-LC	LC-LC	LC-LC	LC-LC
Fiber Mode	Single Mode	Single Mode	OM3	OM3	OM4	OM4
Polish Type	UPC	UPC	UPC	UPC	UPC	UPC
Color	Blue	Blue	Aqua	Aqua	Violet	Violet
Body Style	Duplex	Duplex	Duplex	Duplex	Duplex	Duplex
Insertion Loss	≤0.2dB	≤0.2dB	≤0.2dB	≤0.2dB	≤0.2dB	≤0.2dB
Mounting Type	Reduced Flanged		Reduced Flanged		Reduced Flanged	
Durability	1000 times	1000 times	1000 times	1000 times	1000 times	1000 times
Flammability Rate	UL 94V-0	UL 94V-0	UL 94V-0	UL 94V-0	UL 94V-0	UL 94V-0
Operating Temperature	-25 to 70°C (-13 to 158°F)		-25 to 70°C (-13 to 158°F)		-25 to 70°C (-13 to 158°F)	
Storage Temperature	-25 to 70°C (-13 to 158°F)		-25 to 70°C (-13 to 158°F)		-25 to 70°C (-13 to 158°F)	
Package Quantity	1pc	10pcs	1pc	10pcs	1pc	10pcs