

LJ6C-Style Wallplate Insert Datasheet



Overview

The inserts are designed to fit into 25 mm x 38 mm LJ6C-style openings. Inserts mount to back box with faceplate frame, compatible with any type of keystone jack modules and include ID window kits for port designation. The insert features a spring-loaded shutter to protect the connectors from dust and debris when not in use. Inserts are available in white ABS plastic.

Benefits

- Mount to Back Box with Faceplate Frame, Compatible with Any Type of Keystone Jack Modules
- Includes ID window for port designation
- Inserts with spring-loaded shutters protect copper jacks while not in use
- Sloped port provides additional bend radius control to protect cable
- High-strength ABS Construction Designed to Last Long in Your Decor

Technical Specification

Parameter	Value
Product Type	LJ6C-Style Wallplate Insert
Shuttered	With Shutter
Material	ABS
Operation Temperature	-25 to 70°C (-13 to 158°F)
Color	White
Installation Method	Snap-on

Product Dimension

