

M5 & M6 SCREW AND NUT



M5 & M6 Model Screw And Nut

FS supplies M5 and M6 models of screw and nut. The "M" designation for metric screws indicates the nominal outer diameter. For example, an M6 screw has a nominal outer diameter of 6 millimeters.

These M5 & M6 screws and nuts for server racks and cabinets are convenient to have on hand for installing a server, network, AV, and other rackmount equipment securely into your storage cabinet or server rack.

Features

- Package of 50 M5/M6 Screws and 50 M6 Nuts
- Nickel/Zinc-plated Finish to Prevent Rust
- High Hardness Screws and Nuts
- Square Cage Nut Designed for Racks and Cabinets with Square Holes
- Washer Protects the Screw and the Contact Surface of the Equipment

Product Specification				
Part Number	FS-SN-M5	FS-SN-M6	FS-SN-M6-20	FS-SN-M6-20B
Thread Type	M5	M6	M6	M6
Material	Carbon Steel	Carbon Steel	Carbon Steel	Carbon Steel
Surface Polish	Nickel-plated	Nickel-Plated	Nickel-plated	Zinc-plated
Color	Silver	Silver	Silver	Black
Size	M5×16mm	M6×16mm	M6×20mm	M6×20mm
Yield Strength	/	> 6000N	>6000 N	>6000 N
Application	Patch Panels, Cable Managers, Standard-thickness Switches, Cabinet Mounting Brackets		Patch Panels, Cable Managers, High-thickness Switches, Cabinet Mounting Brackets	