


MMC Fiber Adapter Panel



Overview

The 1U fiber adapter panel is pre-loaded with 66 US Conec's 4-port MMC adapters. Each adapter can accommodate 4 pairs of MMC-12/16/24 male to female connectors. Compared to MTP®/MPO adapter, the MMC adapter offers three times the cabling port density. The 1U 19" adapter panel is compatible with any standard EIA 19" racks or cabinets. The rear cable manager, used with cable ties, can help manage large cables. This high performance fiber optic panel is suitable for applications in data center and telecommunication networks.

Benefits

- Space Saving 1U Design, Mount to Standard EIA 19" Rack Rails
- US Conec MMC Adapter Ensures Quality and Reliability
- 66 MMC Adapters in 1U, Up to 6336 Fibers (MMC-24)
- 3x Cabling Port Density over the MTP®/MPO format
- Protective Dust Cap Keeps Adapter's Interior Clean from Dust
- Built-in Rear Cable Manager for Easy Maintenance


Product Specifications

Specifications	#336349
Part Number	FS-FAP66MMCS
Number of Ports	66
Fiber Count	3168F (MMC-12); 4224F (MMC-16); 6336F (MMC-24)
Fiber Mode	OS2
Adapter Type	US Conec MMC
Adapter Color	Green
Material of Plate	Steel, Powder-coated Black
Operating Temperature	-10 to 60 °C
Dimensions(HxWxD)	1.73"x19"x8.62"(44x483x219mm)

Matching Products

ID	Description
#253289	1m (3ft) MMC Jumper, MMC-16 APC (Female) to MMC-16 APC (Female)
#253291	2m (7ft) MMC Jumper, MMC-16 APC (Female) to MMC-16 APC (Female)
#253293	3m (7ft) MMC Jumper, MMC-16 APC (Female) to MMC-16 APC (Female)

Technical Drawing



Technical Drawing

