

Pro's Kit[®] PT-1216 12V Cordless Brushless Drill Driver



Description

The PT-1216 features a next-generation brushless motor paired with a powerful 2000mAh Li-ion battery and 35N.m torque output—ready to tackle materials like metal, wood, and plastic with ease. Its dual-speed transmission (0–500 / 0–1600 rpm) allows seamless switching between drilling and screwdriving. Combined with an ergonomic grip and a built-in LED working light, it delivers exceptional control and comfort in both job site and indoor settings. The newly designed blow-molded carrying case ensures organized storage and professional mobility.

Features

- Brushless Motor Delivers High Efficiency and Long Service Life.
- Dual Rotation Speed (0-500/0-1600rpm) for Both Drilling and Screwdriving.
- Maximum Output Torque of 35N.m for Demanding Tasks.
- Fast Charging 2000mAh Lithium-ion Battery Enhanced Work Efficiency.
- Built-in LED Light for Clear Visibility in Dimly Lit Working Environments.
- 19+1 Torque Adjustment for Precise Control.
- Ergonomic Dual Color Grip with Compact Body to be Carried Easily.
- Blow-modeled Case Provides Secure Storage and Portability.

Product Specifications

Product Models	PT-1216G	PT-1216F	PT-1216A
Product Brand	Pro's Kit®	Pro's Kit®	Pro's Kit®
Rated Voltage	DC 12V	DC 12V	DC 12V
Input Voltage	AC 230V 50Hz	AC 230V 50Hz	AC 120V 60Hz
Battery Type	Lithium-ion	Lithium-ion	Lithium-ion
Battery Model	5PT-1206-BAT	5PT-1206-BAT	5PT-1206-BAT
Battery Capacity	2000mAh	2000mAh	2000mAh
Charging Time	1-1.5 Hours	1-1.5 Hours	1-1.5 Hours
Max. Torque	35N.m	35N.m	35N.m
Chuck Type	3/8" Keyless Chuck	3/8" Keyless Chuck	3/8" Keyless Chuck
Rotation Speed	0-500/0-1600 rpm	0-500/0-1600 rpm	0-500/0-1600 rpm
Size Range of Drilling Bit	φ0.03"-0.40" (0.8-10mm)	φ0.03"-0.40" (0.8-10mm)	φ0.03"-0.40" (0.8-10mm)
Max. Drilling Capacity	Metal: 0.71" (18mm)	Metal: 0.71" (18mm)	Metal: 0.71" (18mm)
Dimensions (HxWxD)	7.52"x2.24"x6.26" (190x57x160mm)	7.52"x2.24"x6.26" (190x57x160mm)	7.52"x2.24"x6.26" (190x57x160mm)