


Self-locking Cable Ties Datasheet



Overview

Organize your cables efficiently with our standard locking cable tie. This cable tie has a curved tip for easy threading and a nylon material that resists weather. With a tensile strength of 17.6 lbs (8 kg), these ties are strong for high quality performance.

Due to the large amount of tie products and relatively simple design, making the tie becomes a data center cabling in the wiring harness of the very economical equipment system, and suitable for different occasions of multi-purpose projects. Ideal accessories for wiring management.

Benefits

- 17.6 lbs (8 kg) Tensile Strength, Reliable Nylon Material for High Quality Performance
- Precise Head Hole for Easy and Fast Attachment
- Inside Serration for a Strong Grip on Bundles
- Inside Serration for a Strong Grip on Bundles, Fastener for Securing Loose Cords to Eliminate Tripping Hazard
- Easy Application, Either Manually or with a Tensioning Tool
- Multi-purpose for Office, Data Center and Other Indoor/Outdoor Wiring Scenarios

Technical Specification

Parameter	Value
Color	Blue, Green, Yellow, White
Material	Nylon
Environment	Indoor/Outdoor
Thickness	1.2mm
Maximum Bundle Diameter	20mm
Minimum Loop Tensile	17.6lbs (8kg)
Strength Function	Cable Management & Daily Necessities Organization
Package	100-Pack
Dimensions (LxW)	4"x0.1" (100x3mm)
Working Temperature	32 to 185°F (0 to 85°C)

Product Specification

Unit:MM

