

MC-15SP, 15 Slots Media Converter Chassis

COST-EFFECTIVE DATA LINK AND POWER SOURCING SOLUTION



Overview

The MC-15SP 15-slot Rackmount chassis is specially designed to accommodate UMC-1F1T, UMC-1SC1T-SM, UMC-1SC1T-MM, UMC-1S1T and UMC-1F1T-PD Media Converter for central power supply, saving space and power cables. You can start with single media converters, and when your requirements grow bigger, you can mount a chassis to install your media converters in the chassis.

The chassis lets you install multiple media converters in an equipment rack together with the network devices for which they provide media conversion. This provides for space saving, and the cabling will look neat. The power type of this device is AC by default.

Benefits

- Houses and Powers up to 15 Hot-swappable Media Converters
- Mounted Two Cooling Fans for Better Ventilation
- High Quality 19" Rack-mountable Chassis Installation
- LED Indicators Keep You Informed at A Glance for Input Power
- Maintains and Manages the Status of Media Converters at one time

Specification

	MC-15SP
Slot	15 open slots Slot Dimensions: 2.80"x1.06"x3.74 (71x27x95mm)
Matching Products	UMC-1F1T, UMC-1SC1T-SM, UMC-1SC1T-MM, UMC-1S1T, UMC-1F1T-PD
Power Requirements	100~240V AC, 3.3A, 50-60Hz
Power Output	Each slot 5V DC 1A
Power Consumption	10 watts / 34.1BTU (System only) 80 watts / 272BTU (Full loading)
LED	Power 1, Fan1, Fan2
Fan Numbers	2
Weight	4.3kg
Dimensions (HxWxD)	4.06"x17.24"x7.87"(103x438x200mm), 2.4U high
Operating Temperature	0 to 50°C (32 to 122°F)
Storage Temperature	-20 to 70°C (-4 to 158°F)
Operating Humidity	5 to 90%, non-condensing
Storage Humidity	5 to 90%, non-condensing

Specification

Models	Description
UMC-1F1T	Unmanaged 1 x 10/100/1000Base-T to 1 x 100/1000Base-X SFP Slot Gigabit Ethernet Media Converter,
UMC-1S1T	Unmanaged 1 x 100M/1G/2.5G/5G/10GBase-T to 1 x 10GBase-X SFP+ Slot 10Gigabit Ethernet Media Converter
UMC-1SC1T-SM	Unmanaged 1 x 10/100/1000Base-T to 1 x 1000Base-X Single Mode SC 1310nm 10km Gigabit Ethernet Media Converter
UMC-1SC1T-MM	Unmanaged 1 x 10/100/1000Base-T to 1 x 1000Base-X Multimode SC 850nm 220/550m Gigabit Ethernet Media Converter
UMC-1F1T-PD	1 x 10/100/1000BASE-T RJ45 to 1 x 100/1000BASE-X SFP Slot Gigabit Ethernet PoE+ PD Media Converter