Cable Labels Datatsheet

Offers a broad selection of industry approved styles and sizes to meet a full range of networking applications.

Cable Labels Description

FS provides high performance wire cable labels to save time and workload when managing the network. Adhesive label papers are waterproof, tear resistant, scratch resistant and the words on label can be both handwritten and printed. Even in the low temperature environment, they have a relatively strong stickiness. Numeric cable markers are made for fixing cable, and the cable markers can mark the color-coded cables to make it easier to identify the cable.

Features

- Keeps cables neat and tidy.
- A full range of styles to select.
- Easy to install and identify quickly.
- It can be printed with printer according to your special needs.
- Simpler troubleshooting and maintenance procedures.

Standards Compliance

- RoHS Compliant
- ISO9001 Certificate

Numeric Cable Markers

They are made for fixing various cables, which are good tools for managers to identify the messy cable quickly for an easy and cost-efficient cable management solution.

Product Specifications		
Part Number	CMLN-C5	CMLN-C6
Style	Cable Wire Marker	Cable Wire Marker
Material	POM	POM
Colors	Black, Brown, Red, Orange,Yellow, Blue, Green, White, Purple, Grey	Black, Brown, Red, Orange,Yellow, Blue, Green, White, Purple, Grey
Cable Diameter Range	0.12"-0.22" (3-5.5mm) 26-28AWG	0.24"-0.28" (6-7mm) 23-26AWG
Package	10pcs/pack	10pcs/pack
Dimensions (HxWxD/LxW)	0.12"x3.9"x0.49" (2.93x100.8x12.4mm)	0.18"x2.9"x0.4" (4.5x73x9mm)
Application	Coax, Copper and Fiber Optic Cables	Coax, Copper and Fiber Optic Cables

Adhesive Cable Labels

W Winding Type Cable Label: Printable liner for records and placement instructions; easy wrap-around design and pre-cut self-laminating vinyl labels give them excellent protection against abrasion, dust and dirt.

W P Type Cable Adhesive Label Paper: Colorful labels creat a neat and comfortable data center, they are easy to install and help managers to identify the kind of labels at a glance.

Product Specifications			
Pic.			
Part Number	CMLP-17WTWT	CMLP-27PTWT CMLP-27PTRE	CMLP-A4PTWT
Style	W Winding Type	W P Type	W P Type
Material	PET	PET	PET
Colors	White	White, Red	Red, Yellow, Blue, Green, White, Orange
Type of Printer	Ribbon Printer	Ribbon Printer	Ribbon Printer
Operating Temperature	-20°C to 60°C	0°C to 60°C	-20°C to 60°C
Package	500pcs/pack	1 Roll (1000pcs/roll)	10 sheets (30pcs/sheet)
Dimensions (HxWxD/LxW)	1.75"x0.75" (44.5x19mm)	2.76"x0.94" (70x24mm)	3.31"x1.02" (84x26mm)
Application	Fiber Patch Cable, Copper Cable and etc.	Fiber Patch Cable, Copper Cable and etc.	Fiber Patch Cable, Copper Cable and etc.

Technical Drawing



CMLP-A4PTWT



CMLP-27PTWT
CMLP-27PTRE



CMLP-17WTWT

Dimensions are in inches. (Dimensions in parentheses are in millimeters).

Product List

I. Cable Labels List

Item No.	ID	Description
1	#23297	10pcs/pack Color Label Numeric Cable Wire Marker Identification for Ø3-5.5mm, 26-28AWG Cat5e/Cat6/Cat6a
2	#23298	10pcs/pack Cat6 Color Label Numeric Cable Wire Marker Identification for Ø6-7mm, 23-26AWG Cat5e/Cat6/Cat6a
3	#57003	1.75in.L x0.75in.W Winding Type Cable Label-500pcs/pack
4	#63058	2.76in.L x 0.94in.W P Type Cable Adhesive Label Paper-1000pcs/roll, White
5	#63059	2.76in.L x 0.94in.W P Type Cable Adhesive Label Paper-1000pcs/roll, Red
6	#65341	A4 Size 3.31in.Lx1.02in.W P Type Adhesive Label Paper-300pcs/10 Sheets, White

II. Matching Product List

Item No.	ID	Description
1	#70595	3ft (0.9m) Cat6 Snagless Unshielded (UTP) PVC CM Ethernet Network Patch Cable, Blue
2	#70705	1ft (0.3m) Cat5e Snagless Unshielded (UTP) PVC CM Ethernet Patch Cable, Blue
3	#70664	2ft (0.6m) Cat6a Snagless Shielded (SFTP) PVC CMX Ethernet Network Patch Cable, Blue
4	#63440	1ft (0.3m) Cat6 Snagless Unshielded (UTP) PVC CM Slim Ethernet Network Patch Cable, Blue
5	#40191	1m (3ft) LC UPC to LC UPC Duplex OS2 PVC (OFNR) 2.0mm Fiber Optic Patch Cable
6	#40180	1m (3ft) LC UPC to LC UPC Duplex OM4 Multimode PVC (OFNR) 2.0mm Fiber Optic Patch Cable
7	#68017	1m (3ft) MTP® Female Type B Plenum (OFNP) OM4 (OM3) 50/125 Elite Trunk Cable