

MC-16DP Managed Ethernet Media Converter Datasheet

EXCELLENT SOLUTION TO EXTENDING COMMUNICATION DISTANCE IN A NETWORK



Overview

The MC-16DP 16-slot Rackmount chassis is specially designed to accommodate MMC-1SC1T-MM-SIM、MMC-1SC1T-SM-20-SIM、MMC-1F1T-SIM、MMC-1S1XMG-SIM Media Converter for central power supply, saving space and power cables.

When your requirements grow, you can mount a chassis to install your media converters. The chassis allows multiple converters to be organized in an equipment rack, saving space and keeping cabling neat alongside network devices.

It is configurable via console, Web, and SNMP, supporting NTP clock synchronization and both remote and local system logging. Additionally, the removable power module enhances flexibility, making this device ideal for scalable, streamlined network management. The power type of this device is AC by default.

Benefits


- Fits A Standard 19" Rack - 2U Height
- Support to 16-slot Hot-swappable Media Converter
- Support WEB/SNMP/CONSOLE Management
- Supports NTP Clock, Remote and Local System Log
- LED Indicators for System, Power, and Fan Conditions

Specification

	MC-16DP
Product Type	Managed Media Converter Chassis
Number of Slots	16
Input Power	100-240V AC, 1A, 50-60Hz
Output Power	DC 5V Per slot, 2A Maximum
System Management	Console/ Web/ SNMPv1/v2c
Power Consumption	10W
Dimensions (HxWxD)	17.32" x13.78" x3.46" (440x350x88mm)
Weight	7kg
Operating Temperature	0° C to 50° C
Storage Temperature	-20° C to 70° C
Rack Space	2U
LED Indicator	MGM, Console, LNK/ACT, PWR ON x 2, PWR FAIL x 2, FAN FAIL x 2
Standards and Protocols	IEEE 802.3 10BASE-T Ethernet IEEE 802.3u 100BASE-TX Fast Ethernet IEEE 802.3ab 1000BASE-T Gigabit Ethernet IEEE 802.3x Flow Control
Warranty	2 Years

Specification

Models	Description
MMC-1F1T-SIM	Managed 1x 10/ 100/ 1000Base-T RJ45 to 1x 100/ 1000Base-X SFP Slot Gigabit Ethernet Media Converter, Slide- in Module
MMC-1S1XMG-SIM	Managed 1x 100M/ 1G/ 2.5G/5G/ 10GBase-T RJ45 to 1x 10GBase-X SFP+ Slot 10Gigabit Ethernet Media Converter, Slide- in Module
MMC-1SC1T-MM-SIM	Managed 1x 10/ 100/ 1000Base-T RJ45 to 1x 100/ 1000Base-X Multimode SC Duplex 850nm 550m Gigabit Ethernet Media Converter, Slide- in Module
MMC-1SC1T-SM-20-SIM	Managed 1x 10/ 100/ 1000Base-T RJ45 to 1x 100/ 1000 Base-X Single Mode Duplex SC 1310nm 20km Gigabit Ethernet Media Conerter, Slide- in Module



 <https://www.fs.com>



The information in this document is subject to change without notice. FS has made all efforts to ensure the accuracy of the information, but all information in this document does not constitute any kind of warranty.