

Cat6 Ethernet Bulk Cable


24AWG • 4 Twisted Pairs • CM • U/UTP • 550MHz • Stranded Copper

Available Colors:  



Overview

The next step up from standard Cat5e cable, Cat6 is a "4 twisted pairs" network cable used for 1000Base-T Ethernet applications up to 550MHz, can also provide at speed of 10G rate with 30-40m transmission distance. This cable is perfect to all your advanced networking installations.



Key Features

- Stranded Bare Copper Better than CCA
CM In-Wall Rated
- Tangle and Twist-free Packaging
- Marked Every 1m (3.28ft) on Cable Makes Measuring Easy
- Support PoE, PoE+ (IEEE 802.3af/at)
- CE, Reach, RoHS Certified and UL Listed
- CM Rated (in-Wall) for in-Wall Use for Commercial Class Buildings
- Tested with a Fluke DSX-8000 Versiv CableAnalyzer

Application

- Use for Commercial Class Buildings
- Rated for any 10/100/1000Base-T Ethernet
- Connect with Switches, Routers, Computers, IP Cameras, Xbox, Apple TV and Much More

Specifications

Physical Characteristics

Operating Temp. Range	-20 to +75°C (-4 to 167°F)
Max. Operating Voltage (v)	300
Reference Standard	ISO/IEC 11801, ANSI/TIA-568.2-D

Conductor

Conductor Type	Stranded Bare Copper
Wire Gauge (AWG)	24
Conductor Nom.O.D. (mm)	0.600 ± 0.005
Conductor Qty.	4 Twisted Pairs

Insulation

Insulation Material	HDPE
Insulation Diameter (mm)	0.98 ± 0.05
Core Color	A. Blue, White – Blue B. Orange, White – Orange C. Green, White - Green D. Brown, White - Brown

Jacket

Material	PVC (Complies RoHS), CM
External O.D. (mm)	6.1 ± 0.4
Thickness (mm)	0.55 ± 0.05
Color	Blue/Gray
Surface	Clean, Frap, Satiation
Rip Cord	Yes

Specifications

Electrical Characteristics

1.0-250.0MHz Impedance(ohms)	100 ± 15
1.0-250.0MHz Delay Skew (ns/100m)	≤45
Capacitance Unbalance (pF/100m)	≤160
Max. Conductor DC Resistance @20°C (ohms/100m)	9.38
Resistance Unbalance (%)	≤5.0

Mechanical Characteristics

Before Aging Tensile Strength (Mpa)	≥13.5
Before Aging Elongation (%)	≥150
Aging Period (°C×hrs)	100°C×24h×7d
After Aging Tensile Strength (Mpa)	≥12.5
After Aging Elongation (%)	≥125
Cold Bend (-20±2°C×4h)	8 × Cable O.D., No Visible Cracks

Packing

Packing Type	1000ft (305m) Pull Box
Carton Dimension (HxWxD)	350×330×265 MM