


Cat5e Coupler Patch Panel, 24-Port, 1RU, Cable Management Bar Included

MANAGING AND ORGANISING COPPER ETHERNET NETWORK



Overview

24-port Cat5e patch panel for high density and easy patching solutions in data centers. The Cat5e Ethernet patch panel is designed for use in 19" racks and ideal for 10/100/1000Base-T Ethernet applications. It bundles the networks together to connect incoming and outgoing lines and improve the organisation of a wired network. The clear numbering on the front and back of the network patch panel enables quick and easy identification of cable runs, and the detachable cable management bar keeps Ethernet cables neat and tidy.

Benefits

- Mount to Any EIA 19" Rack or Cabinet in Enterprise Networks and Data Center
- UTP Couplers Snap In and Out of the Patch Panel for Easy Moves, Adds and Changes
- Can Be Clearly Identified with Optional Labels and Icons for Port Identification
- ISO/IEC11801 and TIA/EIA568 Standards at Swept Frequencies 1 to 250 MHz
- Backwards Compatible with 6/8p RJ45 UTP Patch Cords with T568A/B Wiring Schemes
- Support POE/POE+/POE++ (IEEE 802.3af/at)
- Detachable Rear Strain Relief Bars Help Support and Manage Cables

Technical Specification

Parameter	Value
Category	Cat5e
No. of Ports	24
Shielding Type	Unshielded
No. of Rack Spaces	1U
Material	SPCC + ABS Plastics
Color	Black
Type of Patch Panel	Flat
Connector Type	RJ45 Ethernet
Dimensions (HxWxD)	1.75"x19"x3.62" (44.5x482.5x92mm)
Operating Temperature Range	-25 to 70°C (-13 to 158°F)

Product Dimension

