


Horizontal Cable Managers with Finger Duct

Horizontal cable managers are typically used in applications that require a large number of Moves, Adds and Changes (MAC).



Horizontal Cable Managers with Finger Duct

Horizontal cable managers ensure optimal cable radius to prevent deterioration or breakage. Flexible fingers maximize the care and protection of the equipment and cables, keeping the structured cabling system unhurt and totally functional. Removable cover makes it easy to add or remove bundled cables quickly.

High capacity horizontal cable managers provide an efficient way to manage high performance copper, fiber and etc. on any 19" rack.

Standards Compliance

- RoHS Compliant
- ISO9001 Certificate

Features

- **Integral bend radius control** — Maintains bend radius as cables transition to and from horizontal and vertical pathways.
- **Convenient hinged cover** — Allows access to the cable pathway without having to completely remove the cover.
- **Flexible finger ducts** — Provides for easy installation and organizes cables simplifying moves, adds, and changes.
- **Cable pass through holes** — Provides ease of installation and cable maintenance.
- **Available in 2U version (CMH-DFD2U)** — Increases more space for Ethernet cable runs.
- **Available in single sided version (CMH-SFD1U)** — Manages more cables in 1U space, saving rack space and money.


Horizontal Cable Managers with Finger Duct

The standard design can be easily installed in any standard 19-inch cabinet. Made of high-quality SPCC and plastic materials to ensure a stable and durable structure. Helps keep network cabling neat and organized. This product is an ideal choice for building an efficient and reliable network system, and can meet the cable management needs in various scenarios.

Product Specifications		
Part Number	CMH-SFDS1U	CMH-DFDS2U
Style	Finger Duct with Cover	Finger Duct with Cover
No. of Rack Spaces	1U	2U
Type	Single Sided	Dual Sided
Backbone Material	Steel/SPCC	Steel/SPCC
Cover Material	Steel/SPCC	Steel/SPCC
Color	Black	Black
Orientation	Horizontal	Horizontal
Detachable Cover	Yes	Yes
Rack System Width	19.23"	19.23"
RDi mensions (HxWxD)	19"x4.46"x4.17" (483x113.3x106mm)	19"x3.31"x9.1" (483x84.1x232mm)
Application	Matching for 1U Open Rack	Matching for 2U Open Rack


Technical Drawing

CMH-SFDS1U



Technical Drawing

CMH-DFDS2U



Product List

I. Horizontal Cable Manager List

Item No.	#ID	Description
1	#29038	1U Plastic Single Sided Horizontal Cable Manager with Finger Duct
2	#29039	2U Plastic Single Sided Horizontal Cable Manager with Finger Duct
3	#29040	1U Plastic Dual Sided Horizontal Cable Manager with Finger Duct
4	#29034	1U Metal Horizontal Cable Manager with 5 D-rings
5	#72911	1U Metal Horizontal Lacer Panel with 5 Rotating and Detachable Plastic D-rings
6	#68690	1U Metal Recessed Horizontal Cable Manager with 4 D-rings & Brush Strip
7	#64184	1U Metal Horizontal Cable Manager with End Rings Manager
8	#29033	1U Metal Horizontal Cable Manager with Brush Strip
9	#59566	1U L-Shaped Horizontal Cable Lacer Bar with Angled 4" Offset, 5pcs/pack
10	#72910	1U 19" Cable Management Panel with 5 Detachable Plastic D-rings and Lacing Bar

II. Matching Product List

Item No.	#ID	Description
1	#29123	S5850-48S6Q 48-Port 10Gb SFP+ L2/L3 Data Center ToR/Leaf Switch
2	#29122	S5850-32S2Q 32-Port 10Gb SFP+ L2/L3 Data Center Leaf Switch
3	#70595	3ft (0.9m) Cat6 Snagless Unshielded (UTP) PVC CM Ethernet Network Patch Cable
4	#70664	2ft (0.6m) Cat6a Snagless Shielded (SFTP) PVC CMX Ethernet Network Patch Cable
5	#40191	1m (3ft) LC UPC to LC UPC Duplex OS2 PVC (OFNR) 2.0mm Fiber Optic Patch Cable
6	#68017	1m (3ft) MTP® Female Type B Plenum (OFNP) OM4 (OM3) 50/125 Elite Trunk Cable
7	#29015	25pcs/Bag 10in.L x 0.5in.W T type Reusable Cable Ties-Colorful
8	#61882	25m/Roll 1000in.L x0.48in.W Back to Back Reusable Cable Ties-Black