

RJ45 Surface Mount Box

IDEAL FOR HOME THEATER, VoIP OR ETHERNET IN-WALL WIREING INSTALLATIONS



Overview

The RJ45 Surface Mount Box features RJ45 female connectors as a fast, easy and cost-effective tool for expanding your audio/video, voice or Ethernet network. The box offers a variety of mounting options using adhesive tape, screws, etc. Just snap open the top cover to terminate 22–26 AWG Cat5e copper cables using a standard 110 IDC punch down tool.

The termination blocks are color-coded for easy T568A or T568B wiring. Zip ties are included for neatly securing the cables to the surface-mount box, which features rear routing slots to allow the box to be installed flush against a wall or ceiling.

Benefits

- Quick Cover Removal Provides Easy Access for Moves, Adds and Changes
- Pre-installed RJ45 Keystone Jacks for Quick Installation
- The Box Includes a Label Pocket to Meet TIA/EIA-606B Labeling Standards
- The Sticker Color Codes Combine Two Wirings of T568A & T568B
- Ideal for Home Theater, VoIP or Ethernet In-wall Wiring Installations


Specification

	SMB SUC6WHLP	SMB DUC6WHLP
Product Type	RJ45 Surface Mount Box	
Number of Ports	1	2
Network Type	Cat6 Unshielded	
Identification Type	Pocket Label	
Color	White	
Material	PC / ABS	
Dimension (HxWxD)	0.98"x1.94"x2.58" (25x49.2x65.6mm)	1.04"x2.44"x2.35" (26.4x62x59.7mm)
Operation Temperature	-20 to 68°C (-4 to 154.4°F)	


	SMBSFC6WHLP	SMBSFC6AWHLP	SMBDFC6WHLP	SMBDFC6AWHLP
Product Type	RJ45 Surface Mount Box			
Number of Ports	1	1	2	2
Network Type	Cat6 Shielded	Cat6a Shielded	Cat6 Shielded	Cat6a Shielded
Identification Type	Pocket Label			
Color	White			
Material	PC / ABS			
Dimension (HxWxD)	0.98"x1.95"x2.58" (25.0x49.2x65.6mm)		1.04"x2.44"x2.35" (26.4x62x59.7mm)	
Operation Temperature	-20 to 68°C (-4 to 154.4°F)			



Drawing



SMBSUC6WHLP




SMBDUC6WHLP



SMBSFC6WHLP**SMBSFC6AWHLP**

SMBDFC6WHLP**SMBDFC6AWHLP**



 <https://www.fs.com>



The information in this document is subject to change without notice. FS has made all efforts to ensure the accuracy of the information, but all information in this document does not constitute any kind of warranty.

Copyright © 2009-2022 FS.COM All Rights Reserved.