


A solid red circle.

1G/2.5G SFP Cable and Transceiver Modules Data Sheet

Product overview

The FS® 1000BASE Quad Small Form-Factor Pluggable (SFP) portfolio offers customers a wide variety of high-density and low-power 1000BASE Ethernet connectivity options for data center, high-performance computing networks, enterprise core and distribution layers, and service provider applications. The SFP-1G modules are our latest generation of 1000BASE transceiver modules solution based on a SFP form factor. (See Figure1)



•SFP1G-SX-85 •SFP1G-LX-31 •SFP-GB-GE-T •SFP1G-LX-31

Figure 1.

SFP 1000BASE Optical modules

Features and benefits

- Hot-swappable input/output device that plugs into an Ethernet SFP port
- Interoperable with other IEEE-compliant 1000BASE interfaces where applicable
- Digital optical monitoring capability for strong diagnostic capabilities
- Certified and tested on Cisco, Arista, Juniper, Brocade SFP 1G ports for superior performance, quality, and reliability. For more details, refer to the [FS Assured Program for Transceivers](#)

Table 1 describes the SFP 1000BASE portfolio.

Table 1 . SFP 1000 BASE portfolio

Product	Description	Connector type
SFP-GB-GE-T	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble	RJ-45
SFP-GB-GE-T-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble, I-Temp	RJ-45
SFP-GB-GE-TL	1000BASE-TL SFP Transceiver, RJ-45, 100m over Copper Caable	RJ-45
SFP-GB-GE-TL-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble, I-Temp	RJ-45
SFP-2.5G-T	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Calble	RJ-45
SFP-2.5G-T-I	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Cable, I-Temp	RJ-45
SFP1G-SX-85	1.25GBASE SX SFP Transceiver, LC, 550m over MMF	Duplex LC
SFP1G-SX-31	1000BASE SX SFP Transceiver, LC, 2 km over MMF	Duplex LC
SFP1G -LX-31	1000BASE LX/ LH SFP Transceiver, LC, 10 km over SMF	Duplex LC
SFP1G-LH-31	1.25GBASE LH SFP Transceiver, LC, 40km over SMF	Duplex LC
SFP1G-EX-55	1000BASE EX SFP Transceiver, LC, 40km over SMF, I-Temp	Duplex LC
SFP1G-ZX-55	1000BASE ZX SFP Transceiver, LC, 80km over SMF	Duplex LC
SFP1G-EZX-55	1000BASE EZX SFP Transceiver, LC, 120km over SMF	Duplex LC

SFP1G-ZXC-55	1000BASE ZXC SFP Transceiver, LC, 160km over SMF	Duplex LC
SFP12-BXMMF	622BASE BX SFP Transceiver, LC, 2 km over MMF, 1310nm/ 1550nm	Simplex LC
SFP12-BX	622BASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm	Simplex LC
SFP12-BX40	622BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm	Simplex LC
SFP12-BX80	622BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	Simplex LC
SFP12-BX120	622BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm	Simplex LC
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10km over SMF, 1310nm/ 1490nm, 1490nm/ 1310nm, 1310nm/ 1550nm, 1550nm/ 1310nm	Simplex LC
SFP-GE-2BX	1000BASE 2BX SFP Transceiver, LC, 10 km over SMF, 1310nm/ 1490nm	Duplex LC
SFP-GE-BX40	1000BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm	Simplex LC
SFP-GE-BX80	1000BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	Simplex LC
SFP-GE-BX120	1000BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm	Simplex LC
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 15 km over SMF, 1310nm/ 1550nm	Simplex LC
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm	Simplex LC
SFP-2G-BX80	2.5GBASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	Simplex LC
CWDM-SFP1G-ZX	1000BASE CWDM SFP Transceiver, LC , 80km over SMF, 1270nm-1610nm	Duplex LC
CWDM-SFP1G-EZX	1000BASE CWDM SFP Transceiver, LC, 100km over SMF, 1270nm-1610nm	Duplex LC
CWxx-SFP1G-ZXC	1000BASE CWDM SFP Transceiver, LC, 160km over SMF, 1470nm-1610nm	Duplex LC
CWxx-SFP1G-120-I	1000BASE CWDM SFP Transceiver, LC, 120km over SMF, 1470nm-1610nm	Duplex LC
DWDM-SFP1G-ZX	1000BASE DWDM SFP Transceiver, LC, 80km over SMF, C17-C61	Duplex LC
DWDM-SFP1G-EZX	1000BASE DWDM SFP Transceiver, LC, 100km over SMF, C17-C61	Duplex LC
DWxxx-SFP1G-120	1000BASE DWDM SFP Transceiver, LC, 120km over SMF, C17-C61	Duplex LC
DWCxx-SFP1G-ZXC	1000BASE DWDM SFP Transceiver, LC, 160km over SMF, C17-C61	Duplex LC
SFP-PCxx (0 . 5M, 1 M, 2M, 3M, 5M,7M)	1000BASE SFP Passive Copper Cable	Duplex LC
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10km over SMF, 1310nm/ 1490nm, 1490nm/ 1310nm, 1310nm/ 1550nm, 1550nm/ 1310nm	Simplex LC

SFP-GB-GE-T

The SFP-GB-GE-T transceiver supports up to 100m link lengths over a copper connection via a RJ-45 connector. Each SFP transceiver module is individually tested to be used on a series of switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for enterprise networking for LAN applications and different other networking places using copper connections.

SFP-GB-GE-T-I

The SFP-GB-GE-T-I transceiver supports up to 100m link lengths over a copper connection via a RJ-45 connector. Each SFP transceiver module is individually tested to be used on a series of switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 10/100/1000BASE-T SFP transceiver is ideal for enterprise networking for LAN applications and different other networking places using copper connections.

SFP-GB-GE-TL

The SFP-GB-GE-TL transceiver supports up to 100m link lengths over a copper connection via a RJ-45 connector. Each SFP transceiver module is individually tested to be used on a series of Arista switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for enterprise networking for LAN applications and different other networking places using copper connections.

SFP-GB-GE-TL-I

The SFP-GB-GE-TL-I transceiver supports up to 100m link lengths over a copper connection via a RJ-45 connector. Each SFP transceiver module is individually tested to be used on a series of Arista switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, this industrial optic transceiver provides 1G BASE Ethernet connectivity options for Gigabit Ethernet, Telecom and Data Centers, suitable for both outdoor and indoor deployments.

SFP-2.5G-T

The SFP-2.5G-T transceiver supports up to 100m link lengths over a copper connection via a RJ-45 connector. Each SFP transceiver module is individually tested to be used on a series of Generic switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption and high speed, the 2.5G SFP transceiver is ideal for enterprise networking for LAN applications and different other networking places using copper connections.

SFP-2.5G-T-I

The SFP-2.5G-T-I transceiver supports up to 100m link lengths over a copper connection via a RJ-45 connector. Each SFP transceiver module is individually tested to be used on switches. Featuring low power consumption and high speed, the 2.5G SFP transceiver is ideal for enterprise networking for LAN applications and different other networking places using copper connections.

SFP1G-SX-85

The SFP1G-SX-85 transceiver supports up to 550m link lengths over multi-mode fiber (MMF) using a wavelength of 850nm via a LC connector. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

SFP1G-SX-31 (2km)

The SFP1G-SX-31 transceiver supports up to 2 km link lengths over LC duplex MMF fiber. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

SFP1G-LX-31 (10km)

The SFP1G-LX-31 transceiver supports up to 10 km link lengths over LC duplex SMF fiber or up to 550m link lengths over LC duplex MMF fiber. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

SFP1G-LH-31 (40km)

The SFP1G-LH-31 transceiver supports up to 40km link lengths over LC duplex SMF fiber. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN

Networks, Data Center LAN & SAN Networks and other optical links.

SFP1G-EX-55 / SFP1G-EX-55(40km)

The SFP1G-EX-55 /SFP1G-EX-55-I transceiver supports up to 40km link lengths over LC duplex SMF fiber. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN &SAN Networks and other optical links.

SFP1G-ZX-55 (80km)

The SFP1G-ZX-55 transceiver supports up to 80km link lengths over LC duplex SMF fiber. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

SFP1G-EZX-55 (120km)

The SFP1G-EZX-55 transceiver supports up to 120km link lengths over LC duplex SMF fiber. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

SFP1G-ZXC-55 (160km)

The SFP1G-ZXC-55 transceiver supports up to 160km link lengths over LC duplex SMF fiber. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interfacecard (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks

SFP12-BXMMF (2km)

The SFP12-BXMMF transceiver provides up to 2 km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers .

SFP12-BX (20km)

The SFP12-BX transceiver provides up to 20km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP12-BX40

The SFP12-BX40 transceiver provides up to 40km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP12-BX80

The SFP12-BX80 transceiver provides up to 80km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This

bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP12-BX120

The SFP12-BX120 transceiver provides up to 120km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-GE-BX

The SFP-GE-BX transceiver provides up to 10/20km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-GE-2BX

The SFP-GE-2BX transceiver provides up to 10 km of 1000Base-BX throughput over single-mode fiber (SMF) via LC duplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-GE-BX40

The SFP-GE-BX80 transceiver provides up to 40km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-GE-BX80

The SFP-GE-BX80 transceiver provides up to 80km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-GE-BX120

The SFP-GE-BX120 transceiver provides up to 120km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-2G-BX (15km)

The SFP-2G-BX transceiver provides up to 15km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-2G-BX (20km)

The SFP-2G-BX transceiver provides up to 20km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

SFP-2G-BX80

The SFP-2G-BX80 transceiver provides up to 80km of 1000Base-BX throughput over single-mode fiber (SMF) via LC simplex connectors. This bi-directional unit must be used with another transceiver or network equipment of complementary wavelengths. It provides 1000BASE Ethernet connectivity options for Fast Ethernet, Telecom and Data Centers.

CWDM-SFP1G-ZX

The CWDM-SFP1G-ZX transceiver supports up to 80km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

CWDM-SFP1G-EZX

The CWDM-SFP1G-EZX transceiver supports up to 100km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP transceiver module is individually tested to be used on a series of FS switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

CWxx-SFP1G-ZXCa

The CWxx-SFP1G-ZXC transceiver supports up to 160km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP transceiver module is individually tested to be used on a series of FS switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

CWxx-SFP1G-120-I

The CWxx-SFP1G-120-I transceiver supports up to 120km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP transceiver module is individually tested to be used on a series of FS switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

DWDM-SFP1G-ZX

The DWDM-SFP1G-ZX transceiver supports up to 80km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

DWDM-SFP1G-EZX

The DWDM-SFP1G-EZX transceiver supports up to 100km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

DWxxx-SFP1G-120

The DWxxx-SFP1G-120 transceiver supports up to 120km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP

transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

DWCxx-SFP1G-ZXC

The DWCxx-SFP1G-ZXC transceiver supports up to 160km link lengths over single-mode fiber (SMF) via an LC duplex connector. Each SFP transceiver module is individually tested to be used on a series of Cisco switches, routers, servers, network interface card (NICs) etc. Featuring low power consumption, the hot swappable 1G SFP transceiver is ideal for Internet Service Provider (ISP) Gigabit Ethernet communication links, Enterprise LAN & SAN Networks, Data Center LAN & SAN Networks and other optical links.

SFP-PCxx

FS SFP Copper Twinax (Figure2) direct-attach cables are suitable for very short distances and offer a cost-effective way to connect within racks and across adjacent racks. FS offers passive Twinax cables in lengths of 0.5, 1, 2, 3, 5 and 7 meters or can be customized for longer meters.



Figure 2 .
SFP-PCxx

Product Specifications

Table 2 shows the key electrical characteristics for the 1000BASE SFP modules.

Table 2. Electrical specifications

Product	Description	Nominal datarate (Gbs)	Link meter
SFP-GB-GE-T	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble	1000Mbps	100m
SFP-GB-GE-T-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble, I-Temp	1000Mbps	100m
SFP-GB-GE-TL	1000BASE-TL SFP Transceiver, RJ-45, 100m over Copper Caable	1000Mbps	100m
SFP-GB-GE-TL-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble, I-Temp	1000Mbps	100m
SFP-2.5G-T	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Calble	2.5Gbps	100m
SFP-2.5G-T-I	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Cable, I-Temp	2.5Gbps	100m
SFP1G-SX-85	1.25GBASE SX SFP Transceiver, LC, 550m over MMF	1.25Gbps	550m
SFP1G-SX-31	1000BASE SX SFP Transceiver, LC, 2 km over MMF	1000Mbps	2km
SFP1G -LX-31	1000BASE LX/ LH SFP Transceiver, LC, 10 km over SMF	1.25Gbps	10km
SFP1G-LH-31	1.25GBASE LH SFP Transceiver, LC, 40km over SMF	1000Mbps	40km

SFP1G-EX-55	1000BASE EX SFP Transceiver, LC, 40km over SMF, I-Temp	1000Mbps	40km
SFP1G-ZX-55	1000BASE ZX SFP Transceiver, LC, 80km over SMF	1000Mbps	80km
SFP1G-EZX-55	1000BASE EZX SFP Transceiver, LC, 120km over SMF	1000Mbps	120km
SFP1G-ZXC-55	1000BASE ZXC SFP Transceiver, LC, 160km over SMF	1000Mbps	160km
SFP12-BXMMF	622BASE BX SFP Transceiver, LC, 2 km over MMF, 1310nm/ 1550nm	622Mbps	2km
SFP12-BX	622BASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm	622Mbps	20km
SFP12-BX40	622BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm	622Mbps	40km
SFP12-BX80	622BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	622Mbps	80km
SFP12-BX120	622BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm	622Mbps	120km
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10km over SMF, 1310nm/ 1490nm, 1490nm/ 1310nm, 1310nm/ 1550nm, 1550nm/ 1310nm	1000Mbps	10km
SFP-GE-2BX	1000BASE 2BX SFP Transceiver, LC, 10 km over SMF, 1310nm/ 1490nm	1000Mbps	10km
SFP-GE-BX40	1000BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm	1000Mbps	40km
SFP-GE-BX80	1000BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	1000Mbps	80km
SFP-GE-BX120	1000BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm	1000Mbps	120km
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 15 km over SMF, 1310nm/ 1550nm	2.5Gbps	15km
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm	2.5Gbps	20km
SFP-2G-BX80	2.5GBASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	2.5Gbps	80km
CWDM-SFP1G-ZX	1000BASE CWDM SFP Transceiver, LC , 80km over SMF, 1270nm-1610nm	1000Mbps	80km
CWDM-SFP1G-EZX	1000BASE CWDM SFP Transceiver, LC, 100km over SMF, 1270nm-1610nm	1000Mbps	100km
CWxx-SFP1G-ZXC	1000BASE CWDM SFP Transceiver, LC, 160km over SMF, 1470nm-1610nm	1000Mbps	160km
CWxx-SFP1G-120-I	1000BASE CWDM SFP Transceiver, LC, 120km over SMF, 1470nm-1610nm	1000Mbps	120km
DWDM-SFP1G-ZX	1000BASE DWDM SFP Transceiver, LC, 80km over SMF, C17-C61	1000Mbps	80km

DWDM-SFP1G-EZX	1000BASE DWDM SFP Transceiver, LC, 100km over SMF, C17-C61	1000Mbps	100km
DWxxx-SFP1G-120	1000BASE DWDM SFP Transceiver, LC, 120km over SMF, C17-C61	1000Mbps	120km
DWCxx-SFP1G-ZXC	1000BASE DWDM SFP Transceiver, LC, 160km over SMF, C17-C61	1000Mbps	160km
SFP-PCxx (0 . 5M, 1 M, 2M, 3M, 5M,7M)	1000BASE SFP Passive Copper Cable	1000Mbps	0.5, 1, 2, 3, 5, 7
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10km over SMF, 1310nm/ 1490nm, 1490nm/ 1310nm, 1310nm/ 1550nm, 1550nm/ 1310nm	1000Mbps	20km

Table 3 shows the key optical characteristics for the 1000BASE SFP modules.

Table 3. Optical specifications

Product	Description	Transmit Power (dBm)		Receive Power (dBm)		Transmit and Receive Wavelength (nm)
		Minimum	Maximum	Minimum	Maximum	
SFP-GB-GE-T	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble	-	-	-	-	-
SFP-GB-GE-T-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble, I-Temp	-	-	-	-	-
SFP-GB-GE-TL	1000BASE-TL SFP Transceiver, RJ-45, 100m over Copper Caable	-	-	-	-	-
SFP-GB-GE-TL-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Calble, I-Temp	-	-	-	-	-
SFP-2.5G-T	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Calble	-	-	-	-	-
SFP-2.5G-T-I	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Cable, I-Temp	-	-	-	-	-
SFP1G-SX-85	1.25GBASE SX SFP Transceiver, LC, 550m over MMF	-9.5	-3	-17	-3	850
SFP1G-SX-31	1000BASE SX SFP Transceiver, LC, 2 km over MMF	-9	-3	-19	-3	1310
SFP1G-LX-31	1000BASE LX/ LH SFP Transceiver, LC, 10 km over SMF	-9.5	-3	-23	-3	1310
SFP1G-LH-31	1.25GBASE LH SFP Transceiver, LC, 40km over SMF	-5	0	-24	-3	1310
SFP1G-EX-55	1000BASE EX SFP Transceiver, LC, 40km over SMF, I-Temp	-5	0	-24	-3	1550
SFP1G-ZX-55	1000BASE ZX SFP Transceiver, LC, 80km over SMF	0	5	-24	-3	1550
SFP1G-EZX-55	1000BASE EZX SFP Transceiver, LC, 120km over SMF	0	5	-32	-10	1550

SFP1G-ZXC-55	1000BASE ZXC SFP Transceiver, LC, 160km over SMF	1	6	-33	-10	1550
SFP12-BXMMF	622BASE BX SFP Transceiver, LC, 2 km over MMF, 1310nm/ 1550nm	-9	-3	-21	-3	1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)
SFP12-BX	622BASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm	-9	-3	-23	-3	1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)
SFP12-BX40	622BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm	-2(MQEL-K40F35) - 5(MQEL-K40B53)	3(MQEL-K40F35) - 5(MQEL-K40B53)	-23	-3	1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)
SFP12-BX80	622BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	-2	3	-24	-3	1490/1550 (Tx/Rx) 1550/1490 (Tx/Rx)
SFP12-BX120	622BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm	-1	4	-31	-8	1490/1550 (Tx/Rx) 1550/1490(Tx/Rx)
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10km over SMF, 1310nm/ 1490nm, 1490nm/ 1310nm, 1310nm/ 1550nm, 1550nm/ 1310nm	-9	-3	-23	-3	1310/1490 (Tx/Rx) 1490/1310 (Tx/Rx) 1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)
SFP-GE-2BX	1000BASE 2BX SFP Transceiver, LC, 10 km over SMF, 1310nm/ 1490nm	-9	-3	-23	-3	10/1490 (Tx/Rx) 1490/1310(Tx/Rx)
SFP-GE-BX40	1000BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm	-2(MQEL-K40F35) - 5(MQEL-K40B53)	3(MQEL-K40F35) - 5(MQEL-K40B53)	-23	-3	1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)
SFP-GE-BX80	1000BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	-2	3	-24	-3	1490/1550 (Tx/Rx) 1550/1490 (Tx/Rx)
SFP-GE-BX120	1000BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm	-1	4	-31	-8	1490/1550 (Tx/Rx) 1550/1490 (Tx/Rx)
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 15 km over SMF, 1310nm/ 1550nm	-5	0	-18	0	1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm	-9	-3	-23	-3	1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)
SFP-2G-BX80	2.5GBASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm	-2	3	-24	-3	1490/1550 (Tx/Rx) 1550/1490 (Tx/Rx)
CWDM-SFP1G-ZX	1000BASE CWDM SFP Transceiver, LC , 80km over SMF, 1270nm-1610nm	0	4	-24	-8	1270 to 1610
CWDM-SFP1G-EZX	1000BASE CWDM SFP Transceiver, LC, 100km over SMF, 1270nm-1610nm	0	4	-32	-8	1270 to 1610
CWxx-SFP1G-ZXC	1000BASE CWDM SFP Transceiver, LC, 160km over SMF, 1470nm-1610nm	1	6	-33	-10	1470 to 1610

CWxx-SFP1G-120-I	1000BASE CWDM SFP Transceiver, LC, 120km over SMF, 1470nm-1610nm	0	5	-31	0	1470 to 1610
DWDM-SFP1G-ZX	1000BASE DWDM SFP Transceiver, LC, 80km over SMF, C17-C61	0	5	-24	-3	1563.86 to 1528.77
DWDM-SFP1G-EZX	1000BASE DWDM SFP Transceiver, LC, 100km over SMF, C17-C61	0	5	-32	-8	1563.86 to 1528.77
DWxxx-SFP1G-120	1000BASE DWDM SFP Transceiver, LC, 120km over SMF, C17-C61	0	5	-30	-10	1563.86 to 1528.77
DWCxx-SFP1G-ZXC	1000BASE DWDM SFP Transceiver, LC, 160km over SMF, C17-C61	1	6	-33	-10	1563.86 to 1528.77
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10km over SMF, 1310nm/ 1490nm, 1490nm/ 1310nm, 1310nm/ 1550nm, 1550nm/ 1310nm	-9	-3	-23	-3	1310/1490 (Tx/Rx) 1490/1310 (Tx/Rx) 1310/1550 (Tx/Rx) 1550/1310 (Tx/Rx)

Table 4 shows the mechanical characteristics for the 1000BASE SFP modules.

Table 4. Mechanical specifications

Parameter	Product	Weight
Module dimension with pull tab	(HxWxD) 8 . 5 x 13 . 4 x 5 6 . 5 mm	
Module weight (Max)	Optical modules	
	SFP-PC005	50. 5g
	SFP-PC01	64.8g
	SFP-PC02	88g
	SFP-PC03	113.6g
	SFP-PC05	242.4g
	SFP-PC07	317.6g

Warranty

- Standard warranty: 5 years
- For more information for FS Returns & Refund spolicy, visit [Products Warranty](#) or [Returns & Refunds](#)

Ordering information

Table 5 provides the ordering information for SFP 1000BASE modules and related cables.

Table 5. Ordering information

Part number	Description
SFP Optics Modules	
SFP-GB-GE-T	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Cable
SFP-GB-GE-T-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Cable, I-Temp
SFP-GB-GE-TL	1000BASE-TL SFP Transceiver, RJ-45, 100m over Copper Cable

SFP-GB-GE-TL-I	1000BASE-T SFP Transceiver, RJ-45, 100m over Copper Cable, I-Temp
SFP- 2. 5G - T	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Cable
SFP-2.5G-T-I	2.5GBASE-T SFP Transceiver, RJ-45, 100m over Copper Cable, I-Temp 1 . 25GBASE SX SFP Transceiver, LC, 550m over MMF
SFP1 G - SX- 8 5	1.25GBASE SX SFP Transceiver, LC, 10 km over SMF
SFP1 G - SX- 3 1	1000BASE SX SFP Transceiver, LC, 2 km over MMF
SFP1 G - LX- 3 1	1.25GBASE LX/ LH SFP Transceiver, LC, 10 km over SMF
SFP1 G - LH- 3 1	1000BASE LH SFP Transceiver, LC, 40km over SMF
SFP1 G - EX- 5 5	1000BASE EX SFP Transceiver, LC, 40km over SMF, I-Temp
SFP1 G - ZX- 5 5	1000BASE ZX SFP Transceiver, LC, 80km over SMF
SFP1G-EZX-55	1000BASE EZX SFP Transceiver, LC, 120km over SMF 1000BASE ZXC SFP Transceiver, LC, 160km over SMF
SFP1G-ZXC-55	1000BASE ZXC SFP Transceiver, LC, 160km over SMF
SFP12-BXMMF	622BASE BX SFP Transceiver, LC, 2km over MMF, 1310nm/ 1550nm
SFP12-BXMMF	622BASE BX SFP Transceiver, LC, 2km over MMF, 1550nm/ 1310nm
SFP12-BX	622BASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm
SFP12-BX	622BASE BX SFP Transceiver, LC, 20km over SMF, 1550nm/ 1310nm
SFP12-BX40	622BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm
SFP12-BX40	622BASE BX40 SFP Transceiver, LC, 40km over SMF, 1550nm/ 1310nm
SFP12-BX80	622BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm
SFP12-BX80	622BASE BX80 SFP Transceiver, LC, 80km over SMF, 1550nm/ 1490nm
SFP1 2 - BX1 2 0	622BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm
SFP1 2 - BX1 2 0	622BASE BX120 SFP Transceiver, LC, 120km over SMF, 1550nm/ 1490nm
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10 km over SMF, 1310nm/ 1490nm
SFP-GE-BX	1000BASE BX SFP Transceiver, LC, 10 km/20km over SMF, 1490nm/ 1310nm,
SFP-GE-2BX	1000BASE 2BX SFP Transceiver, LC, 10 km over SMF, 1310nm/ 1490nm
SFP-GE-2BX	1000BASE 2BX SFP Transceiver, LC, 10 km over SMF, 1490nm/ 1310nm
SFP-GE-BX40	1000BASE BX40 SFP Transceiver, LC, 40km over SMF, 1310nm/ 1550nm
SFP-GE-BX40	1000BASE BX40 SFP Transceiver, LC, 40km over SMF, 1550nm/ 1310nm
SFP-GE-BX80	1000BASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm
SFP-GE-BX80	1000BASE BX80 SFP Transceiver, LC, 80km over SMF, 1550nm/ 1490nm
SFP-GE-BX120	1000BASE BX120 SFP Transceiver, LC, 120km over SMF, 1490nm/ 1550nm
SFP-GE-BX120	1000BASE BX120 SFP Transceiver, LC, 120km over SMF, 1550nm/ 1490nm
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 15 km over SMF, 1310nm/ 1550nm
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 15 km over SMF, 1550nm/ 1310nm
SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 20km over SMF, 1310nm/ 1550nm

SFP-2G-BX	2.5GBASE BX SFP Transceiver, LC, 20km over SMF, 1550nm/ 1310nm
SFP- 2 G - BX8 0	2.5GBASE BX80 SFP Transceiver, LC, 80km over SMF, 1490nm/ 1550nm
SFP- 2 G - BX8 0	2.5GBASE BX80 SFP Transceiver, LC, 80km over SMF, 1550nm/ 1490nm
CWxx-SFP1G-ZXC	1000BASE CWDM SFP Transceiver , LC, 160km over SMF, 1470nm-1610nm
CWxx-SFP1G-120-I	1000BASE CWDM SFP Transceiver , LC, 120km over SMF, 1470nm-1610nm
DWDM-SFP1G-ZX	1000BASE DWDM SFP Transceiver, LC, 80km overS MF, C17-C61
DWDM-SFP1G-EZX	1000BASE DWDM SFP Transceiver, LC, 100km over SMF, C17-C61
DWxxx-SFP1G-120	1000BASE DWDM SFP Transceiver, LC, 120km over SMF, C17-C61
DWCxx-SFP1G-ZXC	1000BASE DWDM SFP Transceiver, LC, 160km over SMF, C17-C61
SFP+ Copper Cables	
SFP-PC005	1000BASE SFP Passive Copper Cable,0.5-meter
SFP-PC01	1000BASE SFP Passive Copper Cable, 1-meter
SFP-PC02	1000BASE SFP Passive Copper Cable, 2-meter
SFP-PC03	1000BASE SFP Passive Copper Cable,3-meter
SFP-PC05	1000BASE SFP Passive Copper Cable, 5-meter
SFP-PC07	1000BASE SFP Passive Copper Cable, 7-meter

Regulatory and standards compliance

Standards

- IEEE 802 . 3z
- IEEE 802 . 3ah
- GR-20-CORE: Generic Requirements for Optical Fiber and Optical Fiber Cable
- GR-326-CORE: Generic Requirements for Single-Mode Optical Connectors and Jumper Assemblies
- GR-1435-CORE: Generic Requirements for Multifiber Optical Connectors
- IEC60603-7 :2000 : Generic Requirements for RJ- 45 connectors

Safety

- Laser Class I 21CFR1040 LN # 507/ 2001
- Laser Class I IEC 60825 - 1


Table 6. Laser class for the SFP 1000BASE optical modules

Product	Laser class
SFP1G-SX-85	1
SFP1G-SX-31	1
SFP1G-LX-31	1
SFP1G-LH-31	1
SFP1G-EX-55	1

SFP1G-ZX-55	1
SFP1G-EZX-55	1
SFP1G-ZXC-55	1
SFP12-BXMMF	1
SFP12-BX	1
SFP12-BX40	1
SFP12-BX80	1
SFP12-BX120	1
SFP-GE-BX	1
SFP-GE-2BX	1
SFP-GE-BX40	1
SFP-GE-BX80	1
SFP-GE-BX120	1
SFP-2G-BX	1
SFP-2G-BX80	1
CWDM-SFP1G-ZX	1
CWDM-SFP1G-EZX	1
CWxx-SFP1G-ZXC	1
CWxx-SFP1G-120-I	1
DWDM-SFP1G-ZX	1
DWDM-SFP1G-EZX	1
DWxxx-SFP1G-120	1
DWCxx-SFP1G-ZXC	1

Additional information

For more information about 1000BASE SFP optics and copper modules, contacty our account manager or visit <https://www.fs.com/c/optics-and-transceivers-9>



Delaware, United States

Address: Delaware: 380 Centerpoint Blvd, New Castle, DE 19720, United States
Email: US@fs.com
Tel: +1 (888) 468-9910

Germany

Address: Röntgenstraße 18, 85757 Karlsfeld, Germany
Email: DE@fs.com
Tel: +49 (0) 8131 377 3008

Australia

Address: 57-59 Edison Rd, Dandenong South, VIC 3175, Australia
Email: AU@fs.com
Tel: +61 3 5909 9990

Japan

Address: JS Progress Building 5F, 4-1-23, Heiwajima, Ota Ku, Tokyo, 143-0006, Japan
Email: JP@fs.com
Tel: +81-3-6897-9438

Wuhan (China)

Address: Building A1-A4, Chuangxin Tiandi, No. 88 Guanggu Sixth Road, Hongshan District
Email: sales@feisu.com
Tel: +86(400)865 2852

California, United States

Address: California: 15241 Don Julian Rd, City of Industry, CA 91745, United States
Email: US@fs.com
Tel: +1 (888) 468-9910

United Kingdom

Address: Unit 8, Urban Express Park, Union Way, Aston, Birmingham B6 7FH, United Kingdom
Email: UK@fs.com
Tel: +44 (0) 121 726 4775

Singapore

Address: 7002 ANG MO KIO AVENUE 5 #05-02 Singapore 569914
Email: SG@fs.com
Tel: +65 31381992

Shenzhen (China)

Address: Room 1903-1904, Block C, China Resources Tower, Dachong Community, Yuehai Subdistrict, Nanshan District
Email: sales@feisu.com
Tel: +86(400)865 2852

Shanghai (China)

Address: Unit 1201, Lee Gardens Shanghai Office Tower, No. 668 Xinzha Road, Jing'an District
Email: sales@feisu.com
Tel: +86(400)865 2852



FS has several offices around the world. Addresses, phone numbers are listed on the FS Website at https://www.fs.com/contact_us.html. FS and FS logo are trademarks or registered trademarks of FS in the U.S. and other countries.