


Fibers Fusion Splice Tray



Fiber Fusion Splice Tray

Fiber optic splice trays are designed to provide a location to store and to protect the fiber cables and the splices. Each tray provides space for mounting fiber splice protectors and excess fiber. It's divided into common splice tray, module integration and splitter tray.

Optical fiber glass inside the fiber tray can be melt with any other strand optical fiber in the tray, thus different fiber optic cables can be melt connected directly via the tray. Optical cable fiber can also be melted with the fiber optic pigtail end, and via pigtail it can connect out to other fiber optic equipment.

Standards Compliance


- CE Compliant
- ISO9001 Certificate

Specifications

Product Specification		
ID	#28774	#28769
Capacity	24 Fibers	6 Fibers
Material	ABS	ABS
Dimensions(HxWxD)	0.72"x6.26"x4.13" (18.3x159.1x104.9mm)	0.52"x3.83"x3.31" (13.3x97.2x84mm)
Life	1000 times	1000 times
Tensile Strength	>1000N	>1000N
Working Temperature	-40 to 60°C (-40 to 140°F)	-40 to 60°C (-40 to 140°F)
ABS Heat Resistance	85 to 100°C (185 to 212°F)	85 to 100°C (185 to 212°F)
Relative Humidity	≤ 85% (30°)	≤ 85% (30°)
Air Pressure	70Kpa~106Kpa	70Kpa~106Kpa
Sealing Performance	Remain Unchanged for 72h on Pressure 70kpa	
Application	Fiber Splice Enclosure, Fiber Termination Box, Cable Distribution Box	

Technical Drawing

• 24F



• 6F

