

Cat6 UTP Patch Cables

Ideal for 1/10GBase-T Copper Cabling Solution



Overview

Cat6 network patch cable is the cost-effective solution for data center and SMB applications. Design for computer, hubs, switches, routers, DSL/cable modems and patch panel in Gigabit datacenter application. With fast transmission and excellent signal quality, it ensures peak performance through your LAN.

Application

- Rated for any 1/10GBase-T Ethernet.
- Perfect for data center and SMB applications.
- Ideal for switches, servers, patch panels, or other equipment.

Key Features

- Protected by LSZH jacket
- Stranded Pure Bare Copper
- RJ45 Plugs with 50 Microinches Gold-plated Connectors
- Snagless Design Protects Clips When Plugging and Unplugging
- Multiple Colors and Lengths Helps Simplify Complicated Cable Runs
- 4 Twisted Pairs and Cross Separator Reduce Crosstalk, Noise and Interference
- Tested with a Fluke DSX-8000 Versiv CableAnalyzer
- CE, Reach, RoHS Certified

Specification

Product Type	
Shielding Type	Unshielded (U/UTP)
Termination End	RJ45 Plug
Reference Standard	ISO/IEC 11801, ANSI/TIA-568.2-D
Conductor	
Conductor Type	Stranded
Conductor Material	Pure Bare Copper
Wire Gauge (AWG)	24 (7/0.20mm)
Conductor Qty.	4 Twisted Pairs
Insulation	
Insulation Material	HDPE
Insulation Diameter (mm)	0.98 ± 0.05
Core Color	A. Orange, White-Orange, B. Blue, White-Blue, C. Green, White-Green, D. Brown, White-Brown
Sheath	
Material	LSZH (Complies RoHS)
Outer O.D. (mm)	6.1 ± 0.4
Thickness (mm)	0.55 ± 0.05
Color	Blue/ Gray/ Black
Surface	Clean, Frap, Satiation

Specification

Electrical Characteristics (20 °C)	
Data Rate Support	1/10GBase-T
Standard Bandwidth (MHz)	250
Reference Bandwidth (MHz)	550
1-250MHz, Characteristic Impedance (Ω)	100 ± 15
Max. DC Conductor ResistanceUnbalance (%)	5.0
1 -250MHz, Delay Skew 20°C (ns/100m)	≤45
Max. DC Resistance 20°C (Ω/100m)	9.38

Sheath Physical Properties	
Before Aging Tensile Strength (Mpa)	≥10
Before Aging Elongation (%)	≥125
Aging Period (°C×hrs)	100°C×24h×7d
After Aging Tensile Strength (Mpa)	≥8
After Aging Elongation (%)	≥100
Cold Bend (-20±2°C×4h)	No Visible Cracks

Surface Printing	
Letter Height (mm)	3.0 ± 0.3
Color	Black

Specification

Others	
Rip Cord	No
Drain Wire	No