

Fiber Optic Terminal Box Datasheet

Without Pigtailed or Adapters



Overview

FTB-SC8-WOPA type fiber optic terminal box is designed for FTTx application, which is cable to meet at least 8 users requirements. It can help splicing, splitting, storage and management with suitable space. Simple with light weight in design, special snap clip close system coinvent for user, protecting the fiber to pigtail splice.

Application

- Widely used in optical fiber communication industry.
- It can be used for the fixing of optical cable terminals, the fusion of optical cables and pigtails, and the accommodation and protection of remaining fibers.

Benefits

- Meet Less Than $\Phi 12\text{mm}$ Fiber Cable Diameter and 8 Figure Drop Cable Connection;
- 8-core Splicing Tray, and The Maximum Capacity is 8 Cores;
- The Box Body is Mechanically Sealed, with Good Sealing Performance and Waterproof.
- It Supports Indoor and Outdoor Use, IP55 Protection Level;
- Wall-mount and Pole-mount Model;
8× SC Simplex/8× LC Duplex Adapters and 1× 1:8 Mini PLC.
- Can be Installed;
- It Adopts The Combination of Fiber Disc and Flap, Which is More Practical;
- Supports Pulling Optical Cables, Which is Convenient and Widely Used;

FEATURES

Product Type	
Model	FTB-SC8-WOPA
Color	Grey White
Material	PC+ABS

Installation	
Adaptor	8 x SC simplex / 8 x LC duplex
Splice tray	8 Cores
Splitter	1:8 mini PLC
Input port	2 port≤12mm
Output port	8 drop cable
Installation mode	Pole/Wall mounted

Protection Performance	
RoHS2.0	Yes
UV protection	500h
Flame retardant performance	UL94 V0
Protection Level	IP55

FEATURES

Specification	
Dimension L*W*D mm	209*180*50
Weight	1kg