




KEYSIGHT
TECHNOLOGIES

IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 08/25/2025 16:18:25

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Test Info	4
4.	Port Map	5
5.	Aggregate Graphs	6
6.	IterationCharts	14
7.	Aggregated Results	20
8.	Per Flow Results	22
9.	Iteration Data	24
10.	Theoretical Max Rates	36

RFC2544 - Throughput/Latency - Info

Test Information

Product Information

Product Label : N8550-24CD8D
 Product Version : 4.5.3E
 Serial Number : 219801A6AM6242V0000B
 Comments :

Test Settings

Date Executed : 08/25/2008
 Time Executed : 16:18:25
 User Name : FS.COM
 Number of Trials Executed : 1
 Stream Duration (sec) : 20
 Calculate Latency : True
 Latency Type : Store and Forward

Output Parameters

Number of Trials Passed : N/A
 Test Duration (sec) : 00:31:33

RFC2544 - Throughput/Latency - Info

Test Information

Port Information

Port Count: 8
 Port Speeds: 100000 Mbps; 400000 Mbps; 200000 Mbps
 Additional Details:

Topology Information

Topology Count: 3
 Device Group Count: 3
 Protocols: Ethernet
 Additional Details:

Traffic Information

Traffic-Item Count: 3
 Source-Destination Mesh: One - One
 Route Mesh: One - One
 Bi-directional: False
 Additional Details:

Packet Stack Information

Frame Size Type: Fixed
 Additional Layer 2 Details: Frame Ordering Type: No Ordering
 Packet Type: Ethernet
 Source Start Port:
 Destination Start Port:
 Additional Layer 4 Details:

Test Execution Information


Version Used: 10.00.2312.4
 Test Execution Date: Friday 08 August 2025 - 16:18:26
 Test Result Location: C:\Users\Aurelie.huang\AppData\Local\Ixia\IxNetwork\data\result\DP.Rfc2544Tput\4a2907c8-3edd-43f9-a9a3-77e33342134c\Run0001
 Additional Details:

RFC2544 - Throughput/Latency - Port Map Information


Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.36.15.201/15.1	100000	10.36.15.201/16.1	100000
	10.36.15.201/16.1	100000	10.36.15.201/15.1	100000


RFC2544 - Throughput/Latency - Aggregated Graph

Total Frames Transmitted and Received



RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Aggregated Graph**Aggregated Frame Loss**

Trial - Framesize - Iteration


RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Line Rate




RFC2544 - Throughput/Latency - Per Flow Graph





RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Latency



RFC2544 - Throughput/Latency - Per Flow Graph


Tx / Rx Frame Count




Trial

RFC2544 - Throughput/Latency - Iteration Graph


Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128




Aggregated Frame Loss for Trial 1 and Framesize 256




Aggregated Frame Loss for Trial 1 and Framesize 512




Aggregated Frame Loss for Trial 1 and Framesize 1024



Aggregated Frame Loss for Trial 1 and Framesize 1280




Aggregated Frame Loss for Trial 1 and Framesize 1518




RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	L2 Throughput				L1 Throughput Rate Mbps	Throughput (frames)	Latency (ns)		
	Tx Rate	Rx Rate							
	%	Real %	FPS	Mbps					
Trial: 1 / FS: 64 / Iter: 9	100.0	100.0	297619045.5	152,380.95	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	5952380952 5952380952 0 0.0	Min : 5912 Max : 6120 Avg : 6062	
Trial: 1 / FS: 128 / Iter: 9	100.0	100.0	168918917.8	172,972.97	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	3378378378 3378378378 0 0.0	Min : 5915 Max : 6107 Avg : 6055	
Trial: 1 / FS: 256 / Iter: 9	100.0	100.0	90579709.5	185,507.25	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	1811594202 1811594202 0 0.0	Min : 5997 Max : 6190 Avg : 6141	
Trial: 1 / FS: 512 / Iter: 9	100.0	100.0	46992481.0	192,481.20	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	939849624 939849624 0 0.0	Min : 5902 Max : 6047 Avg : 5998	
Trial: 1 / FS: 1024 / Iter: 9	100.0	100.0	23946360.1	196,168.58	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	478927204 478927204 0 0.0	Min : 5877 Max : 6020 Avg : 5963	
Trial: 1 / FS: 1280 / Iter: 9	100.0	100.0	19230769.2	196,923.08	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	384615384 384615384 0 0.0	Min : 5917 Max : 6065 Avg : 6008	

Column Header	Column Header Description
Trial	Trial number of the test run
Frame Size	The size of the frames used in the test
Trial / Framesize / Iteration	Iteration number of test
L2Tx Rate %	Aggregated L2 Throughput Transmit-side Line Rate
L2Rx Rate %	Aggregated L2 Throughput Receive-side Line Rate
L2Rx FPS	Aggregated L2 Throughput Receive-side Frame Rate
L2Rx Mbps	Aggregated L2 Throughput Receive-side Rate
L1Tx Mbps	Aggregated L1 Throughput Transmit-side Rate
L1Rx Mbps	Aggregated L1 Throughput Receive-side Rate
L1 Lost Bits%	Aggregated L1 Bits Loss Percentage
Tx Count	Throughput (frames) Sent Count
Rx Count	Throughput (frames) Received Count
Loss Count	Throughput (frames) Lost Count
Loss%	Throughput (frames) Loss Percentage
MinLatency (ns)	Minimum Latency Observed In Nanoseconds
MaxLatency (ns)	Maximum Latency Observed In Nanoseconds
AvgLatency (ns)	Average Latency Observed In Nanoseconds

RFC2544 - Throughput/Latency - Per Flow Statistics

Trial / Framesize / Iteration / Flow Group	Tx Port	Rx Port	L2 Throughput					L1 Throughput	Throughput (frames)	Latency (ns)	
			Tx Rate		Rx Rate						
			%	Real %	Real %	FPS	Mbps				
Trial: 1 / FS: 64 / Iter: 9	15	16	100.00		100	148809522.7	76190.48		Tx : 2976190476 Rx : 2976190476 Loss : 0 Loss% : 0.000	Min : 5912 Max : 6090 Avg : 6040	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 9	16	15	100.00		100	148809522.8	76190.48		Tx : 2976190476 Rx : 2976190476 Loss : 0 Loss% : 0.000	Min : 5955 Max : 6120 Avg : 6083	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 128 / Iter: 9	15	16	100.00		100	84459458.9	86486.49		Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000	Min : 5915 Max : 6085 Avg : 6034	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 128 / Iter: 9	16	15	100.00		100	84459458.9	86486.49		Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000	Min : 5952 Max : 6107 Avg : 6075	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 256 / Iter: 9	15	16	100.00		100	45289854.8	92753.62		Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000	Min : 5997 Max : 6155 Avg : 6121	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 256 / Iter: 9	16	15	100.00		100	45289854.7	92753.62		Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000	Min : 6030 Max : 6190 Avg : 6161	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 512 / Iter: 9	15	16	100.00		100	23496240.5	96240.60		Tx : 469924812 Rx : 469924812 Loss : 0 Loss% : 0.000	Min : 5902 Max : 6027 Avg : 5976	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 512 / Iter: 9	16	15	100.00		100	23496240.5	96240.60		Tx : 469924812 Rx : 469924812 Loss : 0 Loss% : 0.000	Min : 5957 Max : 6047 Avg : 6020	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 1024 / Iter: 9	15	16	100.00		100	11973180.0	98084.29		Tx : 239463602 Rx : 239463602 Loss : 0 Loss% : 0.000	Min : 5877 Max : 5972 Avg : 5939	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											

Trial: 1 / FS: 1024 / Iter: 9 16 15 100.00 100 11973180.0 98084.29								Tx : 239463602 Min : 5920 Rx : 239463602 Max : 6020 Loss : 0 Avg : 5986 Loss% : 0.000	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001									
Trial: 1 / FS: 1280 / Iter: 9 15 16 100.00 100 9615384.6 98461.54								Tx : 192307692 Min : 5917 Rx : 192307692 Max : 6020 Loss : 0 Avg : 5987 Loss% : 0.000	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001									
Trial: 1 / FS: 1280 / Iter: 9 16 15 100.00 100 9615384.6 98461.54								Tx : 192307692 Min : 5967 Rx : 192307692 Max : 6065 Loss : 0 Avg : 6029 Loss% : 0.000	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001									

RFC2544 - Throughput/Latency - Iteration Statistics

Trial / Framesize / Iteration / Flow Group	Tx Port	Rx Port	L2 Throughput				L1 Throughput Mbps	Throughput (frames)	Latency (ns)		
			Tx Rate		Rx Rate						
			%	Real %	Real %	FPS					Mbps
Trial: 1 / FS: 64 / Iter: 1	15	16	10.00		10.00	14880952.4	7619.05	Tx : 297619048 Rx : 297619048 Loss : 0 Loss% : 0.000	Min : 5890 Max : 5945 Avg : 5906		
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 1	16	15	10.00		10.00	14880952.4	7619.05	Tx : 297619048 Rx : 297619048 Loss : 0 Loss% : 0.000	Min : 5932 Max : 5987 Avg : 5949		
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 2	15	16	55.00		55.00	81845356.9	41904.82	Tx : 1636904762 Rx : 1636904762 Loss : 0 Loss% : 0.000	Min : 5907 Max : 6000 Avg : 5948		
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 2	16	15	55.00		55.00	81845356.9	41904.82	Tx : 1636904762 Rx : 1636904762 Loss : 0 Loss% : 0.000	Min : 5950 Max : 6045 Avg : 5988		
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 3	15	16	77.50		77.50	115327263.3	59047.56	Tx : 2306547619 Rx : 2306547619 Loss : 0 Loss% : 0.000	Min : 5900 Max : 6015 Avg : 5961		
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 3	16	15	77.50		77.50	115327263.3	59047.56	Tx : 2306547619 Rx : 2306547619 Loss : 0 Loss% : 0.000	Min : 5950 Max : 6055 Avg : 6001		
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 4	15	16	88.75		88.75	132068365.7	67619.00	Tx : 2641369048 Rx : 2641369048 Loss : 0 Loss% : 0.000	Min : 5917 Max : 6022 Avg : 5969		
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 4	16	15	88.75		88.75	132068365.7	67619.00	Tx : 2641369048 Rx : 2641369048 Loss : 0 Loss% : 0.000	Min : 5950 Max : 6060 Avg : 6009		
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 5	15	16	94.38		94.38	140438650.9	71904.59	Tx : 2808779762 Rx : 2808779762 Loss : 0 Loss% : 0.000	Min : 5910 Max : 6032 Avg : 5976		
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001											

Trial: 1 / FS: 64 / Iter: 5	16	15	94.38	94.38	140438650.9	71904.59	Tx : 2808779762	Min : 5955
							Rx : 2808779762	Max : 6067
							Loss : 0	Avg : 6017
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	15	16	97.19	97.19	144624597.0	74047.79	Tx : 2892485119	Min : 5910
							Rx : 2892485119	Max : 6027
							Loss : 0	Avg : 5982
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	16	15	97.19	97.19	144624597.0	74047.79	Tx : 2892485119	Min : 5947
							Rx : 2892485119	Max : 6070
							Loss : 0	Avg : 6023
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 7	15	16	98.59	98.59	146716641.5	75118.92	Tx : 2934337798	Min : 5907
							Rx : 2934337798	Max : 6030
							Loss : 0	Avg : 5987
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 7	16	15	98.59	98.59	146716641.6	75118.92	Tx : 2934337798	Min : 5957
							Rx : 2934337798	Max : 6072
							Loss : 0	Avg : 6028
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 8	15	16	99.30	99.30	147763347.3	75654.83	Tx : 2955264137	Min : 5927
							Rx : 2955264137	Max : 6035
							Loss : 0	Avg : 5992
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 8	16	15	99.30	99.30	147763347.3	75654.83	Tx : 2955264137	Min : 5955
							Rx : 2955264137	Max : 6075
							Loss : 0	Avg : 6034
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 9	15	16	100.00	100.00	148809522.7	76190.48	Tx : 2976190476	Min : 5912
							Rx : 2976190476	Max : 6090
							Loss : 0	Avg : 6040
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 9	16	15	100.00	100.00	148809522.8	76190.48	Tx : 2976190476	Min : 5955
							Rx : 2976190476	Max : 6120
							Loss : 0	Avg : 6083
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 128 / Iter: 1	15	16	10.00	10.00	8445945.9	8648.65	Tx : 168918919	Min : 5895
							Rx : 168918919	Max : 5952
							Loss : 0	Avg : 5912
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	

Trial: 1 / FS: 128 / Iter: 1	16	15	10.00	10.00	8445945.9	8648.65	Tx : 168918919 Rx : 168918919 Loss : 0 Loss% : 0.000	Min : 5937 Max : 5992 Avg : 5955
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 2	15	16	55.00	55.00	46452718.0	47567.58	Tx : 929054054 Rx : 929054054 Loss : 0 Loss% : 0.000	Min : 5910 Max : 5987 Avg : 5946
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 2	16	15	55.00	55.00	46452717.9	47567.58	Tx : 929054054 Rx : 929054054 Loss : 0 Loss% : 0.000	Min : 5950 Max : 6032 Avg : 5987
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 3	15	16	77.50	77.50	65456070.1	67027.02	Tx : 1309121622 Rx : 1309121622 Loss : 0 Loss% : 0.000	Min : 5912 Max : 6007 Avg : 5962
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 3	16	15	77.50	77.50	65456070.3	67027.02	Tx : 1309121622 Rx : 1309121622 Loss : 0 Loss% : 0.000	Min : 5960 Max : 6047 Avg : 6002
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 4	15	16	88.75	88.75	74957689.7	76756.67	Tx : 1499155405 Rx : 1499155405 Loss : 0 Loss% : 0.000	Min : 5915 Max : 6017 Avg : 5967
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 4	16	15	88.75	88.75	74957689.7	76756.67	Tx : 1499155405 Rx : 1499155405 Loss : 0 Loss% : 0.000	Min : 5952 Max : 6055 Avg : 6007
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 5	15	16	94.38	94.38	79708565.3	81621.57	Tx : 1594172297 Rx : 1594172297 Loss : 0 Loss% : 0.000	Min : 5912 Max : 6017 Avg : 5970
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 5	16	15	94.38	94.38	79708565.4	81621.57	Tx : 1594172297 Rx : 1594172297 Loss : 0 Loss% : 0.000	Min : 5957 Max : 6062 Avg : 6010
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 6	15	16	97.19	97.19	82084168.1	84054.19	Tx : 1641680743 Rx : 1641680743 Loss : 0 Loss% : 0.000	Min : 5917 Max : 6020 Avg : 5973
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 128 / Iter: 6	16	15	97.19	97.19	82084168.1	84054.19	Tx : 1641680743 Rx : 1641680743 Loss : 0 Loss% : 0.000	Min : 5955 Max : 6067 Avg : 6013
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 7	15	16	98.59	98.59	83271800.9	85270.32	Tx : 1665434966 Rx : 1665434966 Loss : 0 Loss% : 0.000	Min : 5910 Max : 6022 Avg : 5977
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 7	16	15	98.59	98.59	83271800.9	85270.32	Tx : 1665434966 Rx : 1665434966 Loss : 0 Loss% : 0.000	Min : 5957 Max : 6067 Avg : 6018
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 8	15	16	99.30	99.30	83865683.6	85878.46	Tx : 1677312078 Rx : 1677312078 Loss : 0 Loss% : 0.000	Min : 5917 Max : 6027 Avg : 5980
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 8	16	15	99.30	99.30	83865683.6	85878.46	Tx : 1677312078 Rx : 1677312078 Loss : 0 Loss% : 0.000	Min : 5957 Max : 6065 Avg : 6022
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 9	15	16	100.00	100.00	84459458.9	86486.49	Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000	Min : 5915 Max : 6085 Avg : 6034
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 9	16	15	100.00	100.00	84459458.9	86486.49	Tx : 1689189189 Rx : 1689189189 Loss : 0 Loss% : 0.000	Min : 5952 Max : 6107 Avg : 6075
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 1	15	16	10.00	10.00	4528985.5	9275.36	Tx : 90579710 Rx : 90579710 Loss : 0 Loss% : 0.000	Min : 5977 Max : 6027 Avg : 5994
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 1	16	15	10.00	10.00	4528985.5	9275.36	Tx : 90579710 Rx : 90579710 Loss : 0 Loss% : 0.000	Min : 6020 Max : 6067 Avg : 6036
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 2	15	16	55.00	55.00	24909411.5	51014.48	Tx : 498188406 Rx : 498188406 Loss : 0 Loss% : 0.000	Min : 5977 Max : 6035 Avg : 5996
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 256 / Iter: 2	16	15	55.00	55.00	24909411.5	51014.48	Tx : 498188406 Rx : 498188406 Loss : 0 Loss% : 0.000	Min : 6017 Max : 6075 Avg : 6038
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 3	15	16	77.50	77.50	35099650.1	71884.08	Tx : 701992754 Rx : 701992754 Loss : 0 Loss% : 0.000	Min : 5980 Max : 6045 Avg : 6001
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 3	16	15	77.50	77.50	35099650.1	71884.08	Tx : 701992754 Rx : 701992754 Loss : 0 Loss% : 0.000	Min : 6020 Max : 6082 Avg : 6043
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 4	15	16	88.75	88.75	40194756.1	82318.86	Tx : 803894928 Rx : 803894928 Loss : 0 Loss% : 0.000	Min : 5987 Max : 6047 Avg : 6008
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 4	16	15	88.75	88.75	40194756.1	82318.86	Tx : 803894928 Rx : 803894928 Loss : 0 Loss% : 0.000	Min : 6027 Max : 6090 Avg : 6050
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 5	15	16	94.38	94.38	42742320.5	87536.27	Tx : 854846014 Rx : 854846014 Loss : 0 Loss% : 0.000	Min : 5992 Max : 6080 Avg : 6045
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 5	16	15	94.38	94.38	42742320.5	87536.27	Tx : 854846014 Rx : 854846014 Loss : 0 Loss% : 0.000	Min : 6042 Max : 6122 Avg : 6087
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 6	15	16	97.19	97.19	44016052.0	90144.87	Tx : 880321558 Rx : 880321558 Loss : 0 Loss% : 0.000	Min : 5992 Max : 6097 Avg : 6062
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 6	16	15	97.19	97.19	44016052.0	90144.87	Tx : 880321558 Rx : 880321558 Loss : 0 Loss% : 0.000	Min : 6040 Max : 6135 Avg : 6103
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 7	15	16	98.59	98.59	44652979.9	91449.30	Tx : 893059330 Rx : 893059330 Loss : 0 Loss% : 0.000	Min : 5992 Max : 6105 Avg : 6071
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 256 / Iter: 7	16	15	98.59	98.59	44652979.9	91449.30	Tx : 893059330 Rx : 893059330 Loss : 0 Loss% : 0.000	Min : 6035 Max : 6150 Avg : 6112
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 8	15	16	99.30	99.30	44971374.5	92101.38	Tx : 899428216 Rx : 899428216 Loss : 0 Loss% : 0.000	Min : 5995 Max : 6115 Avg : 6079
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 8	16	15	99.30	99.30	44971374.5	92101.38	Tx : 899428216 Rx : 899428216 Loss : 0 Loss% : 0.000	Min : 6042 Max : 6157 Avg : 6120
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 9	15	16	100.00	100.00	45289854.8	92753.62	Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000	Min : 5997 Max : 6155 Avg : 6121
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 9	16	15	100.00	100.00	45289854.7	92753.62	Tx : 905797101 Rx : 905797101 Loss : 0 Loss% : 0.000	Min : 6030 Max : 6190 Avg : 6161
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 1	15	16	10.00	10.00	2349624.1	9624.06	Tx : 46992481 Rx : 46992481 Loss : 0 Loss% : 0.000	Min : 5895 Max : 5945 Avg : 5911
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 1	16	15	10.00	10.00	2349624.1	9624.06	Tx : 46992481 Rx : 46992481 Loss : 0 Loss% : 0.000	Min : 5937 Max : 5990 Avg : 5953
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 2	15	16	55.00	55.00	12922929.4	52932.32	Tx : 258458647 Rx : 258458647 Loss : 0 Loss% : 0.000	Min : 5895 Max : 5950 Avg : 5911
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 2	16	15	55.00	55.00	12922929.4	52932.32	Tx : 258458647 Rx : 258458647 Loss : 0 Loss% : 0.000	Min : 5937 Max : 5990 Avg : 5954
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 3	15	16	77.50	77.50	18209585.2	74586.46	Tx : 364191729 Rx : 364191729 Loss : 0 Loss% : 0.000	Min : 5895 Max : 5950 Avg : 5913
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 512 / Iter: 3	16	15	77.50	77.50	18209585.2	74586.46	Tx : 364191729 Rx : 364191729 Loss : 0 Loss% : 0.000	Min : 5937 Max : 5992 Avg : 5955
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 4	15	16	88.75	88.75	20852916.9	85413.55	Tx : 417058271 Rx : 417058271 Loss : 0 Loss% : 0.000	Min : 5895 Max : 5952 Avg : 5916
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 4	16	15	88.75	88.75	20852916.9	85413.55	Tx : 417058271 Rx : 417058271 Loss : 0 Loss% : 0.000	Min : 5937 Max : 5992 Avg : 5959
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 5	15	16	94.38	94.38	22174581.5	90827.09	Tx : 443491541 Rx : 443491541 Loss : 0 Loss% : 0.000	Min : 5897 Max : 5955 Avg : 5917
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 5	16	15	94.38	94.38	22174581.5	90827.09	Tx : 443491541 Rx : 443491541 Loss : 0 Loss% : 0.000	Min : 5940 Max : 5997 Avg : 5960
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 6	15	16	97.19	97.19	22835408.4	93533.83	Tx : 456708177 Rx : 456708177 Loss : 0 Loss% : 0.000	Min : 5905 Max : 5957 Avg : 5924
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 6	16	15	97.19	97.19	22835408.4	93533.83	Tx : 456708177 Rx : 456708177 Loss : 0 Loss% : 0.000	Min : 5945 Max : 6002 Avg : 5966
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 7	15	16	98.59	98.59	23165827.5	94887.23	Tx : 463316494 Rx : 463316494 Loss : 0 Loss% : 0.000	Min : 5907 Max : 5960 Avg : 5929
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 7	16	15	98.59	98.59	23165827.5	94887.23	Tx : 463316494 Rx : 463316494 Loss : 0 Loss% : 0.000	Min : 5947 Max : 6002 Avg : 5970
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 8	15	16	99.30	99.30	23331033.6	95563.91	Tx : 466620653 Rx : 466620653 Loss : 0 Loss% : 0.000	Min : 5905 Max : 5965 Avg : 5927
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 512 / Iter: 8	16	15	99.30	99.30	23331033.6	95563.91	Tx : 466620653 Rx : 466620653 Loss : 0 Loss% : 0.000	Min : 5950 Max : 6005 Avg : 5972
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 9	15	16	100.00	100.00	23496240.5	96240.60	Tx : 469924812 Rx : 469924812 Loss : 0 Loss% : 0.000	Min : 5902 Max : 6027 Avg : 5976
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 9	16	15	100.00	100.00	23496240.5	96240.60	Tx : 469924812 Rx : 469924812 Loss : 0 Loss% : 0.000	Min : 5957 Max : 6047 Avg : 6020
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 1	15	16	10.00	10.00	1197318.0	9808.43	Tx : 23946360 Rx : 23946360 Loss : 0 Loss% : 0.000	Min : 5862 Max : 5912 Avg : 5879
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 1	16	15	10.00	10.00	1197318.0	9808.43	Tx : 23946360 Rx : 23946360 Loss : 0 Loss% : 0.000	Min : 5905 Max : 5955 Avg : 5922
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 2	15	16	55.00	55.00	6585249.7	53946.37	Tx : 131704981 Rx : 131704981 Loss : 0 Loss% : 0.000	Min : 5862 Max : 5925 Avg : 5886
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 2	16	15	55.00	55.00	6585249.7	53946.37	Tx : 131704981 Rx : 131704981 Loss : 0 Loss% : 0.000	Min : 5905 Max : 5962 Avg : 5927
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 3	15	16	77.50	77.50	9279215.2	76015.33	Tx : 185584291 Rx : 185584291 Loss : 0 Loss% : 0.000	Min : 5865 Max : 5917 Avg : 5883
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 3	16	15	77.50	77.50	9279215.2	76015.33	Tx : 185584291 Rx : 185584291 Loss : 0 Loss% : 0.000	Min : 5905 Max : 5965 Avg : 5926
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 4	15	16	88.75	88.75	10626198.6	87049.82	Tx : 212523946 Rx : 212523946 Loss : 0 Loss% : 0.000	Min : 5865 Max : 5927 Avg : 5884
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1024 / Iter: 4	16	15	88.75	88.75	10626198.6	87049.82	Tx : 212523946 Rx : 212523946 Loss : 0 Loss% : 0.000	Min : 5907 Max : 5967 Avg : 5929
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 5	15	16	94.38	94.38	11299689.4	92567.06	Tx : 225993774 Rx : 225993774 Loss : 0 Loss% : 0.000	Min : 5865 Max : 5922 Avg : 5886
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 5	16	15	94.38	94.38	11299689.4	92567.06	Tx : 225993774 Rx : 225993774 Loss : 0 Loss% : 0.000	Min : 5910 Max : 5967 Avg : 5931
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 6	15	16	97.19	97.19	11636432.4	95325.65	Tx : 232728688 Rx : 232728688 Loss : 0 Loss% : 0.000	Min : 5867 Max : 5922 Avg : 5887
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 6	16	15	97.19	97.19	11636432.4	95325.65	Tx : 232728688 Rx : 232728688 Loss : 0 Loss% : 0.000	Min : 5910 Max : 5967 Avg : 5930
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 7	15	16	98.59	98.59	11804807.5	96704.98	Tx : 236096145 Rx : 236096145 Loss : 0 Loss% : 0.000	Min : 5867 Max : 5925 Avg : 5890
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 7	16	15	98.59	98.59	11804807.5	96704.98	Tx : 236096145 Rx : 236096145 Loss : 0 Loss% : 0.000	Min : 5912 Max : 5970 Avg : 5933
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 8	15	16	99.30	99.30	11888993.9	97394.64	Tx : 237779873 Rx : 237779873 Loss : 0 Loss% : 0.000	Min : 5872 Max : 5930 Avg : 5895
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 8	16	15	99.30	99.30	11888994.0	97394.64	Tx : 237779873 Rx : 237779873 Loss : 0 Loss% : 0.000	Min : 5917 Max : 5972 Avg : 5939
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 9	15	16	100.00	100.00	11973180.0	98084.29	Tx : 239463602 Rx : 239463602 Loss : 0 Loss% : 0.000	Min : 5877 Max : 5972 Avg : 5939
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1024 / Iter: 9	16	15	100.00	100.00	11973180.0	98084.29	Tx : 239463602	Min : 5920
							Rx : 239463602	Max : 6020
							Loss : 0	Avg : 5986
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 1	15	16	10.00	10.00	961538.5	9846.15	Tx : 19230769	Min : 5897
							Rx : 19230769	Max : 5947
							Loss : 0	Avg : 5915
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 1	16	15	10.00	10.00	961538.5	9846.15	Tx : 19230769	Min : 5940
							Rx : 19230769	Max : 5992
							Loss : 0	Avg : 5956
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 2	15	16	55.00	55.00	5288461.8	54153.85	Tx : 105769231	Min : 5900
							Rx : 105769231	Max : 5955
							Loss : 0	Avg : 5921
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 2	16	15	55.00	55.00	5288461.8	54153.85	Tx : 105769231	Min : 5940
							Rx : 105769231	Max : 6005
							Loss : 0	Avg : 5961
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 3	15	16	77.50	77.50	7451922.7	76307.69	Tx : 149038462	Min : 5897
							Rx : 149038462	Max : 5955
							Loss : 0	Avg : 5918
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 3	16	15	77.50	77.50	7451922.7	76307.69	Tx : 149038462	Min : 5940
							Rx : 149038462	Max : 6010
							Loss : 0	Avg : 5960
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 4	15	16	88.75	88.75	8533654.8	87384.63	Tx : 170673077	Min : 5900
							Rx : 170673077	Max : 5962
							Loss : 0	Avg : 5923
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 4	16	15	88.75	88.75	8533654.8	87384.63	Tx : 170673077	Min : 5942
							Rx : 170673077	Max : 6005
							Loss : 0	Avg : 5964
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 1280 / Iter: 5	15	16	94.38	94.38	9074519.5	92923.08	Tx : 181490385	Min : 5900
							Rx : 181490385	Max : 5960
							Loss : 0	Avg : 5921
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	

Trial: 1 / FS: 1280 / Iter: 5	16	15	94.38	94.38	9074519.5	92923.08	Tx : 181490385 Rx : 181490385 Loss : 0 Loss% : 0.000	Min : 5942 Max : 6007 Avg : 5966
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 6	15	16	97.19	97.19	9344951.7	95692.31	Tx : 186899038 Rx : 186899038 Loss : 0 Loss% : 0.000	Min : 5905 Max : 5962 Avg : 5927
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 6	16	15	97.19	97.19	9344951.7	95692.31	Tx : 186899038 Rx : 186899038 Loss : 0 Loss% : 0.000	Min : 5945 Max : 6005 Avg : 5968
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 7	15	16	98.59	98.59	9480168.3	97076.92	Tx : 189603365 Rx : 189603365 Loss : 0 Loss% : 0.000	Min : 5905 Max : 5967 Avg : 5929
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 7	16	15	98.59	98.59	9480168.3	97076.92	Tx : 189603365 Rx : 189603365 Loss : 0 Loss% : 0.000	Min : 5947 Max : 6015 Avg : 5974
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 8	15	16	99.30	99.30	9547774.9	97769.22	Tx : 190955529 Rx : 190955529 Loss : 0 Loss% : 0.000	Min : 5907 Max : 5977 Avg : 5935
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 8	16	15	99.30	99.30	9547774.9	97769.22	Tx : 190955529 Rx : 190955529 Loss : 0 Loss% : 0.000	Min : 5952 Max : 6012 Avg : 5978
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 9	15	16	100.00	100.00	9615384.6	98461.54	Tx : 192307692 Rx : 192307692 Loss : 0 Loss% : 0.000	Min : 5917 Max : 6020 Avg : 5987
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 9	16	15	100.00	100.00	9615384.6	98461.54	Tx : 192307692 Rx : 192307692 Loss : 0 Loss% : 0.000	Min : 5967 Max : 6065 Avg : 6029
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 1	15	16	10.00	10.00	812743.8	9869.96	Tx : 16254876 Rx : 16254876 Loss : 0 Loss% : 0.000	Min : 5822 Max : 5885 Avg : 5848
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1518 / Iter: 1	16	15	10.00	10.00	812743.8	9869.96	Tx : 16254876	Min : 5862
							Rx : 16254876	Max : 5920
							Loss : 0	Avg : 5885
							Loss% : 0.000	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 2	15	16	55.00	55.00	4470090.8	54284.78	Tx : 89401821	Min : 5820
							Rx : 89401821	Max : 5882
							Loss : 0	Avg : 5843
							Loss% : 0.000	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 2	16	15	55.00	55.00	4470090.8	54284.78	Tx : 89401821	Min : 5862
							Rx : 89401821	Max : 5925
							Loss : 0	Avg : 5883
							Loss% : 0.000	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 3	15	16	77.50	77.50	6298764.7	76492.20	Tx : 125975293	Min : 5820
							Rx : 125975293	Max : 5880
							Loss : 0	Avg : 5842
							Loss% : 0.000	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 3	16	15	77.50	77.50	6298764.7	76492.20	Tx : 125975293	Min : 5862
							Rx : 125975293	Max : 5927
							Loss : 0	Avg : 5885
							Loss% : 0.000	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 4	15	16	88.75	88.75	7213102.4	87595.92	Tx : 143720314	Min : 5820
							Rx : 143720254	Max : 5880
							Loss : 60	Avg : 5843
							Loss% : 0.000	
N8550-24CD8D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 4	16	15	88.75	88.75	7213102.4	87595.92	Tx : 143720314	Min : 5862
							Rx : 143720253	Max : 5922
							Loss : 61	Avg : 5885
							Loss% : 0.000	
N8550-24CD8D-Endpoint Set-2 - Flow Group 0001								

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730