

A solid red circle graphic.

FMU-O162931MD Data Sheet

Contents

Product Overview	3
Features and Benefits	4
Front Panel and Port Description	4
Technical Specification	5
ITU Channel Guiding	6
Layout and Dimension	6
Ordering Information	7

Product Overview

The 16CH Mux Demux, based on TFF (Thin Film Filter), is a passive O-band DWDM device featuring high density, low loss, and long-haul transmission suitability. It is integrated with a monitor port. The 1% monitor port allows easy troubleshooting without downtime. In addition, this unit can be used as either a multiplexer or demultiplexer (Mux/Demux). It combines 16-channel of DWDM wavelengths into a composite signal and separates the combined DWDM signal into 16-channel individual wavelengths over a pair of single-mode optical fiber.

It is suitable for short-distance and long-distance transmission, such as 5G pre-transmission, data center interconnects (DCI), metro access, and point-to-point access networks, with the advantage of low-cost, simplified network architecture, meeting FS customers' short-reach 100G transmission requirements.



Features and Benefits

- Multiplexing of up to 16 Channels on Fiber Pair to Maximize the Using of Existing Fiber
- Compatible with ITU Grid and Interconnects with Optical Networking Products
- Monitor Port Taps off 1% of the Signal to Monitor the Channel Power Levels
- Passive Transparent Multiplexing at Any Rate, Any Service, Including Ethernet, SDH/SONET, Fiber Channel, FTTx, and CATV
- Suitable for Short-distance Transmission
- The Solution can be [Customized](#) per Customer Application Requirements

Front Panel and Port Description



LINE

Line interface for common signal

MON

1% Monitoring for easy troubleshooting

Technical Specification

Parameter	Value
ITU Channel	16 Channels
Wavelength	228.4, 228.6, 228.8, 229.0, 229.2, 229.4, 229.6, 229.8, 230.0, 230.2, 230.4, 230.6, 230.8, 231.0, 231.2, 231.4THz
Technology	TFF (The Film Filter)
Channel Passband	ITU±0.2nm
Insertion Loss	≤ 5.4dB, 5.0dB Typical
Insertion Loss (+1% Mon)	≤ +0.3dB
Channel Spacing	200GHz
-1dB Channel Bandwidth	≥1nm
Passband Ripple	≤0.5dB
Adjacent Channel Isolation	≥30dB
Non-adjacent Channel Isolation	≥40dB
Return Loss	≥45dB
Directivity	≥45dB
Polarization Dependent Loss	≤0.3dB
Polarization Mode Dispersion	≤0.1ps
Operating Temperature	-40 to 85°C (-40 to 185°F)
Storage Temperature	-40 to 85°C (-40 to 185°F)


Notes: 1.Specified with connectors and adapters.

ITU Channel Guiding

No.	O1	O2	O3	O4	O5	O6	O7	O8
Wavelength (nm)	1312.58	1311.43	1310.28	1309.14	1308.00	1306.85	1305.72	1304.58
Frequency Repetition (THz)	228.40	228.60	228.80	229.00	229.20	229.40	229.60	229.80

No.	O9	O10	O11	O12	O13	O14	O15	O16
Wavelength (nm)	1303.45	1302.31	1301.18	1300.05	1298.83	1297.80	1296.68	1295.56
Frequency Repetition (THz)	230.00	230.20	230.40	230.60	230.80	231.00	231.20	231.40

Layout and Dimension



Height: 1.73" (44mm)
Width: 19" (482.6mm)
Depth: 10.28" (261.2mm)

Ordering Information

Mux Demux & OADM

FMU Series
CWDM Mux
Demux

FMU-MC045561ES	4 Channels CWDM Mux or Demux, 1550-1610nm, with Expansion Port, 1.5dB Typical IL, LC/UPC, Single Fiber, FMU Plug-in Module#214979
FMU-MC163161EMS	16 Channels CWDM Mux or Demux, 1310-1610nm, with Monitor and Expansion Port, 4.5dB Typical IL, LC/UPC, Single Fiber, FMU Plug-in Module#214981
FMU-MC082759EMA	8 Channels CWDM Mux Demux, 1270-1590nm, with Monitor and Expansion Port, 4.5dB Typical IL, LC/UPC, Single Fiber, Side A, FMU Plug-in Module#214983
FMU-MC082961EMB	8 Channels CWDM Mux Demux, 1290-1610nm, with Monitor and Expansion Port, 4.5dB Typical IL, LC/UPC, Single Fiber, Side B, FMU Plug-in Module#214985
FMU-C182761M	18 Channels CWDM Mux Demux, 1270-1610nm, with Monitor Port, 5.0dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#33489
FMU-MC082745	8 Channels CWDM Mux Demux, 1270-1450nm (Skip 1390, 1410nm), 2.5dB Typical IL, LC/UPC, Dual Fiber, FMU Plug-in Module#42937
FMU-MC042733	4 Channels CWDM Mux Demux, 1270-1330nm, 1.0dB Typical IL, LC/UPC, Dual Fiber, FMU Plug-in Module#42972
FMU-MC09B	9 Channels CWDM Mux Demux, 1290-1610nm, 2.4dB Typical IL, LC/UPC, Single Fiber, Side-B, FMU Plug-in Module#43699
FMU-MC09A	9 Channels CWDM Mux Demux, 1270-1590nm, 2.4dB Typical IL, LC/UPC, Single Fiber, Side-A, FMU Plug-in Module#43711

FMU Series
DWDM Mux
Demux

FMU-MC084761EM	8 Channels CWDM Mux Demux, 1470-1610nm, with Monitor and Expansion Port, 2.0dB Typical IL, LC/UPC, Dual Fiber, FMU Plug-in Module#78163
FMU-C182761M	18 Channels CWDM Mux Demux, 1270-1610nm, with Monitor Port, 2.2dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#123533
FMU-D60OCMW5	60 Odd Channels DWDM Mux Demux, Super C-band 100GHz 1524.50-1571.65nm, with Monitor Port, 6.0dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#166000
FMU-D60ECMW5	60 Even Channels DWDM Mux Demux, Super C-band 100GHz 1524.89-1572.06nm, with Monitor Port, 6.0dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#166001
FMU-D40ODMW5	40 Odd Channels Super C-band 150GHz 190.7875-196.6375THz, with Monitor Port, 5.5dB Typical IL, LC/UPC, Dual Fiber DWDM Mux Demux, 1U Rack Mount#166002
FMU-D40EDMW5	40 Even Channels Super C-band 150GHz 190.7125-196.5625THz, with Monitor Port, 5.5dB Typical IL, LC/UPC, Dual Fiber DWDM Mux Demux, 1U Rack Mount#166003
FMU-D64BMW5	64 Channels DWDM Mux Demux, Super C-band 75GHz 1528.87-1566.62nm, with Monitor Port, 5.8dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#166004
FMU-MD042023EMD	4 Channels DWDM Mux Demux, 100GHz C20-C23, with Monitor and Expansion Port, 1.6dB Typical IL, LC/UPC, Dual Fiber, FMU Plug-in Module#214975

Mux Demux & OADM		
FMU Series DWDM Mux Demux	FMU-D402160M3	40 Channels DWDM Mux Demux, 100GHz C21-C60, with 1310nm and Monitor Port, 3.5dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#35887
	FMU-D162136EM3	16 Channels DWDM Mux Demux, 100GHz C21-C36, with Monitor, Expansion and 1310nm Port, 4.4dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#72430
	FMU-D162136A	16 Channels DWDM Mux Demux, 100GHz C21-C36, 4.0dB Typical IL, LC/UPC, Single Fiber, Side-A, 1U Rack Mount#78535
	FMU-D164560B	16 Channels DWDM Mux Demux, 100GHz C45-C60, 4.0dB Typical IL, LC/UPC, Single Fiber, Side-B, 1U Rack Mount#78536
	FMU-FD402160M3	40 Channels DWDM Mux Demux, 100GHz C21-C60, with 1310nm Port and Monitor Port, 4.5dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#84492
	FMU-MD085360E	8 Channels DWDM Mux Demux, C53-C60, with Expansion Port, 2.8dB Typical IL, LC/UPC, Dual Fiber, FMU Plug-in Module, CWDM/DWDM Hybrid Solution#30568
	FMU-D402160M	40 Channels DWDM Mux Demux, 100GHz C21-C60, with Monitor Port, 3.0dB Typical IL, LC/UPC, Dual Fiber, 1U Rack Mount#33485
	FMU-MD08EB	8 Channels DWDM Mux Demux, 100GHz C22-C36, with Expansion Port, 4.2dB Typical IL, LC/UPC, Single Fiber, Side-B, FMU Plug-in Module#50116
FMU Series OWDM Mux Demux	FMU-MD08EA	8 Channels DWDM Mux Demux, 100GHz C21-C35, with Expansion Port, 4.2dB Typical IL, LC/UPC, Single Fiber, Side-A, FMU Plug-in Module#50117
	FMU-MD085360EM3	8 Channels DWDM Mux Demux, 100GHz C53-C60, with Monitor, Expansion and 1310nm Port, 3.0dB Typical IL, LC/UPC, Dual Fiber, FMU Plug-in Module, CWDM/DWDM Hybrid Solution#72433
	FMU-O162931MD	16 Channels O-band DWDM Mux Demux, 228.4-231.4THz, with Monitor Port, 5.0dB Typical IL, LC/UPC, Dual Fiber, FMU 1U Rack Mount#374863
Custom Mux Demux	MUX-DWDM	Customized Dual and Single Fiber DWDM Mux Demux#322911
	MUX-CWDM	Customized Dual and Single Fiber CWDM Mux Demux#70410
	MUX-CCWDM	Customized Dual and Single Fiber Compact CWDM Mux Demux#73961
OADM	DOADM-EAW	Customized Dual and Single Fiber DWDM OADM, East and West#70427
	DOADM-EOW	Customized Dual and Single Fiber DWDM OADM, East or West#73795
	COADM-EAW	Customized Dual and Single Fiber CWDM OADM, East and West#70425
	COADM-EOW	Customized Dual and Single Fiber CWDM OADM, East or West#73794
Chassis	FMU-1UFMX-N	FMU 2-Slot 1U 19" Rack Chassis Unloaded, Holds up to 2 Units FMU Plug-in Module#30408

TRANSPONDERS & MUXPONDERS

10G	FMT4DL-OEO25GSFP28	FMT4DL-OEO25GSFP28, 4 Channels 25G WDM Transponder (Converter) for FMT Managed Chassis, 8 SFP28/SFP+ Slots#92056
	FMT4DL-OEO10GSFP	FMT4DL-OEO10GSFP, 4 Channels WDM Transponder (Converter) for FMT Managed Chassis, 8 SFP/SFP+ Slots#30515
	FMT04-CH1U	FMT04-CH1U, 4 Slots 1U Managed Chassis Unloaded Platform, Redundant AC PSUs, Support SNMP V1 Network Management#39214
Chassis	FMT-CH	FMT-CH, Customized 4/8/16 Slots 1U/2U/4U Managed Chassis Unloaded Platform, Redundant AC/DC PSUs, Support SNMP Network Management#70413

WDM TRANSCEIVERS

100G/200G CFP2	CFP2-DCO-200G-M	C14 1566.31nm CFP2-DCO 100G/200G DWDM C-band Tunable 96Chs ITU CH13-CH60 50GHz 80km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#120128
25G SFP28	DW-SFP25G10-17	Cisco C17 DWDM-SFP25G-63.86 Compatible SFP28 25G DWDM 1563.86nm 100GHz 10km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#87000
	CW-SFP25G30-27	Cisco CWDM-SFP25G-1270-30 Compatible SFP28 25G CWDM 1270nm 30km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#100112
	CW-SFP25G10-27	Cisco CWDM-SFP25G-1270-10 Compatible SFP28 25G CWDM 1270nm 10km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#76003
10G SFP+	LW-SFP25G40-86	Cisco LWDM-SFP25G-86.66 Compatible SFP28 25G LWDM 1286.66nm 40km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#93786
	DW-SFP10G80-21-I	Cisco C21 DWDM-SFP10G-60.61-I Compatible SFP+ 10G DWDM 1560.61nm 100GHz 80km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission (Industrial)#113562
	DW-SFP10G40-21-I	Cisco C21 DWDM-SFP10G-60.61-I Compatible SFP+ 10G DWDM 1560.61nm 100GHz 40km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission (Industrial)#113511
1GSFP	CW-SFP10G80-47	Cisco CWDM-SFP10G-1470 Compatible SFP+ 10G CWDM 1470nm 80km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#19367
	CW-SFP10G40-27-I	Cisco CWDM-SFP10G-1270-I Compatible SFP+ 10G CWDM 1270nm 40km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission (Industrial)#112392
	DWDM-SFP1G-EZX	Cisco C17 DWDM-SFP-6386 Compatible SFP 1000BASE-DWDM 1563.86nm 100GHz 100km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#54150
	DWDM-SFP1G-ZX	Cisco C17 DWDM-SFP-6386-80 Compatible SFP 1000BASE-DWDM 1563.86nm 100GHz 80km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#47697
	CWDM-SFP1G-ZX	Cisco CWDM-SFP-1270 Compatible SFP 1000BASE-CWDM 1270nm 80km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#33234
	DWDM-SFP1G-ZX	Cisco C17 DWDM-SFP-6386-80 Compatible SFP 1000BASE-DWDM 1563.86nm 100GHz 80km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#47697
	CWDM-SFP1G-ZX	Cisco CWDM-SFP-1270 Compatible SFP 1000BASE-CWDM 1270nm 80km DOM Duplex LC/UPC SMF Optical Transceiver Module for Transmission#33234

*Standard products are listed above. Customized specifications are available upon request.



Delaware, United States

Address: Delaware: 380 Centerpoint Blvd, New Castle, DE 19720, United States
Email: US@fs.com
Tel: +1 (888) 468-9910

Germany

Address: Röntgenstraße 18, 85757 Karlsfeld, Germany
Email: DE@fs.com
Tel: +49 (0) 8131 377 3008

Australia

Address: 57-59 Edison Rd, Dandenong South, VIC 3175, Australia
Email: AU@fs.com
Tel: +61 3 5909 9990

Japan

Address: JS Progress Building 5F, 4-1-23, Heiwajima, Ota Ku, Tokyo, 143-0006, Japan
Email: JP@fs.com
Tel: +81-3-6897-9438

California, United States

Address: California: 15241 Don Julian Rd, City of Industry, CA 91745, United States
Email: US@fs.com
Tel: +1 (888) 468-9910

United Kingdom

Address: Unit 8, Urban Express Park, Union Way, Aston, Birmingham B6 7FH, United Kingdom
Email: UK@fs.com
Tel: +44 (0) 121 726 4775

Singapore

Address: 7002 ANG MO KIO AVENUE 5 #05-02 Singapore 569914
Email: SG@fs.com
Tel: +65 31381992



FS has several offices around the world. Addresses, phone numbers are listed on the FS Website at https://www.fs.com/contact_us.html. FS and FS logo are trademarks or registered trademarks of FS in the U.S. and other countries.