

IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 09/07/2026 12:17:55

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Port Map	4
4.	Aggregate Graphs	5
5.	IterationCharts	13
6.	Aggregated Results	19
7.	Aggregated Results Per Iteration	20
8.	Per Flow Results	25
9.	Iteration Data	27
10.	Theoretical Max Rates	42

RFC2544 - Throughput/Latency - Info

Test Information

Product Information

Product Label :	IES5200W-8U2F2SD
Product Version :	v1.2412b251204
Serial Number :	110SQ25080002N00001
Comments :	

Test Settings

Date Executed :	09/07/2026
Time Executed :	12:17:55
User Name :	FS.COM
Number of Trials Executed :	1
Stream Duration (sec) :	20
Calculate Lantency :	True
Lantency Type :	Store and Forward


Output Parameters

Number of Trials Passed :	N/A
Test Duration (sec) :	00:35:54


RFC2544 - Throughput/Latency - Port Map Information

Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.28.162.200;07;06	10000	10.28.162.200;07;07	10000
	10.28.162.200;07;07	10000	10.28.162.200;07;06	10000


RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Per Flow Graph




RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Per Flow Graph




RFC2544 - Throughput/Latency - Iteration Graph







Aggregated Frame Loss for Trial 1 and Framesize 256




Aggregated Frame Loss for Trial 1 and Framesize 512




Aggregated Frame Loss for Trial 1 and Framesize 1024




Aggregated Frame Loss for Trial 1 and Framesize 1280





Aggregated Frame Loss for Trial 1 and Framesize 1518
6
4
2
0
-2
-4
-6
(%)
0.00
0.00
0.00
0.00
0.00
0.00
0.00
0.00
0.00
1
2
3
4
5
6
7
8
9
Iteration

RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput			Throughput (frames)			Agg Latency (ns)		
	AggTx Rate %	Agg Rx Rate											
		%	FPS	Mbps									
Trial: 1 / FS: 64 / Iter: 9	100.00	100	29761904.7	15238.095	Tx Rate Mbps :	Tx :	595238096.000	Min :	2017				
					Rx Rate Mbps :	Rx :	595238096.000	Max :	2195				
						Loss :	0	Average :	2072.000				
					Lost Bits % :	Loss% :	0.00						
Trial: 1 / FS: 128 / Iter: 8	88.05	88	14872825.7	15229.774	Tx Rate Mbps :	Tx :	297455658.000	Min :	1952				
					Rx Rate Mbps :	Rx :	297455658.000	Max :	2110				
						Loss :	0	Average :	2021.500				
					Lost Bits % :	Loss% :	0.00						
Trial: 1 / FS: 256 / Iter: 9	100.00	100	9057971.0	18550.725	Tx Rate Mbps :	Tx :	181159420.000	Min :	2015				
					Rx Rate Mbps :	Rx :	181159420.000	Max :	2170				
						Loss :	0	Average :	2126.000				
					Lost Bits % :	Loss% :	0.00						
Trial: 1 / FS: 512 / Iter: 9	100.00	100	4699248.1	19248.120	Tx Rate Mbps :	Tx :	93984962.000	Min :	2117				
					Rx Rate Mbps :	Rx :	93984962.000	Max :	2230				
						Loss :	0	Average :	2190.500				
					Lost Bits % :	Loss% :	0.00						
Trial: 1 / FS: 1024 / Iter: 9	100.00	100	2394636.0	19616.858	Tx Rate Mbps :	Tx :	47892720.000	Min :	2020				
					Rx Rate Mbps :	Rx :	47892720.000	Max :	2165				
						Loss :	0	Average :	2124.500				
					Lost Bits % :	Loss% :	0.00						
Trial: 1 / FS: 1280 / Iter: 9	100.00	100	1923076.9	19692.308	Tx Rate Mbps :	Tx :	38461538.000	Min :	2087				
					Rx Rate Mbps :	Rx :	38461538.000	Max :	2180				
						Loss :	0	Average :	2138.500				
					Lost Bits % :	Loss% :	0.00						
Trial: 1 / FS: 1518 / Iter: 9	100.00	100	1625487.6	19739.922	Tx Rate Mbps :	Tx :	32509752.000	Min :	2045				
					Rx Rate Mbps :	Rx :	32509752.000	Max :	2172				
						Loss :	0	Average :	2125.500				
					Lost Bits % :	Loss% :	0.00						

RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	Agg L2 Throughput				Agg L1 Throughput		Throughput (frames)		Agg Latency		
	AggTx Rate %	Agg Rx Rate			Tx Rate Mbps	Rx Rate Mbps			Min (ns)	Max (ns)	Average (ns)
		%	FPS	Mbps							
Trial: 1 / FS: 64 / Iter: 1	10	10	2976190.5	1523.810			Tx : 59523810.000 Rx : 59523810.000 Loss : 0 Loss% : 0.00		1940	2107	2003.500
Trial: 1 / FS: 64 / Iter: 2	55	55	16369123.7	8380.991			Tx : 327380952.000 Rx : 327380952.000 Loss : 0 Loss% : 0.00		1942	2107	2006.000
Trial: 1 / FS: 64 / Iter: 3	78	78	23065556.6	11809.565			Tx : 461309524.000 Rx : 461309524.000 Loss : 0 Loss% : 0.00		1947	2107	2016.000
Trial: 1 / FS: 64 / Iter: 4	89	89	26413809.5	13523.870			Tx : 528273810.000 Rx : 528273810.000 Loss : 0 Loss% : 0.00		1957	2107	2026.000
Trial: 1 / FS: 64 / Iter: 5	94	94	28088038.4	14381.076			Tx : 561755952.000 Rx : 561755952.000 Loss : 0 Loss% : 0.00		1960	2110	2032.000
Trial: 1 / FS: 64 / Iter: 6	97	97	28924919.5	14809.559			Tx : 578497024.000 Rx : 578497024.000 Loss : 0 Loss% : 0.00		1965	2112	2035.500
Trial: 1 / FS: 64 / Iter: 7	99	99	29343664.7	15023.956			Tx : 586867560.000 Rx : 586867560.000 Loss : 0 Loss% : 0.00		1972	2112	2040.000
Trial: 1 / FS: 64 / Iter: 8	99	99	29552669.5	15130.967			Tx : 591052828.000 Rx : 591052828.000 Loss : 0 Loss% : 0.00		1980	2115	2045.000
Trial: 1 / FS: 64 / Iter: 9	100	100	29761904.7	15238.095			Tx : 595238096.000 Rx : 595238096.000 Loss : 0 Loss% : 0.00		2017	2195	2072.000
Trial: 1 / FS: 128 / Iter: 1	10	10	1689189.2	1729.730			Tx : 33783784.000 Rx : 33783784.000 Loss : 0 Loss% : 0.00		1942	2107	2006.500
Trial: 1 / FS: 128 / Iter: 2	55	55	9290543.6	9513.517			Tx : 185810810.000 Rx : 185810810.000 Loss : 0 Loss% : 0.00		1940	2110	2006.500
Trial: 1 / FS: 128 / Iter: 3	78	78	13091281.0	13405.472			Tx : 261824324.000 Rx : 261824324.000 Loss : 0 Loss% : 0.00		1952	2110	2014.000
Trial: 1 / FS: 128 / Iter: 4	89	89	14991625.7	15351.425			Tx : 299831082.000 Rx : 120553372.000 Loss : 179277710 Loss% : 59.79		1957	2110	2023.000

Trial: 1 / FS: 128 / Iter: 5	83	83	14041400.2	14378.394	Tx : Rx : Loss : Loss% :	280827702.000 280827702.000 0 0.00	1952	2110	2017.500
Trial: 1 / FS: 128 / Iter: 6	86	86	14516504.0	14864.900	Tx : Rx : Loss : Loss% :	290329392.000 290329392.000 0 0.00	1952	2110	2019.500
Trial: 1 / FS: 128 / Iter: 7	87	87	14754022.7	15108.119	Tx : Rx : Loss : Loss% :	295080236.000 295080236.000 0 0.00	1952	2110	2021.000
Trial: 1 / FS: 128 / Iter: 8	88	88	14872825.7	15229.774	Tx : Rx : Loss : Loss% :	297455658.000 297455658.000 0 0.00	1952	2110	2021.500
Trial: 1 / FS: 256 / Iter: 1	10	10	905797.1	1855.072	Tx : Rx : Loss : Loss% :	18115942.000 18115942.000 0 0.00	1997	2162	2062.500
Trial: 1 / FS: 256 / Iter: 2	55	55	4981892.0	10202.915	Tx : Rx : Loss : Loss% :	99637682.000 99637682.000 0 0.00	1997	2165	2062.500
Trial: 1 / FS: 256 / Iter: 3	78	78	7019930.0	14376.817	Tx : Rx : Loss : Loss% :	140398550.000 140398550.000 0 0.00	1997	2165	2064.500
Trial: 1 / FS: 256 / Iter: 4	89	89	8038963.9	16463.798	Tx : Rx : Loss : Loss% :	160778986.000 160778986.000 0 0.00	2020	2165	2073.000
Trial: 1 / FS: 256 / Iter: 5	94	94	8548464.1	17507.255	Tx : Rx : Loss : Loss% :	170969202.000 170969202.000 0 0.00	2032	2165	2083.000
Trial: 1 / FS: 256 / Iter: 6	97	97	8803240.7	18029.037	Tx : Rx : Loss : Loss% :	176064312.000 176064312.000 0 0.00	2017	2167	2093.000
Trial: 1 / FS: 256 / Iter: 7	99	99	8930596.0	18289.861	Tx : Rx : Loss : Loss% :	178611866.000 178611866.000 0 0.00	2050	2167	2101.000
Trial: 1 / FS: 256 / Iter: 8	99	99	8994290.7	18420.307	Tx : Rx : Loss : Loss% :	179885644.000 179885644.000 0 0.00	2045	2170	2107.000
Trial: 1 / FS: 256 / Iter: 9	100	100	9057971.0	18550.725	Tx : Rx : Loss : Loss% :	181159420.000 181159420.000 0 0.00	2015	2170	2126.000
Trial: 1 / FS: 512 / Iter: 1	10	10	469924.8	1924.812	Tx : Rx : Loss : Loss% :	9398496.000 9398496.000 0 0.00	2062	2230	2130.000
Trial: 1 / FS: 512 / Iter: 2	55	55	2584587.2	10586.469	Tx : Rx : Loss : Loss% :	51691730.000 51691730.000 0 0.00	2062	2227	2130.000

Trial: 1 / FS: 512 / Iter: 3	78	78	3641919.6	14917.303	Tx : Rx : Loss : Loss% :	72838346.000 72838346.000 0 0.00	2062	2230	2130.000
Trial: 1 / FS: 512 / Iter: 4	89	89	4170583.4	17082.709	Tx : Rx : Loss : Loss% :	83411654.000 83411654.000 0 0.00	2062	2230	2133.000
Trial: 1 / FS: 512 / Iter: 5	94	94	4434920.1	18165.433	Tx : Rx : Loss : Loss% :	88698308.000 88698308.000 0 0.00	2080	2230	2141.500
Trial: 1 / FS: 512 / Iter: 6	97	97	4567081.7	18706.767	Tx : Rx : Loss : Loss% :	91341636.000 91341636.000 0 0.00	2092	2230	2148.000
Trial: 1 / FS: 512 / Iter: 7	99	99	4633165.5	18977.446	Tx : Rx : Loss : Loss% :	92663298.000 92663298.000 0 0.00	2102	2230	2155.000
Trial: 1 / FS: 512 / Iter: 8	99	99	4666211.0	19112.800	Tx : Rx : Loss : Loss% :	93324130.000 93324130.000 0 0.00	2112	2232	2161.500
Trial: 1 / FS: 512 / Iter: 9	100	100	4699248.1	19248.120	Tx : Rx : Loss : Loss% :	93984962.000 93984962.000 0 0.00	2117	2230	2190.500
Trial: 1 / FS: 1024 / Iter: 1	10	10	239463.6	1961.686	Tx : Rx : Loss : Loss% :	4789272.000 4789272.000 0 0.00	1997	2165	2064.000
Trial: 1 / FS: 1024 / Iter: 2	55	55	1317049.9	10789.273	Tx : Rx : Loss : Loss% :	26340996.000 26340996.000 0 0.00	2000	2167	2063.500
Trial: 1 / FS: 1024 / Iter: 3	78	78	1855843.0	15203.066	Tx : Rx : Loss : Loss% :	37116858.000 37116858.000 0 0.00	1997	2165	2064.000
Trial: 1 / FS: 1024 / Iter: 4	89	89	2125239.7	17409.964	Tx : Rx : Loss : Loss% :	42504790.000 42504790.000 0 0.00	1997	2165	2064.000
Trial: 1 / FS: 1024 / Iter: 5	94	94	2259938.9	18513.419	Tx : Rx : Loss : Loss% :	45198754.000 45198754.000 0 0.00	1997	2165	2065.500
Trial: 1 / FS: 1024 / Iter: 6	97	97	2327287.5	19065.139	Tx : Rx : Loss : Loss% :	46545738.000 46545738.000 0 0.00	2010	2165	2074.500
Trial: 1 / FS: 1024 / Iter: 7	99	99	2360961.5	19340.997	Tx : Rx : Loss : Loss% :	47219228.000 47219228.000 0 0.00	2037	2165	2086.500
Trial: 1 / FS: 1024 / Iter: 8	99	99	2377798.8	19478.928	Tx : Rx : Loss : Loss% :	47555974.000 47555974.000 0 0.00	2042	2165	2095.500

Trial: 1 / FS: 1024 / Iter: 9	100	100	2394636.0	19616.858	Tx : Rx : Loss : Loss% :	47892720.000 47892720.000 0 0.00	2020	2165	2124.500
Trial: 1 / FS: 1280 / Iter: 1	10	10	192307.7	1969.231	Tx : Rx : Loss : Loss% :	3846154.000 3846154.000 0 0.00	2012	2177	2080.500
Trial: 1 / FS: 1280 / Iter: 2	55	55	1057692.6	10830.772	Tx : Rx : Loss : Loss% :	21153846.000 21153846.000 0 0.00	2012	2182	2081.500
Trial: 1 / FS: 1280 / Iter: 3	78	78	1490385.0	15261.542	Tx : Rx : Loss : Loss% :	29807692.000 29807692.000 0 0.00	2012	2182	2081.500
Trial: 1 / FS: 1280 / Iter: 4	89	89	1706731.5	17476.931	Tx : Rx : Loss : Loss% :	34134616.000 34134616.000 0 0.00	2012	2180	2081.500
Trial: 1 / FS: 1280 / Iter: 5	94	94	1814903.9	18584.616	Tx : Rx : Loss : Loss% :	36298076.000 36298076.000 0 0.00	2012	2182	2081.500
Trial: 1 / FS: 1280 / Iter: 6	97	97	1868991.0	19138.468	Tx : Rx : Loss : Loss% :	37379808.000 37379808.000 0 0.00	2015	2180	2083.500
Trial: 1 / FS: 1280 / Iter: 7	99	99	1896033.7	19415.385	Tx : Rx : Loss : Loss% :	37920674.000 37920674.000 0 0.00	2040	2182	2096.500
Trial: 1 / FS: 1280 / Iter: 8	99	99	1909555.7	19553.850	Tx : Rx : Loss : Loss% :	38191106.000 38191106.000 0 0.00	2055	2182	2108.000
Trial: 1 / FS: 1280 / Iter: 9	100	100	1923076.9	19692.308	Tx : Rx : Loss : Loss% :	38461538.000 38461538.000 0 0.00	2087	2180	2138.500
Trial: 1 / FS: 1518 / Iter: 1	10	10	162548.8	1973.992	Tx : Rx : Loss : Loss% :	3250976.000 3250976.000 0 0.00	2000	2165	2066.000
Trial: 1 / FS: 1518 / Iter: 2	55	55	894018.3	10856.958	Tx : Rx : Loss : Loss% :	17880364.000 17880364.000 0 0.00	2000	2167	2066.000
Trial: 1 / FS: 1518 / Iter: 3	78	78	1259753.2	15298.443	Tx : Rx : Loss : Loss% :	25195058.000 25195058.000 0 0.00	2000	2165	2066.000
Trial: 1 / FS: 1518 / Iter: 4	89	89	1442620.9	17519.188	Tx : Rx : Loss : Loss% :	28852406.000 28852406.000 0 0.00	1997	2165	2066.000
Trial: 1 / FS: 1518 / Iter: 5	94	94	1534054.8	18629.562	Tx : Rx : Loss : Loss% :	30681080.000 30681080.000 0 0.00	2002	2167	2066.500

Trial: 1 / FS: 1518 / Iter: 6	97	97	1579771.0	19184.739	Tx :	31595416.000	2005	2165	2070.000
					Rx :	31595416.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 7	99	99	1602629.3	19462.330	Tx :	32052584.000	2020	2167	2079.500
					Rx :	32052584.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 8	99	99	1614058.4	19601.126	Tx :	32281168.000	2027	2167	2089.500
					Rx :	32281168.000			
					Loss :	0			
					Loss% :	0.00			
Trial: 1 / FS: 1518 / Iter: 9	100	100	1625487.6	19739.922	Tx :	32509752.000	2045	2172	2125.500
					Rx :	32509752.000			
					Loss :	0			
					Loss% :	0.00			

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)	
				Tx Rate %	Rx Rate						
					%	FPS	Mbps				
Trial: 1 / FS: 64 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100	14880952.3	7619.05	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	297619048 297619048 0 0.000
Trial: 1 / FS: 64 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100	14880952.4	7619.05	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	297619048 297619048 0 0.000
Trial: 1 / FS: 128 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.05	88	7436412.9	7614.89	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	148727829 148727829 0 0.000
Trial: 1 / FS: 128 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.05	88	7436412.9	7614.89	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	148727829 148727829 0 0.000
Trial: 1 / FS: 256 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100	4528985.5	9275.36	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	90579710 90579710 0 0.000
Trial: 1 / FS: 256 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100	4528985.5	9275.36	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	90579710 90579710 0 0.000
Trial: 1 / FS: 512 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100	2349624.0	9624.06	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	46992481 46992481 0 0.000
Trial: 1 / FS: 512 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100	2349624.1	9624.06	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	46992481 46992481 0 0.000
Trial: 1 / FS: 1024 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100	1197318.0	9808.43	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	23946360 23946360 0 0.000
Trial: 1 / FS: 1024 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100	1197318.0	9808.43	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	23946360 23946360 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100	961538.5	9846.15	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	19230769 19230769 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100	961538.5	9846.15	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	19230769 19230769 0 0.000
Trial: 1 / FS: 1518 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100	812743.8	9869.96	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	16254876 16254876 0 0.000

Trial: 1 / FS: 1518 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100	812743.8	9869.96	Tx Rate Mbps : Rx Rate Mbps : Lost Bits % :		Tx : Rx : Loss : Loss% :	16254876 16254876 0 0.000

RFC2544 - Throughput/Latency - Per Flow Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2017	2195	2100
Trial: 1 / FS: 64 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2027	2142	2044
Trial: 1 / FS: 128 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1965	2110	2037
Trial: 1 / FS: 128 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2065	2006
Trial: 1 / FS: 256 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2015	2170	2153
Trial: 1 / FS: 256 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2087	2115	2099
Trial: 1 / FS: 512 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2117	2230	2213
Trial: 1 / FS: 512 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2130	2185	2168
Trial: 1 / FS: 1024 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2020	2165	2147
Trial: 1 / FS: 1024 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2035	2120	2102
Trial: 1 / FS: 1280 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2087	2180	2161
Trial: 1 / FS: 1280 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2097	2135	2116
Trial: 1 / FS: 1518 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2045	2172	2149
Trial: 1 / FS: 1518 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2057	2122	2102

RFC2544 - Throughput/Latency - Iteration Statistics - Part 1 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	L2 Throughput				L1 Throughput		Throughput (frames)	
				Tx Rate %	Rx Rate			Tx Rate Mbps	Rx Rate Mbps		
					%	FPS	Mbps				
Trial: 1 / FS: 64 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	10.00	10.00	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	10.00	10.00	1488095.2	761.91			Tx : 29761905 Rx : 29761905 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	55.00	55.00	8184561.8	4190.50			Tx : 163690476 Rx : 163690476 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	55.00	55.00	8184561.9	4190.50			Tx : 163690476 Rx : 163690476 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	77.50	77.50	11532778.3	5904.78			Tx : 230654762 Rx : 230654762 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	77.50	77.50	11532778.3	5904.78			Tx : 230654762 Rx : 230654762 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.75	88.75	13206904.7	6761.94			Tx : 264136905 Rx : 264136905 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.75	88.75	13206904.7	6761.94			Tx : 264136905 Rx : 264136905 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	94.38	94.38	14044019.2	7190.54			Tx : 280877976 Rx : 280877976 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	94.38	94.38	14044019.2	7190.54			Tx : 280877976 Rx : 280877976 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	97.19	97.19	14462459.8	7404.78			Tx : 289248512 Rx : 289248512 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	97.19	97.19	14462459.8	7404.78			Tx : 289248512 Rx : 289248512 Loss : 0 Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	98.59	98.59	14671832.4	7511.98			Tx : 293433780 Rx : 293433780 Loss : 0 Loss% : 0.000	

Trial: 1 / FS: 64 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	98.59	98.59	14671832.4	7511.98	Tx Rx Loss Loss%	: : : :	293433780 293433780 0 0.000
Trial: 1 / FS: 64 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	99.30	99.30	14776334.7	7565.48	Tx Rx Loss Loss%	: : : :	295526414 295526414 0 0.000
Trial: 1 / FS: 64 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	99.30	99.30	14776334.8	7565.48	Tx Rx Loss Loss%	: : : :	295526414 295526414 0 0.000
Trial: 1 / FS: 64 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100.00	14880952.3	7619.05	Tx Rx Loss Loss%	: : : :	297619048 297619048 0 0.000
Trial: 1 / FS: 64 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100.00	14880952.4	7619.05	Tx Rx Loss Loss%	: : : :	297619048 297619048 0 0.000
Trial: 1 / FS: 128 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	10.00	10.00	844594.6	864.87	Tx Rx Loss Loss%	: : : :	16891892 16891892 0 0.000
Trial: 1 / FS: 128 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	10.00	10.00	844594.6	864.87	Tx Rx Loss Loss%	: : : :	16891892 16891892 0 0.000
Trial: 1 / FS: 128 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	55.00	55.00	4645271.8	4756.76	Tx Rx Loss Loss%	: : : :	92905405 92905405 0 0.000
Trial: 1 / FS: 128 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	55.00	55.00	4645271.8	4756.76	Tx Rx Loss Loss%	: : : :	92905405 92905405 0 0.000
Trial: 1 / FS: 128 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	77.50	77.50	6545640.5	6702.74	Tx Rx Loss Loss%	: : : :	130912162 130912162 0 0.000
Trial: 1 / FS: 128 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	77.50	77.50	6545640.5	6702.74	Tx Rx Loss Loss%	: : : :	130912162 130912162 0 0.000
Trial: 1 / FS: 128 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.75	88.75	7495812.8	7675.71	Tx Rx Loss Loss%	: : : :	149915541 60265993 89649548 59.800
Trial: 1 / FS: 128 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.75	88.75	7495812.9	7675.71	Tx Rx Loss Loss%	: : : :	149915541 60287379 89628162 59.786
Trial: 1 / FS: 128 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	83.13	83.13	7020700.1	7189.20	Tx Rx Loss Loss%	: : : :	140413851 140413851 0 0.000
Trial: 1 / FS: 128 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	83.13	83.13	7020700.1	7189.20	Tx Rx Loss Loss%	: : : :	140413851 140413851 0 0.000

Trial: 1 / FS: 128 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	85.94	85.94	7258252.0	7432.45	Tx Rx Loss Loss%	: : : :	145164696 145164696 0 0.000
Trial: 1 / FS: 128 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	85.94	85.94	7258252.0	7432.45	Tx Rx Loss Loss%	: : : :	145164696 145164696 0 0.000
Trial: 1 / FS: 128 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	87.34	87.34	7377011.4	7554.06	Tx Rx Loss Loss%	: : : :	147540118 147540118 0 0.000
Trial: 1 / FS: 128 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	87.34	87.34	7377011.4	7554.06	Tx Rx Loss Loss%	: : : :	147540118 147540118 0 0.000
Trial: 1 / FS: 128 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.05	88.05	7436412.9	7614.89	Tx Rx Loss Loss%	: : : :	148727829 148727829 0 0.000
Trial: 1 / FS: 128 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.05	88.05	7436412.9	7614.89	Tx Rx Loss Loss%	: : : :	148727829 148727829 0 0.000
Trial: 1 / FS: 256 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	10.00	10.00	452898.6	927.54	Tx Rx Loss Loss%	: : : :	9057971 9057971 0 0.000
Trial: 1 / FS: 256 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	10.00	10.00	452898.6	927.54	Tx Rx Loss Loss%	: : : :	9057971 9057971 0 0.000
Trial: 1 / FS: 256 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	55.00	55.00	2490946.0	5101.46	Tx Rx Loss Loss%	: : : :	49818841 49818841 0 0.000
Trial: 1 / FS: 256 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	55.00	55.00	2490946.0	5101.46	Tx Rx Loss Loss%	: : : :	49818841 49818841 0 0.000
Trial: 1 / FS: 256 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	77.50	77.50	3509965.0	7188.41	Tx Rx Loss Loss%	: : : :	70199275 70199275 0 0.000
Trial: 1 / FS: 256 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	77.50	77.50	3509965.0	7188.41	Tx Rx Loss Loss%	: : : :	70199275 70199275 0 0.000
Trial: 1 / FS: 256 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.75	88.75	4019481.9	8231.90	Tx Rx Loss Loss%	: : : :	80389493 80389493 0 0.000
Trial: 1 / FS: 256 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.75	88.75	4019481.9	8231.90	Tx Rx Loss Loss%	: : : :	80389493 80389493 0 0.000
Trial: 1 / FS: 256 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	94.38	94.38	4274232.1	8753.63	Tx Rx Loss Loss%	: : : :	85484601 85484601 0 0.000

Trial: 1 / FS: 256 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	94.38	94.38	4274232.1	8753.63	Tx Rx Loss Loss%	: : : :	85484601 85484601 0 0.000
Trial: 1 / FS: 256 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	97.19	97.19	4401620.3	9014.52	Tx Rx Loss Loss%	: : : :	88032156 88032156 0 0.000
Trial: 1 / FS: 256 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	97.19	97.19	4401620.3	9014.52	Tx Rx Loss Loss%	: : : :	88032156 88032156 0 0.000
Trial: 1 / FS: 256 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	98.59	98.59	4465298.0	9144.93	Tx Rx Loss Loss%	: : : :	89305933 89305933 0 0.000
Trial: 1 / FS: 256 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	98.59	98.59	4465298.0	9144.93	Tx Rx Loss Loss%	: : : :	89305933 89305933 0 0.000
Trial: 1 / FS: 256 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	99.30	99.30	4497145.4	9210.15	Tx Rx Loss Loss%	: : : :	89942822 89942822 0 0.000
Trial: 1 / FS: 256 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	99.30	99.30	4497145.4	9210.15	Tx Rx Loss Loss%	: : : :	89942822 89942822 0 0.000
Trial: 1 / FS: 256 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100.00	4528985.5	9275.36	Tx Rx Loss Loss%	: : : :	90579710 90579710 0 0.000
Trial: 1 / FS: 256 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100.00	4528985.5	9275.36	Tx Rx Loss Loss%	: : : :	90579710 90579710 0 0.000
Trial: 1 / FS: 512 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	10.00	10.00	234962.4	962.41	Tx Rx Loss Loss%	: : : :	4699248 4699248 0 0.000
Trial: 1 / FS: 512 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	10.00	10.00	234962.4	962.41	Tx Rx Loss Loss%	: : : :	4699248 4699248 0 0.000
Trial: 1 / FS: 512 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	55.00	55.00	1292293.6	5293.24	Tx Rx Loss Loss%	: : : :	25845865 25845865 0 0.000
Trial: 1 / FS: 512 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	55.00	55.00	1292293.6	5293.24	Tx Rx Loss Loss%	: : : :	25845865 25845865 0 0.000
Trial: 1 / FS: 512 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	77.50	77.50	1820959.8	7458.65	Tx Rx Loss Loss%	: : : :	36419173 36419173 0 0.000
Trial: 1 / FS: 512 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	77.50	77.50	1820959.8	7458.65	Tx Rx Loss Loss%	: : : :	36419173 36419173 0 0.000

Trial: 1 / FS: 512 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.75	88.75	2085291.7	8541.36	Tx Rx Loss Loss%	: : : :	41705827 41705827 0 0.000
Trial: 1 / FS: 512 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.75	88.75	2085291.7	8541.36	Tx Rx Loss Loss%	: : : :	41705827 41705827 0 0.000
Trial: 1 / FS: 512 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	94.38	94.38	2217460.1	9082.72	Tx Rx Loss Loss%	: : : :	44349154 44349154 0 0.000
Trial: 1 / FS: 512 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	94.38	94.38	2217460.1	9082.72	Tx Rx Loss Loss%	: : : :	44349154 44349154 0 0.000
Trial: 1 / FS: 512 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	97.19	97.19	2283540.8	9353.38	Tx Rx Loss Loss%	: : : :	45670818 45670818 0 0.000
Trial: 1 / FS: 512 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	97.19	97.19	2283540.8	9353.38	Tx Rx Loss Loss%	: : : :	45670818 45670818 0 0.000
Trial: 1 / FS: 512 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	98.59	98.59	2316582.7	9488.72	Tx Rx Loss Loss%	: : : :	46331649 46331649 0 0.000
Trial: 1 / FS: 512 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	98.59	98.59	2316582.8	9488.72	Tx Rx Loss Loss%	: : : :	46331649 46331649 0 0.000
Trial: 1 / FS: 512 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	99.30	99.30	2333105.5	9556.40	Tx Rx Loss Loss%	: : : :	46662065 46662065 0 0.000
Trial: 1 / FS: 512 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	99.30	99.30	2333105.5	9556.40	Tx Rx Loss Loss%	: : : :	46662065 46662065 0 0.000
Trial: 1 / FS: 512 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100.00	2349624.0	9624.06	Tx Rx Loss Loss%	: : : :	46992481 46992481 0 0.000
Trial: 1 / FS: 512 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100.00	2349624.1	9624.06	Tx Rx Loss Loss%	: : : :	46992481 46992481 0 0.000
Trial: 1 / FS: 1024 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	10.00	10.00	119731.8	980.84	Tx Rx Loss Loss%	: : : :	2394636 2394636 0 0.000
Trial: 1 / FS: 1024 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	10.00	10.00	119731.8	980.84	Tx Rx Loss Loss%	: : : :	2394636 2394636 0 0.000
Trial: 1 / FS: 1024 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	55.00	55.00	658525.0	5394.64	Tx Rx Loss Loss%	: : : :	13170498 13170498 0 0.000

Trial: 1 / FS: 1024 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	55.00	55.00	658525.0	5394.64	Tx Rx Loss Loss%	: : : :	13170498 13170498 0 0.000
Trial: 1 / FS: 1024 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	77.50	77.50	927921.5	7601.53	Tx Rx Loss Loss%	: : : :	18558429 18558429 0 0.000
Trial: 1 / FS: 1024 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	77.50	77.50	927921.5	7601.53	Tx Rx Loss Loss%	: : : :	18558429 18558429 0 0.000
Trial: 1 / FS: 1024 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.75	88.75	1062619.9	8704.98	Tx Rx Loss Loss%	: : : :	21252395 21252395 0 0.000
Trial: 1 / FS: 1024 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.75	88.75	1062619.9	8704.98	Tx Rx Loss Loss%	: : : :	21252395 21252395 0 0.000
Trial: 1 / FS: 1024 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	94.38	94.38	1129969.4	9256.71	Tx Rx Loss Loss%	: : : :	22599377 22599377 0 0.000
Trial: 1 / FS: 1024 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	94.38	94.38	1129969.4	9256.71	Tx Rx Loss Loss%	: : : :	22599377 22599377 0 0.000
Trial: 1 / FS: 1024 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	97.19	97.19	1163643.8	9532.57	Tx Rx Loss Loss%	: : : :	23272869 23272869 0 0.000
Trial: 1 / FS: 1024 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	97.19	97.19	1163643.8	9532.57	Tx Rx Loss Loss%	: : : :	23272869 23272869 0 0.000
Trial: 1 / FS: 1024 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	98.59	98.59	1180480.7	9670.50	Tx Rx Loss Loss%	: : : :	23609614 23609614 0 0.000
Trial: 1 / FS: 1024 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	98.59	98.59	1180480.8	9670.50	Tx Rx Loss Loss%	: : : :	23609614 23609614 0 0.000
Trial: 1 / FS: 1024 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	99.30	99.30	1188899.4	9739.46	Tx Rx Loss Loss%	: : : :	23777987 23777987 0 0.000
Trial: 1 / FS: 1024 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	99.30	99.30	1188899.4	9739.46	Tx Rx Loss Loss%	: : : :	23777987 23777987 0 0.000
Trial: 1 / FS: 1024 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100.00	1197318.0	9808.43	Tx Rx Loss Loss%	: : : :	23946360 23946360 0 0.000
Trial: 1 / FS: 1024 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100.00	1197318.0	9808.43	Tx Rx Loss Loss%	: : : :	23946360 23946360 0 0.000

Trial: 1 / FS: 1280 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	10.00	10.00	96153.8	984.62	Tx Rx Loss Loss%	: : : :	1923077 1923077 0 0.000
Trial: 1 / FS: 1280 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	10.00	10.00	96153.8	984.62	Tx Rx Loss Loss%	: : : :	1923077 1923077 0 0.000
Trial: 1 / FS: 1280 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	55.00	55.00	528846.3	5415.39	Tx Rx Loss Loss%	: : : :	10576923 10576923 0 0.000
Trial: 1 / FS: 1280 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	55.00	55.00	528846.3	5415.39	Tx Rx Loss Loss%	: : : :	10576923 10576923 0 0.000
Trial: 1 / FS: 1280 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	77.50	77.50	745192.5	7630.77	Tx Rx Loss Loss%	: : : :	14903846 14903846 0 0.000
Trial: 1 / FS: 1280 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	77.50	77.50	745192.5	7630.77	Tx Rx Loss Loss%	: : : :	14903846 14903846 0 0.000
Trial: 1 / FS: 1280 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.75	88.75	853365.8	8738.47	Tx Rx Loss Loss%	: : : :	17067308 17067308 0 0.000
Trial: 1 / FS: 1280 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.75	88.75	853365.8	8738.47	Tx Rx Loss Loss%	: : : :	17067308 17067308 0 0.000
Trial: 1 / FS: 1280 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	94.38	94.38	907452.0	9292.31	Tx Rx Loss Loss%	: : : :	18149038 18149038 0 0.000
Trial: 1 / FS: 1280 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	94.38	94.38	907452.0	9292.31	Tx Rx Loss Loss%	: : : :	18149038 18149038 0 0.000
Trial: 1 / FS: 1280 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	97.19	97.19	934495.5	9569.23	Tx Rx Loss Loss%	: : : :	18689904 18689904 0 0.000
Trial: 1 / FS: 1280 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	97.19	97.19	934495.5	9569.23	Tx Rx Loss Loss%	: : : :	18689904 18689904 0 0.000
Trial: 1 / FS: 1280 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	98.59	98.59	948016.8	9707.69	Tx Rx Loss Loss%	: : : :	18960337 18960337 0 0.000
Trial: 1 / FS: 1280 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	98.59	98.59	948016.8	9707.69	Tx Rx Loss Loss%	: : : :	18960337 18960337 0 0.000
Trial: 1 / FS: 1280 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	99.30	99.30	954777.8	9776.93	Tx Rx Loss Loss%	: : : :	19095553 19095553 0 0.000

Trial: 1 / FS: 1280 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	99.30	99.30	954777.8	9776.93	Tx Rx Loss Loss%	: : : :	19095553 19095553 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100.00	961538.5	9846.15	Tx Rx Loss Loss%	: : : :	19230769 19230769 0 0.000
Trial: 1 / FS: 1280 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100.00	961538.5	9846.15	Tx Rx Loss Loss%	: : : :	19230769 19230769 0 0.000
Trial: 1 / FS: 1518 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	10.00	10.00	81274.4	987.00	Tx Rx Loss Loss%	: : : :	1625488 1625488 0 0.000
Trial: 1 / FS: 1518 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	10.00	10.00	81274.4	987.00	Tx Rx Loss Loss%	: : : :	1625488 1625488 0 0.000
Trial: 1 / FS: 1518 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	55.00	55.00	447009.2	5428.48	Tx Rx Loss Loss%	: : : :	8940182 8940182 0 0.000
Trial: 1 / FS: 1518 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	55.00	55.00	447009.2	5428.48	Tx Rx Loss Loss%	: : : :	8940182 8940182 0 0.000
Trial: 1 / FS: 1518 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	77.50	77.50	629876.6	7649.22	Tx Rx Loss Loss%	: : : :	12597529 12597529 0 0.000
Trial: 1 / FS: 1518 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	77.50	77.50	629876.6	7649.22	Tx Rx Loss Loss%	: : : :	12597529 12597529 0 0.000
Trial: 1 / FS: 1518 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	88.75	88.75	721310.4	8759.59	Tx Rx Loss Loss%	: : : :	14426203 14426203 0 0.000
Trial: 1 / FS: 1518 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	88.75	88.75	721310.4	8759.59	Tx Rx Loss Loss%	: : : :	14426203 14426203 0 0.000
Trial: 1 / FS: 1518 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	94.38	94.38	767027.4	9314.78	Tx Rx Loss Loss%	: : : :	15340540 15340540 0 0.000
Trial: 1 / FS: 1518 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	94.38	94.38	767027.4	9314.78	Tx Rx Loss Loss%	: : : :	15340540 15340540 0 0.000
Trial: 1 / FS: 1518 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	97.19	97.19	789885.5	9592.37	Tx Rx Loss Loss%	: : : :	15797708 15797708 0 0.000
Trial: 1 / FS: 1518 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	97.19	97.19	789885.5	9592.37	Tx Rx Loss Loss%	: : : :	15797708 15797708 0 0.000

Trial: 1 / FS: 1518 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	98.59	98.59	801314.7	9731.17	Tx Rx Loss Loss%	: : : :	16026292 16026292 0 0.000
Trial: 1 / FS: 1518 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	98.59	98.59	801314.7	9731.17	Tx Rx Loss Loss%	: : : :	16026292 16026292 0 0.000
Trial: 1 / FS: 1518 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	99.30	99.30	807029.2	9800.56	Tx Rx Loss Loss%	: : : :	16140584 16140584 0 0.000
Trial: 1 / FS: 1518 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	99.30	99.30	807029.2	9800.56	Tx Rx Loss Loss%	: : : :	16140584 16140584 0 0.000
Trial: 1 / FS: 1518 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	100.00	100.00	812743.8	9869.96	Tx Rx Loss Loss%	: : : :	16254876 16254876 0 0.000
Trial: 1 / FS: 1518 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	100.00	100.00	812743.8	9869.96	Tx Rx Loss Loss%	: : : :	16254876 16254876 0 0.000

RFC2544 - Throughput/Latency - Iteration Statistics - Part 2 of 2

Trial / Framesize / Iteration	Tx Port	Rx Port	Flow Group	Min Latency (ns)	Max Latency (ns)	Avg Latency (ns)
Trial: 1 / FS: 64 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1940	2107	2008.00
Trial: 1 / FS: 64 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1947	2057	1999.00
Trial: 1 / FS: 64 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1942	2107	2012.00
Trial: 1 / FS: 64 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1950	2060	2000.00
Trial: 1 / FS: 64 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1947	2107	2030.00
Trial: 1 / FS: 64 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2060	2002.00
Trial: 1 / FS: 64 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1960	2107	2048.00
Trial: 1 / FS: 64 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1957	2060	2004.00
Trial: 1 / FS: 64 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2000	2110	2057.00
Trial: 1 / FS: 64 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1960	2060	2007.00
Trial: 1 / FS: 64 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2012	2112	2062.00
Trial: 1 / FS: 64 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1965	2060	2009.00
Trial: 1 / FS: 64 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2025	2112	2067.00
Trial: 1 / FS: 64 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1972	2060	2013.00
Trial: 1 / FS: 64 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2002	2115	2072.00
Trial: 1 / FS: 64 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1980	2060	2018.00
Trial: 1 / FS: 64 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2017	2195	2100.00
Trial: 1 / FS: 64 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2027	2142	2044.00
Trial: 1 / FS: 128 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1942	2107	2009.00

Trial: 1 / FS: 128 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2062	2004.00
Trial: 1 / FS: 128 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1940	2110	2009.00
Trial: 1 / FS: 128 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2065	2004.00
Trial: 1 / FS: 128 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1952	2110	2024.00
Trial: 1 / FS: 128 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2065	2004.00
Trial: 1 / FS: 128 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1967	2110	2039.00
Trial: 1 / FS: 128 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1957	2065	2007.00
Trial: 1 / FS: 128 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1962	2110	2031.00
Trial: 1 / FS: 128 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2065	2004.00
Trial: 1 / FS: 128 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1962	2110	2034.00
Trial: 1 / FS: 128 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2065	2005.00
Trial: 1 / FS: 128 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1965	2110	2036.00
Trial: 1 / FS: 128 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2065	2006.00
Trial: 1 / FS: 128 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1965	2110	2037.00
Trial: 1 / FS: 128 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	1952	2065	2006.00
Trial: 1 / FS: 256 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2162	2066.00
Trial: 1 / FS: 256 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2012	2115	2059.00
Trial: 1 / FS: 256 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2165	2066.00
Trial: 1 / FS: 256 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2012	2117	2059.00
Trial: 1 / FS: 256 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2165	2070.00
Trial: 1 / FS: 256 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2012	2117	2059.00

Trial: 1 / FS: 256 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2020	2165	2081.00
Trial: 1 / FS: 256 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2027	2117	2065.00
Trial: 1 / FS: 256 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2037	2165	2096.00
Trial: 1 / FS: 256 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2032	2117	2070.00
Trial: 1 / FS: 256 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2017	2167	2110.00
Trial: 1 / FS: 256 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2032	2117	2076.00
Trial: 1 / FS: 256 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2077	2167	2122.00
Trial: 1 / FS: 256 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2050	2117	2080.00
Trial: 1 / FS: 256 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2090	2170	2130.00
Trial: 1 / FS: 256 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2045	2117	2084.00
Trial: 1 / FS: 256 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2015	2170	2153.00
Trial: 1 / FS: 256 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2087	2115	2099.00
Trial: 1 / FS: 512 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2062	2230	2130.00
Trial: 1 / FS: 512 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2080	2185	2130.00
Trial: 1 / FS: 512 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2062	2227	2130.00
Trial: 1 / FS: 512 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2080	2185	2130.00
Trial: 1 / FS: 512 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2062	2230	2130.00
Trial: 1 / FS: 512 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2080	2185	2130.00
Trial: 1 / FS: 512 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2062	2230	2136.00
Trial: 1 / FS: 512 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2080	2185	2130.00
Trial: 1 / FS: 512 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2080	2230	2147.00

Trial: 1 / FS: 512 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2097	2185	2136.00
Trial: 1 / FS: 512 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2092	2230	2155.00
Trial: 1 / FS: 512 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2105	2185	2141.00
Trial: 1 / FS: 512 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2102	2230	2163.00
Trial: 1 / FS: 512 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2120	2185	2147.00
Trial: 1 / FS: 512 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2112	2232	2171.00
Trial: 1 / FS: 512 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2127	2185	2152.00
Trial: 1 / FS: 512 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2117	2230	2213.00
Trial: 1 / FS: 512 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2130	2185	2168.00
Trial: 1 / FS: 1024 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2165	2065.00
Trial: 1 / FS: 1024 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2017	2117	2063.00
Trial: 1 / FS: 1024 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2000	2167	2067.00
Trial: 1 / FS: 1024 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2012	2117	2060.00
Trial: 1 / FS: 1024 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2165	2065.00
Trial: 1 / FS: 1024 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2015	2120	2063.00
Trial: 1 / FS: 1024 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2165	2065.00
Trial: 1 / FS: 1024 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2017	2120	2063.00
Trial: 1 / FS: 1024 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2165	2068.00
Trial: 1 / FS: 1024 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2015	2120	2063.00
Trial: 1 / FS: 1024 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2010	2165	2081.00
Trial: 1 / FS: 1024 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2025	2120	2068.00

Trial: 1 / FS: 1024 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2037	2165	2099.00
Trial: 1 / FS: 1024 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2037	2120	2074.00
Trial: 1 / FS: 1024 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2060	2165	2113.00
Trial: 1 / FS: 1024 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2042	2120	2078.00
Trial: 1 / FS: 1024 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2020	2165	2147.00
Trial: 1 / FS: 1024 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2035	2120	2102.00
Trial: 1 / FS: 1280 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2012	2177	2081.00
Trial: 1 / FS: 1280 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2032	2135	2080.00
Trial: 1 / FS: 1280 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2012	2182	2082.00
Trial: 1 / FS: 1280 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2030	2137	2081.00
Trial: 1 / FS: 1280 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2012	2182	2082.00
Trial: 1 / FS: 1280 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2030	2137	2081.00
Trial: 1 / FS: 1280 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2012	2180	2082.00
Trial: 1 / FS: 1280 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2032	2137	2081.00
Trial: 1 / FS: 1280 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2012	2182	2082.00
Trial: 1 / FS: 1280 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2030	2137	2081.00
Trial: 1 / FS: 1280 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2015	2180	2085.00
Trial: 1 / FS: 1280 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2032	2137	2082.00
Trial: 1 / FS: 1280 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2040	2182	2102.00
Trial: 1 / FS: 1280 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2047	2137	2091.00
Trial: 1 / FS: 1280 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2055	2182	2120.00

Trial: 1 / FS: 1280 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2062	2137	2096.00
Trial: 1 / FS: 1280 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2087	2180	2161.00
Trial: 1 / FS: 1280 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2097	2135	2116.00
Trial: 1 / FS: 1518 / Iter: 1	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2000	2165	2067.00
Trial: 1 / FS: 1518 / Iter: 1	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2017	2120	2065.00
Trial: 1 / FS: 1518 / Iter: 2	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2000	2167	2067.00
Trial: 1 / FS: 1518 / Iter: 2	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2017	2122	2065.00
Trial: 1 / FS: 1518 / Iter: 3	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2000	2165	2067.00
Trial: 1 / FS: 1518 / Iter: 3	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2017	2122	2065.00
Trial: 1 / FS: 1518 / Iter: 4	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	1997	2165	2067.00
Trial: 1 / FS: 1518 / Iter: 4	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2017	2120	2065.00
Trial: 1 / FS: 1518 / Iter: 5	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2002	2167	2071.00
Trial: 1 / FS: 1518 / Iter: 5	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2015	2120	2062.00
Trial: 1 / FS: 1518 / Iter: 6	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2005	2165	2073.00
Trial: 1 / FS: 1518 / Iter: 6	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2022	2122	2067.00
Trial: 1 / FS: 1518 / Iter: 7	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2020	2167	2085.00
Trial: 1 / FS: 1518 / Iter: 7	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2037	2120	2074.00
Trial: 1 / FS: 1518 / Iter: 8	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2027	2167	2101.00
Trial: 1 / FS: 1518 / Iter: 8	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2040	2120	2078.00
Trial: 1 / FS: 1518 / Iter: 9	7-6	7-7	IES5200W-8U2F2SD-Endpoint Set-1 - Flow Group 0001	2045	2172	2149.00
Trial: 1 / FS: 1518 / Iter: 9	7-7	7-6	IES5200W-8U2F2SD-Endpoint Set-2 - Flow Group 0001	2057	2122	2102.00

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730