




KEYSIGHT
TECHNOLOGIES

IxNetwork Report

Test: RFC2544 - Throughput/Latency

Test Date: 08/25/2025 17:55:26

www.ixiacom.com
www.ixiacom.com/support

Table of Contents

1.	Cover	1
2.	Info	3
3.	Test Info	4
4.	Port Map	5
5.	Aggregate Graphs	6
6.	IterationCharts	14
7.	Aggregated Results	20
8.	Per Flow Results	22
9.	Iteration Data	24
10.	Theoretical Max Rates	37

RFC2544 - Throughput/Latency - Info

Test Information

Product Information

Product Label : N9550-32D
 Product Version : 4.7.0E
 Serial Number : 971632D2348072
 Comments :

Test Settings

Date Executed : 05/25/2008
 Time Executed : 17:55:26
 User Name : FS.COM
 Number of Trials Executed : 1
 Stream Duration (sec) : 20
 Calculate Latency : True
 Latency Type : Store and Forward

Output Parameters

Number of Trials Passed : N/A
 Test Duration (sec) : 00:33:54

RFC2544 - Throughput/Latency - Info**Test Information****Port Information**

Port Count: 6
Port Speeds: 400000 Mbps; 100000 Mbps
Additional Details:

Topology Information

Topology Count: 1
Device Group Count: 1
Protocols: Ethernet
Additional Details:

Traffic Information

Traffic-Item Count: 2
Source-Destination Mesh: One - One
Route Mesh: One - One
Bi-directional: False
Additional Details:

Packet Stack Information

Frame Size Type: Fixed
Additional Layer 2 Details: Frame Ordering Type: No Ordering
Packet Type: Ethernet
Source Start Port:
Destination Start Port:
Additional Layer 4 Details:

Test Execution Information


Version Used: 10.00.2312.4
Test Execution Date: Tuesday 05 August 2025 - 17:55:28
Test Result Location: C:\Users\Aurelie.huang\AppData\Local\Ixia\IxNetwork\data\result\DP.Rfc2544Tput\dd81de3f-a961-47fe-99c8-0e942c32b9a1\Run0001
Additional Details:

RFC2544 - Throughput/Latency - Port Map Information

Port Map :	Tx Port	Tx Speed (Mbps)	Rx Port	Rx Speed (Mbps)
	10.36.15.201/1	400000	10.36.15.201/2	400000
	10.36.15.201/2	400000	10.36.15.201/1	400000


RFC2544 - Throughput/Latency - Aggregated Graph


Total Frames Transmitted and Received



Trial - Framesize - Iteration

RFC2544 - Throughput/Latency - Aggregated Graph




RFC2544 - Throughput/Latency - Aggregated Graph**Aggregated Frame Loss**

Trial - Framesize - Iteration


RFC2544 - Throughput/Latency - Aggregated Graph

Aggregated Frame Loss per Frame Size




RFC2544 - Throughput/Latency - Aggregated Graph


Aggregated Frame Loss per Line Rate



RFC2544 - Throughput/Latency - Per Flow Graph





RFC2544 - Throughput/Latency - Aggregated Graph



RFC2544 - Throughput/Latency - Per Flow Graph


Tx / Rx Frame Count




Trial

RFC2544 - Throughput/Latency - Iteration Graph


Aggregated Frame Loss for Trial 1 and Framesize 64




Aggregated Frame Loss for Trial 1 and Framesize 128




Aggregated Frame Loss for Trial 1 and Framesize 256




Aggregated Frame Loss for Trial 1 and Framesize 512




Aggregated Frame Loss for Trial 1 and Framesize 1024




Aggregated Frame Loss for Trial 1 and Framesize 1280






RFC2544 - Throughput/Latency - Iteration Graph

Tx / Rx Frames per Frame Size



RFC2544 - Throughput/Latency - Iteration Graph



RFC2544 - Throughput/Latency - Aggregated Results

Trial / Framesize / Iteration	L2 Throughput				L1 Throughput Rate Mbps	Throughput (frames)		Latency (ns)			
	Tx Rate	Rx Rate									
		%	Real %	FPS							
Trial: 1 / FS: 64 / Iter: 5	83.1	83.1	989582325.8	506,666.15	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	19791666666 19791666666 0 0.0	Min : 913 Max : 993 Avg : 931			
Trial: 1 / FS: 128 / Iter: 9	100.0	100.0	675675674.7	691,891.89	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	13513513514 13513513514 0 0.0	Min : 913 Max : 956 Avg : 937			
Trial: 1 / FS: 256 / Iter: 9	100.0	100.0	362318839.7	742,028.98	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	7246376812 7246376812 0 0.0	Min : 920 Max : 985 Avg : 966			
Trial: 1 / FS: 512 / Iter: 9	100.0	100.0	187969924.6	769,924.81	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	3759398496 3759398496 0 0.0	Min : 922 Max : 963 Avg : 946			
Trial: 1 / FS: 1024 / Iter: 9	100.0	100.0	95785440.5	784,674.33	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	1915708812 1915708812 0 0.0	Min : 924 Max : 968 Avg : 950			
Trial: 1 / FS: 1280 / Iter: 9	100.0	100.0	76923076.9	787,692.31	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	1538461538 1538461538 0 0.0	Min : 922 Max : 954 Avg : 937			
Trial: 1 / FS: 1518 / Iter: 9	100.0	100.0	65019505.8	789,596.88	Tx : Rx : Loss % :	Tx : Rx : Loss : Loss % :	1300390118 1300390118 0 0.0	Min : 926 Max : 953 Avg : 936			

Column Header	Column Header Description
Trial	Trial number of the test run
Frame Size	The size of the frames used in the test
Trial / Framesize / Iteration	Iteration number of test
L2Tx Rate %	Aggregated L2 Throughput Transmit-side Line Rate
L2Rx Rate %	Aggregated L2 Throughput Receive-side Line Rate
L2Rx FPS	Aggregated L2 Throughput Receive-side Frame Rate
L2Rx Mbps	Aggregated L2 Throughput Receive-side Rate
L1Tx Mbps	Aggregated L1 Throughput Transmit-side Rate
L1Rx Mbps	Aggregated L1 Throughput Receive-side Rate
L1 Lost Bits%	Aggregated L1 Bits Loss Percentage
Tx Count	Throughput (frames) Sent Count
Rx Count	Throughput (frames) Received Count
Loss Count	Throughput (frames) Lost Count
Loss%	Throughput (frames) Loss Percentage
MinLatency (ns)	Minimum Latency Observed In Nanoseconds
MaxLatency (ns)	Maximum Latency Observed In Nanoseconds
AvgLatency (ns)	Average Latency Observed In Nanoseconds

RFC2544 - Throughput/Latency - Per Flow Statistics

Trial / Framesize / Iteration / Flow Group	Tx Port	Rx Port	L2 Throughput					L1 Throughput	Throughput (frames)	Latency (ns)	
			Tx Rate		Rx Rate						
			%	Real %	Real %	FPS	Mbps				
Trial: 1 / FS: 64 / Iter: 5	1 #1	2 #1	83.13		83	494791162.9	253333.08		Tx : 9895833333 Rx : 9895833333 Loss : 0 Loss% : 0.000	Min : 915 Max : 991 Avg : 932	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 5	2 #1	1 #1	83.13		83	494791162.9	253333.08		Tx : 9895833333 Rx : 9895833333 Loss : 0 Loss% : 0.000	Min : 913 Max : 993 Avg : 930	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 128 / Iter: 9	1 #1	2 #1	100.00		100	337837837.3	345945.95		Tx : 6756756757 Rx : 6756756757 Loss : 0 Loss% : 0.000	Min : 913 Max : 951 Avg : 936	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 128 / Iter: 9	2 #1	1 #1	100.00		100	337837837.3	345945.95		Tx : 6756756757 Rx : 6756756757 Loss : 0 Loss% : 0.000	Min : 915 Max : 956 Avg : 937	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 256 / Iter: 9	1 #1	2 #1	100.00		100	181159419.8	371014.49		Tx : 3623188406 Rx : 3623188406 Loss : 0 Loss% : 0.000	Min : 920 Max : 985 Avg : 966	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 256 / Iter: 9	2 #1	1 #1	100.00		100	181159419.9	371014.49		Tx : 3623188406 Rx : 3623188406 Loss : 0 Loss% : 0.000	Min : 920 Max : 980 Avg : 965	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 512 / Iter: 9	1 #1	2 #1	100.00		100	93984962.3	384962.41		Tx : 1879699248 Rx : 1879699248 Loss : 0 Loss% : 0.000	Min : 922 Max : 963 Avg : 946	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 512 / Iter: 9	2 #1	1 #1	100.00		100	93984962.3	384962.41		Tx : 1879699248 Rx : 1879699248 Loss : 0 Loss% : 0.000	Min : 924 Max : 962 Avg : 945	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 1024 / Iter: 9	1 #1	2 #1	100.00		100	47892720.2	392337.16		Tx : 957854406 Rx : 957854406 Loss : 0 Loss% : 0.000	Min : 925 Max : 968 Avg : 949	
N9550-32D-Endpoint Set-1 - Flow Group 0001											

Trial: 1 / FS: 1024 / Iter: 9 2 #1 1 #1 100.00 100 47892720.2 392337.16 <i>N9550-32D-Endpoint Set-2 - Flow Group 0001</i>								Tx : 957854406 Rx : 957854406 Loss : 0 Loss% : 0.000	Min : 924 Max : 968 Avg : 950
Trial: 1 / FS: 1280 / Iter: 9 1 #1 2 #1 100.00 100 38461538.4 393846.15 <i>N9550-32D-Endpoint Set-1 - Flow Group 0001</i>								Tx : 769230769 Rx : 769230769 Loss : 0 Loss% : 0.000	Min : 925 Max : 951 Avg : 937
Trial: 1 / FS: 1280 / Iter: 9 2 #1 1 #1 100.00 100 38461538.4 393846.15 <i>N9550-32D-Endpoint Set-2 - Flow Group 0001</i>								Tx : 769230769 Rx : 769230769 Loss : 0 Loss% : 0.000	Min : 922 Max : 954 Avg : 936
Trial: 1 / FS: 1518 / Iter: 9 1 #1 2 #1 100.00 100 32509752.9 394798.44 <i>N9550-32D-Endpoint Set-1 - Flow Group 0001</i>								Tx : 650195059 Rx : 650195059 Loss : 0 Loss% : 0.000	Min : 926 Max : 953 Avg : 936
Trial: 1 / FS: 1518 / Iter: 9 2 #1 1 #1 100.00 100 32509752.9 394798.44 <i>N9550-32D-Endpoint Set-2 - Flow Group 0001</i>								Tx : 650195059 Rx : 650195059 Loss : 0 Loss% : 0.000	Min : 928 Max : 950 Avg : 935

RFC2544 - Throughput/Latency - Iteration Statistics

Trial / Framesize / Iteration / Flow Group	Tx Port	Rx Port	L2 Throughput				L1 Throughput Mbps	Throughput (frames)	Latency (ns)		
			Tx Rate		Rx Rate						
			%	Real %	Real %	FPS					Mbps
Trial: 1 / FS: 64 / Iter: 1	1 #1	2 #1	10.00		10.00	59523809.5	30476.19		Tx : 1190476190 Rx : 1190476190 Loss : 0 Loss% : 0.000	Min : 910 Max : 946 Avg : 917	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 1	2 #1	1 #1	10.00		10.00	59523809.6	30476.19		Tx : 1190476190 Rx : 1190476190 Loss : 0 Loss% : 0.000	Min : 908 Max : 945 Avg : 915	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 2	1 #1	2 #1	55.00		55.00	327382474.6	167619.83		Tx : 6547619048 Rx : 6547619048 Loss : 0 Loss% : 0.000	Min : 911 Max : 951 Avg : 927	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 2	2 #1	1 #1	55.00		55.00	327382474.8	167619.83		Tx : 6547619048 Rx : 6547619048 Loss : 0 Loss% : 0.000	Min : 909 Max : 951 Avg : 926	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 3	1 #1	2 #1	77.50		77.50	461311132.5	236191.30		Tx : 9226190476 Rx : 9226190476 Loss : 0 Loss% : 0.000	Min : 913 Max : 952 Avg : 929	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 3	2 #1	1 #1	77.50		77.50	461311132.6	236191.30		Tx : 9226190476 Rx : 9226190476 Loss : 0 Loss% : 0.000	Min : 912 Max : 950 Avg : 927	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 4	1 #1	2 #1	88.75		83.31	495890673.4	253896.03		Tx : 10565476190 Rx : 9917874830 Loss : 647601360 Loss% : 6.129	Min : 914 Max : 8451 Avg : 8401	
N9550-32D-Endpoint Set-1 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 4	2 #1	1 #1	88.75		83.31	495890673.5	253896.03		Tx : 10565476190 Rx : 9917874827 Loss : 647601363 Loss% : 6.129	Min : 913 Max : 8451 Avg : 8400	
N9550-32D-Endpoint Set-2 - Flow Group 0001											
Trial: 1 / FS: 64 / Iter: 5	1 #1	2 #1	83.13		83.13	494791162.9	253333.08		Tx : 9895833333 Rx : 9895833333 Loss : 0 Loss% : 0.000	Min : 915 Max : 991 Avg : 932	
N9550-32D-Endpoint Set-1 - Flow Group 0001											

Trial: 1 / FS: 64 / Iter: 5	2 #1	1 #1	83.13	83.13	494791162.9	253333.08	Tx : 9895833333	Min : 913
							Rx : 9895833333	Max : 993
							Loss : 0	Avg : 930
N9550-32D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 64 / Iter: 6	1 #1	2 #1	85.94	83.31	495890498.4	253895.94	Tx : 10230654762	Min : 917
							Rx : 9917878521	Max : 8453
							Loss : 312776241	Avg : 8401
N9550-32D-Endpoint Set-1 - Flow Group 0001							Loss% : 3.057	
Trial: 1 / FS: 64 / Iter: 6	2 #1	1 #1	85.94	83.31	495890498.3	253895.94	Tx : 10230654762	Min : 915
							Rx : 9917878522	Max : 8451
							Loss : 312776240	Avg : 8399
N9550-32D-Endpoint Set-2 - Flow Group 0001							Loss% : 3.057	
Trial: 1 / FS: 64 / Iter: 7	1 #1	2 #1	84.53	83.31	495890662.0	253896.02	Tx : 10063244048	Min : 913
							Rx : 9917772985	Max : 8449
							Loss : 145471063	Avg : 8399
N9550-32D-Endpoint Set-1 - Flow Group 0001							Loss% : 1.446	
Trial: 1 / FS: 64 / Iter: 7	2 #1	1 #1	84.53	83.31	495890662.1	253896.02	Tx : 10063244048	Min : 919
							Rx : 9917772986	Max : 8449
							Loss : 145471062	Avg : 8398
N9550-32D-Endpoint Set-2 - Flow Group 0001							Loss% : 1.446	
Trial: 1 / FS: 64 / Iter: 8	1 #1	2 #1	83.83	83.31	495890685.9	253896.03	Tx : 9979538690	Min : 916
							Rx : 9917821941	Max : 8450
							Loss : 61716749	Avg : 8398
N9550-32D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.618	
Trial: 1 / FS: 64 / Iter: 8	2 #1	1 #1	83.83	83.31	495890686.0	253896.03	Tx : 9979538690	Min : 912
							Rx : 9917821941	Max : 8451
							Loss : 61716749	Avg : 8397
N9550-32D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.618	
Trial: 1 / FS: 128 / Iter: 1	1 #1	2 #1	10.00	10.00	33783783.8	34594.60	Tx : 675675676	Min : 910
							Rx : 675675676	Max : 930
							Loss : 0	Avg : 914
N9550-32D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 128 / Iter: 1	2 #1	1 #1	10.00	10.00	33783783.8	34594.60	Tx : 675675676	Min : 911
							Rx : 675675676	Max : 931
							Loss : 0	Avg : 915
N9550-32D-Endpoint Set-2 - Flow Group 0001							Loss% : 0.000	
Trial: 1 / FS: 128 / Iter: 2	1 #1	2 #1	55.00	55.00	185810197.8	190269.64	Tx : 3716216216	Min : 910
							Rx : 3716216216	Max : 947
							Loss : 0	Avg : 923
N9550-32D-Endpoint Set-1 - Flow Group 0001							Loss% : 0.000	

Trial: 1 / FS: 128 / Iter: 2	2 #1	1 #1	55.00	55.00	185810197.7	190269.64	Tx : 3716216216	Min : 909
							Rx : 3716216216	Max : 945
							Loss : 0	Avg : 921
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 3	1 #1	2 #1	77.50	77.50	261825619.9	268109.44	Tx : 5236486486	Min : 909
							Rx : 5236486486	Max : 946
							Loss : 0	Avg : 923
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 3	2 #1	1 #1	77.50	77.50	261825619.9	268109.44	Tx : 5236486486	Min : 911
							Rx : 5236486486	Max : 948
							Loss : 0	Avg : 925
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 4	1 #1	2 #1	88.75	88.75	299832515.3	307028.50	Tx : 5996621622	Min : 912
							Rx : 5996621622	Max : 949
							Loss : 0	Avg : 927
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 4	2 #1	1 #1	88.75	88.75	299832515.2	307028.50	Tx : 5996621622	Min : 910
							Rx : 5996621622	Max : 947
							Loss : 0	Avg : 925
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 5	1 #1	2 #1	94.38	94.38	318836247.4	326488.32	Tx : 6376689189	Min : 915
							Rx : 6376689189	Max : 951
							Loss : 0	Avg : 930
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 5	2 #1	1 #1	94.38	94.38	318836247.5	326488.32	Tx : 6376689189	Min : 912
							Rx : 6376689189	Max : 950
							Loss : 0	Avg : 929
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 6	1 #1	2 #1	97.19	97.19	328335620.3	336215.68	Tx : 6566722973	Min : 913
							Rx : 6566722973	Max : 949
							Loss : 0	Avg : 930
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 6	2 #1	1 #1	97.19	97.19	328335620.3	336215.68	Tx : 6566722973	Min : 915
							Rx : 6566722973	Max : 950
							Loss : 0	Avg : 930
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 7	1 #1	2 #1	98.59	98.59	333086120.7	341080.19	Tx : 6661739865	Min : 916
							Rx : 6661739865	Max : 949
							Loss : 0	Avg : 930
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 128 / Iter: 7	2 #1	1 #1	98.59	98.59	333086120.7	341080.19	Tx : 6661739865 Rx : 6661739865 Loss : 0 Loss% : 0.000	Min : 916 Max : 950 Avg : 931
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 8	1 #1	2 #1	99.30	99.30	335460537.2	343511.59	Tx : 6709248311 Rx : 6709248311 Loss : 0 Loss% : 0.000	Min : 915 Max : 950 Avg : 932
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 8	2 #1	1 #1	99.30	99.30	335460537.1	343511.59	Tx : 6709248311 Rx : 6709248311 Loss : 0 Loss% : 0.000	Min : 913 Max : 950 Avg : 931
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 9	1 #1	2 #1	100.00	100.00	337837837.3	345945.95	Tx : 6756756757 Rx : 6756756757 Loss : 0 Loss% : 0.000	Min : 913 Max : 951 Avg : 936
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 128 / Iter: 9	2 #1	1 #1	100.00	100.00	337837837.3	345945.95	Tx : 6756756757 Rx : 6756756757 Loss : 0 Loss% : 0.000	Min : 915 Max : 956 Avg : 937
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 1	1 #1	2 #1	10.00	10.00	18115942.0	37101.45	Tx : 362318841 Rx : 362318841 Loss : 0 Loss% : 0.000	Min : 917 Max : 937 Avg : 921
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 1	2 #1	1 #1	10.00	10.00	18115942.0	37101.45	Tx : 362318841 Rx : 362318841 Loss : 0 Loss% : 0.000	Min : 916 Max : 936 Avg : 919
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 2	1 #1	2 #1	55.00	55.00	99637645.9	204057.90	Tx : 1992753623 Rx : 1992753623 Loss : 0 Loss% : 0.000	Min : 916 Max : 955 Avg : 930
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 2	2 #1	1 #1	55.00	55.00	99637645.9	204057.90	Tx : 1992753623 Rx : 1992753623 Loss : 0 Loss% : 0.000	Min : 915 Max : 953 Avg : 929
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 3	1 #1	2 #1	77.50	77.50	140398600.4	287536.33	Tx : 2807971014 Rx : 2807971014 Loss : 0 Loss% : 0.000	Min : 915 Max : 955 Avg : 929
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 256 / Iter: 3	2 #1	1 #1	77.50	77.50	140398600.4	287536.33	Tx : 2807971014	Min : 915
							Rx : 2807971014	Max : 953
							Loss : 0	Avg : 928
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 4	1 #1	2 #1	88.75	88.75	160778772.1	329274.93	Tx : 3215579710	Min : 919
							Rx : 3215579710	Max : 956
							Loss : 0	Avg : 933
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 4	2 #1	1 #1	88.75	88.75	160778772.1	329274.93	Tx : 3215579710	Min : 917
							Rx : 3215579710	Max : 956
							Loss : 0	Avg : 931
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 5	1 #1	2 #1	94.38	94.38	170968711.1	350143.92	Tx : 3419384058	Min : 921
							Rx : 3419384058	Max : 979
							Loss : 0	Avg : 954
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 5	2 #1	1 #1	94.38	94.38	170968711.1	350143.92	Tx : 3419384058	Min : 918
							Rx : 3419384058	Max : 978
							Loss : 0	Avg : 953
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 6	1 #1	2 #1	97.19	97.19	176064813.5	360580.74	Tx : 3521286232	Min : 918
							Rx : 3521286232	Max : 980
							Loss : 0	Avg : 956
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 6	2 #1	1 #1	97.19	97.19	176064813.5	360580.74	Tx : 3521286232	Min : 918
							Rx : 3521286232	Max : 977
							Loss : 0	Avg : 955
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 7	1 #1	2 #1	98.59	98.59	178611296.9	365795.94	Tx : 3572237319	Min : 920
							Rx : 3572237319	Max : 978
							Loss : 0	Avg : 956
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 7	2 #1	1 #1	98.59	98.59	178611296.9	365795.94	Tx : 3572237319	Min : 923
							Rx : 3572237319	Max : 978
							Loss : 0	Avg : 957
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 8	1 #1	2 #1	99.30	99.30	179885182.3	368404.85	Tx : 3597712862	Min : 922
							Rx : 3597712862	Max : 980
							Loss : 0	Avg : 959
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 256 / Iter: 8	2 #1	1 #1	99.30	99.30	179885182.4	368404.85	Tx : 3597712862 Rx : 3597712862 Loss : 0 Loss% : 0.000	Min : 920 Max : 977 Avg : 957
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 9	1 #1	2 #1	100.00	100.00	181159419.8	371014.49	Tx : 3623188406 Rx : 3623188406 Loss : 0 Loss% : 0.000	Min : 920 Max : 985 Avg : 966
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 256 / Iter: 9	2 #1	1 #1	100.00	100.00	181159419.9	371014.49	Tx : 3623188406 Rx : 3623188406 Loss : 0 Loss% : 0.000	Min : 920 Max : 980 Avg : 965
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 1	1 #1	2 #1	10.00	10.00	9398496.2	38496.24	Tx : 187969925 Rx : 187969925 Loss : 0 Loss% : 0.000	Min : 920 Max : 940 Avg : 923
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 1	2 #1	1 #1	10.00	10.00	9398496.2	38496.24	Tx : 187969925 Rx : 187969925 Loss : 0 Loss% : 0.000	Min : 918 Max : 940 Avg : 923
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 2	1 #1	2 #1	55.00	55.00	51691691.3	211729.17	Tx : 1033834586 Rx : 1033834586 Loss : 0 Loss% : 0.000	Min : 918 Max : 956 Avg : 930
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 2	2 #1	1 #1	55.00	55.00	51691691.4	211729.17	Tx : 1033834586 Rx : 1033834586 Loss : 0 Loss% : 0.000	Min : 915 Max : 955 Avg : 929
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 3	1 #1	2 #1	77.50	77.50	72838392.6	298346.06	Tx : 1456766917 Rx : 1456766917 Loss : 0 Loss% : 0.000	Min : 917 Max : 958 Avg : 930
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 3	2 #1	1 #1	77.50	77.50	72838392.7	298346.06	Tx : 1456766917 Rx : 1456766917 Loss : 0 Loss% : 0.000	Min : 915 Max : 956 Avg : 929
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 4	1 #1	2 #1	88.75	88.75	83411531.6	341653.63	Tx : 1668233083 Rx : 1668233083 Loss : 0 Loss% : 0.000	Min : 919 Max : 957 Avg : 932
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 512 / Iter: 4	2 #1	1 #1	88.75	88.75	83411531.6	341653.63	Tx : 1668233083 Rx : 1668233083 Loss : 0 Loss% : 0.000	Min : 918 Max : 955 Avg : 931
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 5	1 #1	2 #1	94.38	94.38	88698249.2	363308.03	Tx : 1773966165 Rx : 1773966165 Loss : 0 Loss% : 0.000	Min : 920 Max : 958 Avg : 934
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 5	2 #1	1 #1	94.38	94.38	88698249.2	363308.03	Tx : 1773966165 Rx : 1773966165 Loss : 0 Loss% : 0.000	Min : 919 Max : 956 Avg : 933
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 6	1 #1	2 #1	97.19	97.19	91341796.7	374136.00	Tx : 1826832707 Rx : 1826832707 Loss : 0 Loss% : 0.000	Min : 921 Max : 958 Avg : 934
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 6	2 #1	1 #1	97.19	97.19	91341796.7	374136.00	Tx : 1826832707 Rx : 1826832707 Loss : 0 Loss% : 0.000	Min : 920 Max : 956 Avg : 933
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 7	1 #1	2 #1	98.59	98.59	92663309.9	379548.92	Tx : 1853265977 Rx : 1853265977 Loss : 0 Loss% : 0.000	Min : 923 Max : 959 Avg : 936
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 7	2 #1	1 #1	98.59	98.59	92663310.0	379548.92	Tx : 1853265977 Rx : 1853265977 Loss : 0 Loss% : 0.000	Min : 921 Max : 956 Avg : 934
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 8	1 #1	2 #1	99.30	99.30	93324049.5	382255.31	Tx : 1866482613 Rx : 1866482613 Loss : 0 Loss% : 0.000	Min : 926 Max : 960 Avg : 938
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 8	2 #1	1 #1	99.30	99.30	93324049.5	382255.31	Tx : 1866482613 Rx : 1866482613 Loss : 0 Loss% : 0.000	Min : 923 Max : 958 Avg : 936
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 512 / Iter: 9	1 #1	2 #1	100.00	100.00	93984962.3	384962.41	Tx : 1879699248 Rx : 1879699248 Loss : 0 Loss% : 0.000	Min : 922 Max : 963 Avg : 946
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 512 / Iter: 9	2 #1	1 #1	100.00	100.00	93984962.3	384962.41	Tx : 1879699248 Rx : 1879699248 Loss : 0 Loss% : 0.000	Min : 924 Max : 962 Avg : 945
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 1	1 #1	2 #1	10.00	10.00	4789272.0	39233.72	Tx : 95785441 Rx : 95785441 Loss : 0 Loss% : 0.000	Min : 921 Max : 940 Avg : 925
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 1	2 #1	1 #1	10.00	10.00	4789272.0	39233.72	Tx : 95785441 Rx : 95785441 Loss : 0 Loss% : 0.000	Min : 920 Max : 940 Avg : 923
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 2	1 #1	2 #1	55.00	55.00	26340998.6	215785.46	Tx : 526819923 Rx : 526819923 Loss : 0 Loss% : 0.000	Min : 920 Max : 943 Avg : 925
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 2	2 #1	1 #1	55.00	55.00	26340998.6	215785.46	Tx : 526819923 Rx : 526819923 Loss : 0 Loss% : 0.000	Min : 918 Max : 943 Avg : 923
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 3	1 #1	2 #1	77.50	77.50	37116833.9	304061.10	Tx : 742337165 Rx : 742337165 Loss : 0 Loss% : 0.000	Min : 920 Max : 950 Avg : 926
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 3	2 #1	1 #1	77.50	77.50	37116833.9	304061.10	Tx : 742337165 Rx : 742337165 Loss : 0 Loss% : 0.000	Min : 918 Max : 947 Avg : 925
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 4	1 #1	2 #1	88.75	88.75	42504794.2	348199.27	Tx : 850095785 Rx : 850095785 Loss : 0 Loss% : 0.000	Min : 921 Max : 961 Avg : 936
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 4	2 #1	1 #1	88.75	88.75	42504794.2	348199.27	Tx : 850095785 Rx : 850095785 Loss : 0 Loss% : 0.000	Min : 919 Max : 960 Avg : 934
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 5	1 #1	2 #1	94.38	94.38	45198777.5	370268.39	Tx : 903975096 Rx : 903975096 Loss : 0 Loss% : 0.000	Min : 924 Max : 960 Avg : 938
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1024 / Iter: 5	2 #1	1 #1	94.38	94.38	45198777.5	370268.39	Tx : 903975096 Rx : 903975096 Loss : 0 Loss% : 0.000	Min : 921 Max : 959 Avg : 937
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 6	1 #1	2 #1	97.19	97.19	46545708.4	381302.44	Tx : 930914751 Rx : 930914751 Loss : 0 Loss% : 0.000	Min : 925 Max : 962 Avg : 940
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 6	2 #1	1 #1	97.19	97.19	46545708.4	381302.44	Tx : 930914751 Rx : 930914751 Loss : 0 Loss% : 0.000	Min : 924 Max : 959 Avg : 938
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 7	1 #1	2 #1	98.59	98.59	47219230.0	386819.93	Tx : 944384579 Rx : 944384579 Loss : 0 Loss% : 0.000	Min : 927 Max : 962 Avg : 941
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 7	2 #1	1 #1	98.59	98.59	47219230.0	386819.93	Tx : 944384579 Rx : 944384579 Loss : 0 Loss% : 0.000	Min : 923 Max : 961 Avg : 940
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 8	1 #1	2 #1	99.30	99.30	47555975.8	389578.55	Tx : 951119492 Rx : 951119492 Loss : 0 Loss% : 0.000	Min : 928 Max : 962 Avg : 941
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 8	2 #1	1 #1	99.30	99.30	47555975.8	389578.55	Tx : 951119492 Rx : 951119492 Loss : 0 Loss% : 0.000	Min : 925 Max : 962 Avg : 942
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 9	1 #1	2 #1	100.00	100.00	47892720.2	392337.16	Tx : 957854406 Rx : 957854406 Loss : 0 Loss% : 0.000	Min : 925 Max : 968 Avg : 949
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1024 / Iter: 9	2 #1	1 #1	100.00	100.00	47892720.2	392337.16	Tx : 957854406 Rx : 957854406 Loss : 0 Loss% : 0.000	Min : 924 Max : 968 Avg : 950
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 1	1 #1	2 #1	10.00	10.00	3846153.8	39384.62	Tx : 76923077 Rx : 76923077 Loss : 0 Loss% : 0.000	Min : 920 Max : 939 Avg : 923
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1280 / Iter: 1	2 #1	1 #1	10.00	10.00	3846153.8	39384.62	Tx : 76923077 Rx : 76923077 Loss : 0 Loss% : 0.000	Min : 920 Max : 940 Avg : 924
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 2	1 #1	2 #1	55.00	55.00	21153843.0	216615.35	Tx : 423076923 Rx : 423076923 Loss : 0 Loss% : 0.000	Min : 921 Max : 946 Avg : 925
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 2	2 #1	1 #1	55.00	55.00	21153843.0	216615.35	Tx : 423076923 Rx : 423076923 Loss : 0 Loss% : 0.000	Min : 920 Max : 942 Avg : 924
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 3	1 #1	2 #1	77.50	77.50	29807682.2	305230.67	Tx : 596153846 Rx : 596153846 Loss : 0 Loss% : 0.000	Min : 920 Max : 942 Avg : 925
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 3	2 #1	1 #1	77.50	77.50	29807682.2	305230.67	Tx : 596153846 Rx : 596153846 Loss : 0 Loss% : 0.000	Min : 919 Max : 940 Avg : 923
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 4	1 #1	2 #1	88.75	88.75	34134607.7	349538.38	Tx : 682692308 Rx : 682692308 Loss : 0 Loss% : 0.000	Min : 920 Max : 950 Avg : 927
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 4	2 #1	1 #1	88.75	88.75	34134607.7	349538.38	Tx : 682692308 Rx : 682692308 Loss : 0 Loss% : 0.000	Min : 919 Max : 945 Avg : 925
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 5	1 #1	2 #1	94.38	94.38	36298052.4	371692.06	Tx : 725961538 Rx : 725961538 Loss : 0 Loss% : 0.000	Min : 920 Max : 947 Avg : 928
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 5	2 #1	1 #1	94.38	94.38	36298052.4	371692.06	Tx : 725961538 Rx : 725961538 Loss : 0 Loss% : 0.000	Min : 918 Max : 948 Avg : 928
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 6	1 #1	2 #1	97.19	97.19	37379793.3	382769.08	Tx : 747596154 Rx : 747596154 Loss : 0 Loss% : 0.000	Min : 921 Max : 952 Avg : 931
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1280 / Iter: 6	2 #1	1 #1	97.19	97.19	37379793.3	382769.08	Tx : 747596154 Rx : 747596154 Loss : 0 Loss% : 0.000	Min : 920 Max : 950 Avg : 928
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 7	1 #1	2 #1	98.59	98.59	37920645.1	388307.41	Tx : 758413462 Rx : 758413462 Loss : 0 Loss% : 0.000	Min : 922 Max : 953 Avg : 933
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 7	2 #1	1 #1	98.59	98.59	37920645.1	388307.41	Tx : 758413462 Rx : 758413462 Loss : 0 Loss% : 0.000	Min : 921 Max : 946 Avg : 929
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 8	1 #1	2 #1	99.30	99.30	38191113.7	391077.00	Tx : 763822115 Rx : 763822115 Loss : 0 Loss% : 0.000	Min : 922 Max : 950 Avg : 932
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 8	2 #1	1 #1	99.30	99.30	38191113.7	391077.00	Tx : 763822115 Rx : 763822115 Loss : 0 Loss% : 0.000	Min : 921 Max : 948 Avg : 930
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 9	1 #1	2 #1	100.00	100.00	38461538.4	393846.15	Tx : 769230769 Rx : 769230769 Loss : 0 Loss% : 0.000	Min : 925 Max : 951 Avg : 937
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1280 / Iter: 9	2 #1	1 #1	100.00	100.00	38461538.4	393846.15	Tx : 769230769 Rx : 769230769 Loss : 0 Loss% : 0.000	Min : 922 Max : 954 Avg : 936
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 1	1 #1	2 #1	10.00	10.00	3250975.3	39479.84	Tx : 65019506 Rx : 65019506 Loss : 0 Loss% : 0.000	Min : 923 Max : 942 Avg : 926
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 1	2 #1	1 #1	10.00	10.00	3250975.3	39479.84	Tx : 65019506 Rx : 65019506 Loss : 0 Loss% : 0.000	Min : 924 Max : 943 Avg : 927
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 2	1 #1	2 #1	55.00	55.00	17880366.4	217139.17	Tx : 357607282 Rx : 357607282 Loss : 0 Loss% : 0.000	Min : 922 Max : 941 Avg : 926
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1518 / Iter: 2	2 #1	1 #1	55.00	55.00	17880366.4	217139.17	Tx : 357607282	Min : 923
							Rx : 357607282	Max : 943
							Loss : 0	Avg : 927
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 3	1 #1	2 #1	77.50	77.50	25195064.9	305968.87	Tx : 503901170	Min : 923
							Rx : 503901170	Max : 945
							Loss : 0	Avg : 928
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 3	2 #1	1 #1	77.50	77.50	25195064.9	305968.87	Tx : 503901170	Min : 921
							Rx : 503901170	Max : 941
							Loss : 0	Avg : 925
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 4	1 #1	2 #1	88.75	88.75	28852417.6	350383.76	Tx : 577048114	Min : 924
							Rx : 577048114	Max : 950
							Loss : 0	Avg : 931
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 4	2 #1	1 #1	88.75	88.75	28852417.6	350383.76	Tx : 577048114	Min : 922
							Rx : 577048114	Max : 948
							Loss : 0	Avg : 929
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 5	1 #1	2 #1	94.38	94.38	30681096.4	372591.23	Tx : 613621586	Min : 923
							Rx : 613621586	Max : 950
							Loss : 0	Avg : 930
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 5	2 #1	1 #1	94.38	94.38	30681096.4	372591.23	Tx : 613621586	Min : 921
							Rx : 613621586	Max : 948
							Loss : 0	Avg : 929
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 6	1 #1	2 #1	97.19	97.19	31595420.6	383694.79	Tx : 631908322	Min : 924
							Rx : 631908322	Max : 951
							Loss : 0	Avg : 933
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 6	2 #1	1 #1	97.19	97.19	31595420.6	383694.79	Tx : 631908322	Min : 923
							Rx : 631908322	Max : 950
							Loss : 0	Avg : 930
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 7	1 #1	2 #1	98.59	98.59	32052566.2	389246.36	Tx : 641051691	Min : 923
							Rx : 641051691	Max : 950
							Loss : 0	Avg : 931
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								

Trial: 1 / FS: 1518 / Iter: 7	2 #1	1 #1	98.59	98.59	32052566.2	389246.36	Tx : 641051691	Min : 925
							Rx : 641051691	Max : 951
							Loss : 0	Avg : 933
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 8	1 #1	2 #1	99.30	99.30	32281169.0	392022.52	Tx : 645623375	Min : 925
							Rx : 645623375	Max : 951
							Loss : 0	Avg : 933
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 8	2 #1	1 #1	99.30	99.30	32281169.0	392022.52	Tx : 645623375	Min : 925
							Rx : 645623375	Max : 950
							Loss : 0	Avg : 933
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 9	1 #1	2 #1	100.00	100.00	32509752.9	394798.44	Tx : 650195059	Min : 926
							Rx : 650195059	Max : 953
							Loss : 0	Avg : 936
							Loss% : 0.000	
N9550-32D-Endpoint Set-1 - Flow Group 0001								
Trial: 1 / FS: 1518 / Iter: 9	2 #1	1 #1	100.00	100.00	32509752.9	394798.44	Tx : 650195059	Min : 928
							Rx : 650195059	Max : 950
							Loss : 0	Avg : 935
							Loss% : 0.000	
N9550-32D-Endpoint Set-2 - Flow Group 0001								

Theoretical maximum Frame Rates (frames/second) for different frame sizes (bytes)

Speed	64	128	256	512	1024	1280	1518
10 Mbps	14881	8446	4529	2350	1198	962	813
100 Mbps	148810	84460	45290	23497	11973	9616	8128
1000 Mbps	1488096	844595	452899	234963	119732	96154	81275
10 Gbps	14880952	8445946	4528986	2349625	1197318	961539	812744
25 Gbps	37202380	21114864	11322463	5874060	2993295	2403846	2031859
40 Gbps	59523809	33783783	18115942	9398496	4789272	3846153	3250975
100 Gbps	148809523	84459459	45289855	23496240	11973180	9615384	8127438
155 Mbps (Oc - 3)	288000	145116	72840	36491	18263	14614	12324
622 Mbps (Oc - 12)	1152000	580465	291362	145965	73054	58454	49296
2488 Mbps (Oc - 48)	4608000	2321860	1165447	583860	292215	233817	197182
9952 Mbps (Oc - 192)	18432000	9287442	4661790	2335439	1168859	935270	788730